

Voltage Supervisor

Features


- Low Supply Current: 1 μA (Typical),10 μA (Max.)
- Precision Monitoring Trip Point Options:
 - 2.9V and 4.6V (Standard Offerings)
 - 2.0V to 4.7V in 100 mV Increments,
- (Contact the local Microchip Sales Office)
- Resets Microcontroller in a Power-loss Event
- Reset Delay Time Out Option:
- 1.4 ms, 30 ms, 200 ms, or 1.6s (Typical)
- Watchdog Timer Input Time Out Options:
- 6.3 ms, 102 ms, 1.6s, or 25.6s (Typical)
- Manual Reset (MR) Input (Active-low)
- Single and Complementary Reset Output(s)
- Reset Output Options:
 - Push-Pull (Active-high or Active-low)
 - Open-Drain (Internal or External Pull-up)
- Temperature Range:
 - -40°C to +85°C for Trip Points 2.0 to 2.4V and,
 - -40°C to + 125°C for Trip Points > 2.5V
- Voltage Range: 1.0V to 5.5V
- Lead Free Packaging

Description


The MCP131X/2X are voltage supervisor devices designed to keep a microcontroller in Reset until the system voltage has reached and stabilized at the proper level for reliable system operation. The table below shows the available features for these devices.

Device Features

Package Types



Block Diagram



	Reso	et Output A		Rese	et Output B			
Device	Туре	Pull-up Resistor	Active Level	Туре	Pull-up Active Resistor Level		WDI Input	MR Input
MCP1316	Push-Pull		Low	_	_	_	Yes	Yes
MCP1316M	Open-Drain	Internal	Low	_	_	_	Yes	Yes
MCP1317	Push-Pull	_	High	_	_	_	Yes	Yes
MCP1318	Push-Pull	_	Low	Push-Pull	_	High	Yes	No
MCP1318M	Open-Drain	Internal	Low	Push-Pull	_	High	Yes	No
MCP1319	Push-Pull	—	Low	Push-Pull	_	High	No	Yes
MCP1319M	Open-Drain	Internal	Low	Push-Pull	_	High	No	Yes
MCP1320	Open-Drain	External	Low	_	_	_	Yes	Yes
MCP1321	Open-Drain	External	Low	Push-Pull	_	High	Yes	No
MCP1322	Open-Drain	External	Low	Push-Pull	_	High	No	Yes

NOTES:

1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings†

Supply Voltage (V_{DD} to V_{SS})
Input current (V _{DD})10 mA
Output current (RST)10 mA
Voltage on all inputs and outputs, except Open-Drain $\overline{\text{RST}}$ (with no internal pull-up resistor), w.r.t. V_{SS} 0.6V to (V_{DD} + 1.0V)
Voltage on Open-Drain RST
(with no internal pull-up resistor) w.r.t. $V_{\rm SS}$ \ldots -0.6V to 13.5V
Storage temperature
Ambient temp. with power applied40°C to +125°C
Maximum Junction temp. with power applied +150°C
Power Dissipation ($T_A \le +70^{\circ}C$):
5-Pin SOT-23A240 mW
ESD protection on all pins $\ge 4 \text{ kV}$

† Notice: Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

DC CHARACTERISTICS

Electrical Specifications: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (only **MCP1320**, **MCP1321** and **MCP1322**), T_A = -40°C to +125°C.

	<i>// A</i>					
Parameters	Sym	Min	Тур	Max	Units	Conditions
Operating Voltage Range	V _{DD}	1.0	_	5.5	V	
Specified V_{DD} Value to V_{OUT} Low	V _{DD}	1.0	_		V	l _{RST} = 10 μA, V _{RST} < 0.3V
Operating Current:	I _{DD}		5	10	μA	Watchdog Timer Active
		_	1	2	μA	Watchdog Timer Inactive
		_	1	2	μA	V _{DD} < V _{TRIP}
		_	5	10	μA	Reset Delay Timer Active

Note 1: Trip point is ±1.5% from typical value.

- **2:** Trip point is $\pm 2.5\%$ from typical value.
- **3:** Hysteresis is minimum = 1%, maximum = 6% at +25°C.
- 4: This specification allows this device to be used in PIC[®] microcontroller applications that require the In-Circuit Serial Programming[™] (ICSP[™]) feature (see device-specific programming specifications for voltage requirements). The total time that the RST pin can be above the maximum device operational voltage (5.5V) is 100s. Current into the RST pin should be limited to 2 mA. It is recommended that the device operational temperature be maintained between 0°C to +70°C (+25°C preferred). For additional information, refer to Figure 2-35.
- 5: This parameter is established by characterization and is not 100% tested.
- 6: Custom ordered voltage trip point; minimum order volume requirement. Information available upon request.

Electrical Specifications: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (only **MCP1320**, **MCP1321** and **MCP1322**), T_A = -40°C to +125°C.

Param	eters	Sym	Min	Тур	Max	Units	Conditions
V _{DD} Trip Point	MCP13XX-20	V _{TRIP}	1.970	2.00	2.030	V	T _A = +25°C (Note 1)
	(Note 6)		1.950	2.00	2.050	V	T _A = -40°C to +85°C (Note 2)
	MCP13XX-21		2.069	2.10	2.132	V	T _A = +25°C (Note 1)
	(Note 6)		2.048	2.10	2.153	V	T _A = -40°C to +85°C (Note 2)
	MCP13XX-22		2.167	2.20	2.233	V	T _A = +25°C (Note 1)
	(Note 6)		2.145	2.20	2.255	V	T _A = -40°C to +85°C (Note 2)
	MCP13XX-23		2.266	2.30	2.335	V	T _A = +25°C (Note 1)
	(Note 6)		2.243	2.30	2.358	V	T _A = -40°C to +85°C (Note 2)
	MCP13XX-24		2.364	2.40	2.436	V	T _A = +25°C (Note 1)
	(Note 6)		2.340	2.40	2.460	V	T _A = -40°C to +85°C (Note 2)
	MCP13XX-25		2.463	2.50	2.538	V	T _A = +25°C (Note 1)
	(Note 6)		2.438	2.50	2.563	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-26		2.561	2.60	2.639	V	T _A = +25°C (Note 1)
	(Note 6)		2.535	2.60	2.665	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-27		2.660	2.70	2.741	V	T _A = +25°C (Note 1)
	(Note 6)		2.633	2.70	2.768	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-28		2.758	2.80	2.842	V	T _A = +25°C (Note 1)
	(Note 6)		2.730	2.80	2.870	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-29		2.857	2.90	2.944	V	T _A = +25°C (Note 1)
			2.828	2.90	2.973	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-30		2.955	3.00	3.045	V	T _A = +25°C (Note 1)
	(Note 6)		2.925	3.00	3.075	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-31		3.054	3.10	3.147	V	T _A = +25°C (Note 1)
	(Note 6)		3.023	3.10	3.178	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-32		3.152	3.20	3.248	V	T _A = +25°C (Note 1)
	(Note 6)		3.120	3.20	3.280	V	T _A = -40°C to +125°C (Note 2
	MCP13XX-33		3.251	3.30	3.350	V	T _A = +25°C (Note 1)
	(Note 6)		3.218	3.30	3.383	V	T _A = -40°C to +125°C (Note 2

Note 1: Trip point is $\pm 1.5\%$ from typical value.

- **2:** Trip point is ±2.5% from typical value.
- **3:** Hysteresis is minimum = 1%, maximum = 6% at +25°C.
- 4: This specification allows this device to be used in PIC[®] microcontroller applications that require the In-Circuit Serial Programming[™] (ICSP[™]) feature (see device-specific programming specifications for voltage requirements). The total time that the RST pin can be above the maximum device operational voltage (5.5V) is 100s. Current into the RST pin should be limited to 2 mA. It is recommended that the device operational temperature be maintained between 0°C to +70°C (+25°C preferred). For additional information, refer to Figure 2-35.
- 5: This parameter is established by characterization and is not 100% tested.
- 6: Custom ordered voltage trip point; minimum order volume requirement. Information available upon request.

(only MCP1320, MCP1				_			A 11:1
Paramete	ers	Sym	Min	Тур	Max	Units	Conditions
V _{DD} Trip Point (Con't)	MCP13XX-34	V _{TRIP}	3.349	3.40	3.451	V	T _A = +25°C (Note 1)
	(Note 6)		3.315	3.40	3.385	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-35		3.448	3.50	3.553	V	T _A = +25°C (Note 1)
	(Note 6)		3.413	3.50	3.588	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-36		3.546	3.60	3.654	V	T _A = +25°C (Note 1)
	(Note 6)		3.510	3.60	3.690	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-37		3.645	3.70	3.756	V	T _A = +25°C (Note 1)
	(Note 6)		3.608	3.70	3.793	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-38		3.743	3.80	3.857	V	T _A = +25°C (Note 1)
	(Note 6)		3.705	3.80	3.895	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-39		3.842	3.90	3.959	V	T _A = +25°C (Note 1)
	(Note 6)		3.803	3.90	3.998	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-40		3.940	4.00	4.060	V	T _A = +25°C (Note 1)
	(Note 6)		3.900	4.00	4.100	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-41		4.039	4.10	4.162	V	T _A = +25°C (Note 1)
	(Note 6)		3.998	4.10	4.203	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-42		4.137	4.20	4.263	V	T _A = +25°C (Note 1)
	(Note 6)		4.095	4.20	4.305	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-43		4.236	4.30	4.365	V	T _A = +25°C (Note 1)
	(Note 6)		4.193	4.30	4.408	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-44		4.334	4.40	4.466	V	T _A = +25°C (Note 1)
	(Note 6)		4.290	4.40	4.510	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-45		4.433	4.50	4.568	V	T _A = +25°C (Note 1)
	(Note 6)		4.388	4.50	4.613	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-46		4.531	4.60	4.669	V	T _A = +25°C (Note 1)
			4.485	4.60	4.715	V	T _A = -40°C to +125°C (Note 2)
	MCP13XX-47		4.630	4.70	4.771	V	T _A = +25°C (Note 1)
	(Note 6)		4.583	4.70	4.818	V	T _A = -40°C to +125°C (Note 2)
V _{DD} Trip Point Tempco		T _{TPCO}	_	±40	_	ppm/°C	

Note 1: Trip point is ±1.5% from typical value.

- **2:** Trip point is ±2.5% from typical value.
- **3:** Hysteresis is minimum = 1%, maximum = 6% at +25°C.
- 4: This specification allows this device to be used in PIC[®] microcontroller applications that require the In-Circuit Serial Programming[™] (ICSP[™]) feature (see device-specific programming specifications for voltage requirements). The total time that the RST pin can be above the maximum device operational voltage (5.5V) is 100s. Current into the RST pin should be limited to 2 mA. It is recommended that the device operational temperature be maintained between 0°C to +70°C (+25°C preferred). For additional information, refer to Figure 2-35.
- **5:** This parameter is established by characterization and is not 100% tested.
- 6: Custom ordered voltage trip point; minimum order volume requirement. Information available upon request.

Electrical Specifications: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only **MCP1320**, **MCP1321** and **MCP1322**), $T_A = -40^{\circ}$ C to $+125^{\circ}$ C.

Paramete	ers	Sym	Min	Тур	Max	Units	Conditions
Threshold Hysteresis	MCP13XX-20	V _{HYS}	0.020		0.120	V	T _A = +25°C (Note 3)
(Note 3)	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to +85°C
	MCP13XX-21		0.021	_	0.126	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+85^{\circ}C$
	MCP13XX-22		0.022	_	0.132	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+85^{\circ}C$
	MCP13XX-23		0.023	_	0.138	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C \text{ to } +85^{\circ}C$
	MCP13XX-24		0.024	_	0.144	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+85^{\circ}C$
	MCP13XX-25		0.025	—	0.150	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$
	MCP13XX-26		0.026	—	0.156	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-27		0.027	—	0.162	V	T _A = +25°C (Note 3)
	(Note 6)		(Note 6)			V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$
	MCP13XX-28		0.028	—	0.168	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-29		0.029	—	0.174	V	T _A = +25°C (Note 3)
				(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-30		0.030	—	0.180	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$
	MCP13XX-31		0.031	—	0.186	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$
	MCP13XX-32		0.032	—	0.192	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-33		0.033		0.198	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$

Note 1: Trip point is ±1.5% from typical value.

- **2:** Trip point is ±2.5% from typical value.
- **3:** Hysteresis is minimum = 1%, maximum = 6% at +25°C.
- 4: This specification allows this device to be used in PIC[®] microcontroller applications that require the In-Circuit Serial Programming[™] (ICSP[™]) feature (see device-specific programming specifications for voltage requirements). The total time that the RST pin can be above the maximum device operational voltage (5.5V) is 100s. Current into the RST pin should be limited to 2 mA. It is recommended that the device operational temperature be maintained between 0°C to +70°C (+25°C preferred). For additional information, refer to Figure 2-35.
- **5:** This parameter is established by characterization and is not 100% tested.
- 6: Custom ordered voltage trip point; minimum order volume requirement. Information available upon request.

Electrical Specifications: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only MCP1320, MCP1321 and MCP1322), $T_A = -40^{\circ}$ C to +125°C.

Paramete	ers	Sym	Min	Тур	Max	Units	Conditions
Threshold Hysteresis	MCP13XX-34	V _{HYS}	0.034	_	0.204	V	T _A = +25°C (Note 3)
(Continued) (Note 3)	(Note 6)		(Note 6)			V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$
	MCP13XX-35		0.035	_	0.210	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-36		0.036	—	0.216	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-37		0.037		0.222	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-38		0.038	—	0.228	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$
	MCP13XX-39		0.039	—	0.234	V	T _A = +25°C (Note 1)
	(Note 6)			(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-40		0.040	—	0.240	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-41		0.041	—	0.246	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-42		0.042	—	0.252	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-43		0.043	—	0.258	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-44		0.044	—	0.264	V	T _A = +25°C (Note 3)
	(Note 6)		((Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-45		0.045	—	0.270	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$
	MCP13XX-46		0.046	—	0.276	V	T _A = +25°C (Note 3)
				(Note 6)		V	$T_A = -40^{\circ}C$ to $+125^{\circ}C$
	MCP13XX-47		0.047	—	0.282	V	T _A = +25°C (Note 3)
	(Note 6)			(Note 6)		V	$T_{A} = -40^{\circ}C \text{ to } +125^{\circ}C$

Note 1: Trip point is $\pm 1.5\%$ from typical value.

- **2:** Trip point is ±2.5% from typical value.
- **3:** Hysteresis is minimum = 1%, maximum = 6% at + 25° C.
- 4: This specification allows this device to be used in PIC[®] microcontroller applications that require the In-Circuit Serial Programming[™] (ICSP[™]) feature (see device-specific programming specifications for voltage requirements). The total time that the RST pin can be above the maximum device operational voltage (5.5V) is 100s. Current into the RST pin should be limited to 2 mA. It is recommended that the device operational temperature be maintained between 0°C to +70°C (+25°C preferred). For additional information, refer to Figure 2-35.
- 5: This parameter is established by characterization and is not 100% tested.
- 6: Custom ordered voltage trip point; minimum order volume requirement. Information available upon request.

Electrical Specifications: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only **MCP1320**, **MCP1321** and **MCP1322**), $T_A = -40^{\circ}$ C to $+125^{\circ}$ C.

Paramete	ers	Sym	Min	Тур	Max	Units	Conditions
RST/RST Low-Level C	utput Voltage	V _{OL}		_	0.3	V	I_{OL} = 50 µA, 1.0V \leq V _{DD} \leq 1.5V
			_		0.3	V	$I_{OL} = 100 \ \mu A,$ $1.5V < V_{DD} \le 2.5V$
			_		0.3	V	I_{OL} = 2 mA, 2.5V $< V_{DD} \leq 4.5V$
			—	-	0.3	V	I_{OL} = 4 mA, V_{DD} > 4.5V
RST/RST High-Level C	Output Voltage	V _{OH}	V _{DD} – 0.7		_	V	$I_{OH} = 2.5 \text{ mA}, V_{DD} \ge 2.5 \text{ V}$
(Push-Pull Outputs onl	y)		V _{DD} – 0.7		_	V	$I_{OH} = 500 \ \mu\text{A}, \ V_{DD} \ge 1.5 \text{V}$
Input Low Voltage (MR	and WDI pins)	V_{IL}	V _{SS}		$0.3V_{DD}$	V	
Input High Voltage (MR and WDI pins)		V_{IH}	$0.7V_{DD}$	-	V _{DD}	V	
Open-Drain High Voltage on Output (Note 4)		V _{ODH}		_	13.5 (4)	V	Open-Drain Output pin only, $V_{DD} = 3.0V$, Time voltage > 5.5V applied ≤ 100 s, current into pin limited to 2 mA, +25°C operation recommended (Note 4, Note 5)
Input Leakage Current	(MR and WDI)	۱ _{IL}	—	—	±1	μA	$V_{SS} \leq V_{PIN} \leq V_{DD}$
Open-Drain Output Lea (MCP1316M, MCP131 MCP1319M, MCP1320 and MCP1322 only)	8M,	I _{OD}	_	0.003	1.0	μA	
Pull-up Resistance	MR pin	R _{PU}	—	52	—	kΩ	V _{DD} = 5.5V
	WDI pin			52	—	kΩ	V _{DD} = 5.5V
RST pin			—	4.7	—	kΩ	V _{DD} = 5.5V, MCP131XM devices only
Input Pin Capacitance	(MR and WDI)	CI		100	—	pF	
Output Pin <u>Cap</u> acitive (RST and RST)	Loading	Co	—	—	50	pF	This is the tester loading to meet the AC timing specifications.

Note 1: Trip point is ±1.5% from typical value.

- **2:** Trip point is ±2.5% from typical value.
- **3:** Hysteresis is minimum = 1%, maximum = 6% at +25°C.
- 4: This specification allows this device to be used in PIC[®] microcontroller applications that require the In-Circuit Serial Programming[™] (ICSP[™]) feature (see device-specific programming specifications for voltage requirements). The total time that the RST pin can be above the maximum device operational voltage (5.5V) is 100s. Current into the RST pin should be limited to 2 mA. It is recommended that the device operational temperature be maintained between 0°C to +70°C (+25°C preferred). For additional information, refer to Figure 2-35.
- **5:** This parameter is established by characterization and is not 100% tested.
- 6: Custom ordered voltage trip point; minimum order volume requirement. Information available upon request.




FIGURE 1-1: Device Voltage and Reset Pin Waveforms.

TABLE 1-1: DEVICE VOLTAGE AND RESET PIN TIMINGS

Electrical Specifications: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only **MCP1320**, **MCP1321**, and **MCP1322**), $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$.

Parameters	Sym	Min	Тур	Max	Units	Conditions
Falling V _{DD} Trip Point Detected to RST or RST Active	t _{RPD}		650		μs	$\begin{array}{l} V_{DD} \text{ ramped from} \\ V_{TRIPMAX} + 250 \text{ mV down to} \\ V_{TRIPMIN} - 200 \text{ mV}, \\ V_{DD} \text{ falling @ 5 mV/} \mu s, \\ C_L = 50 \text{ pF (Note 1)} \end{array}$
V _{DD} Rise Rate	t _{RR}		Note 3			
Reset active time	t _{RST}	1.0	1.4	2.0	ms	Note 2
(MR Rising Edge, POR/BOR		20	30	40	ms	Note 2
Inactive, or WDT time out) to RST/RST Inactive		140	200	280	ms	Standard Time Out
		1120	1600	2240	ms	Note 2
RST Rise Time after RST Active (Push-Pull Outputs only)	t _{RT}		5	_	μs	For RST 10% to 90% of V _{DD} , C _L = 50 pF (Note 1)
RST Rise Time after RST Inactive (Push-Pull Outputs only)			5	_	μs	For \overrightarrow{RST} 10% to 90% of V _{DD} , C _L = 50 pF (Note 1)
RST Fall Time after RST Inactive	t _{FT}		5	_	μs	For RST 90% to 10% of V _{DD} , C _L = 50 pF (Note 1)
RST Fall Time after RST Active		_	5		μs	For \overrightarrow{RST} 90% to 10% of V _{DD} , C _L = 50 pF (Note 1)

Note 1: These parameters are for design guidance only and are not 100% tested.

2: Custom ordered Reset active time; minimum order volume requirement.

3: Designed to be independent of V_{DD} rise rate. Device characterization was done with a rise rate as slow as 0.1 V/s (@ +25°C).





FIGURE 1-2: MR and Reset Pin Waveforms.

TABLE 1-2: MR AND RESET PIN TIMINGS

Electrical Specifications: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only **MCP1320**, **MCP1321**, and **MCP1322**), $T_A = -40^{\circ}$ C to $+125^{\circ}$ C.

Parameters	Sym	Min	Тур	Max	Units	Conditions
MR Pulse Width	t _{MR}	1	—		μs	
MR Active to RST/RST Active	t _{MRD}	_	235	-	ns	V _{DD} = 5.0V
MR Input Noise filter	t _{NF}		150		ns	V _{DD} = 5.0V

Note 1: These parameters are for design guidance only and are not 100% tested.



Note 1: The WDI pin was a weak pull-up resistor which is disabled after the 1st falling edge on the WDI pin.

FIGURE 1-3: WDI and Reset Pin Waveforms.

TABLE 1-3: WDI AND RESET PIN TIMINGS

Electrical Specifications: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only **MCP1320**, **MCP1321**, and **MCP1322**), $T_A = -40^{\circ}$ C to $+125^{\circ}$ C.

	1					
Parameters	Sym	Min	Тур	Max	Units	Conditions
WDI Pulse Width	t _{WP}	50			ns	
Watchdog Time Out Period	t _{WD}	4.3	6.3	9.3	ms	Note 1
		71	102	153	ms	Note 1
		1.12	1.6	2.4	sec	Standard Time Out
		17.9	25.6	38.4	sec	Note 1

Note 1: Custom ordered WatchDog Timer time out; minimum order volume requirement.

TEMPERATURE CHARACTERISTICS

Electrical Specifications: Unless otherwise noted, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only MCP1316), $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$.										
Parameters	Sym	Min	Тур	Max	Units	Conditions				
Temperature Ranges										
Specified Temperature Range	T _A	-40	_	+85	°C	MCP13XX-25 (or below)				
Specified Temperature Range	T _A	-40	—	+125	°C	Except MCP13XX-25 (or below)				
Maximum Junction Temperature	TJ		—	+150	°C					
Storage Temperature Range	Τ _Α	-65	—	+150	°C					
Package Thermal Resistances										
Thermal Resistance, 5L-SOT-23	θ_{JA}	_	220.7		°C/W					

NOTES:

2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.

Note: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only **MCP1316**; see **Figure 4-1**), $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$.




FIGURE 2-1: I_{DD} vs. Temperature (Reset Power-up Timer Inactive and Watchdog Timer Inactive) (**MCP1318M-4.6**).




FIGURE 2-2: I_{DD} vs. Temperature (Reset Power-up Timer Inactive and Watchdog Timer Inactive) (**MCP1319-2.9**).




FIGURE 2-3: I_{DD} vs. Temperature (Reset Power-up Timer Inactive and Watchdog Timer Inactive) (**MCP1316-2.0**).




FIGURE 2-4: I_{DD} vs. Temperature (Reset Power-up Timer Active) (**MCP1318M-4.6**).




FIGURE 2-5: I_{DD} vs. Temperature (Reset Power-up Timer Active) (**MCP1319-2.9**).




FIGURE 2-6: I_{DD} vs. Temperature (Reset Power-up Timer Active) (**MCP1316-2.0**).

Note: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (only MCP1316; see **Figure 4-1**), $T_A = -40^{\circ}C$ to $+125^{\circ}C$.





FIGURE 2-7: I_{DD} vs. Temperature (Watchdog Timer Active) (MCP1318M-4.6).



(Watchdog Timer Active) (MCP1319-2.9).




FIGURE 2-9: I_{DD} vs. Temperature (Watchdog Timer Active) (MCP1316-2.0).

Note: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only **MCP1316**; see **Figure 4-1**), $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$.




FIGURE 2-10: I_{DD} vs. V_{DD} (Reset Powerup Timer Inactive and Watchdog Timer Inactive) (**MCP1318M-4.6**).




FIGURE 2-11: I_{DD} vs. V_{DD} (Reset Powerup Timer Inactive and Watchdog Timer Inactive) (**MCP1319-2.9**).




FIGURE 2-12: I_{DD} vs. V_{DD} (Reset Powerup Timer Inactive and Watchdog Timer Inactive) (**MCP1316-2.0**).




FIGURE 2-13: I_{DD} vs. V_{DD} (Reset Powerup Timer Active or Watchdog Timer Active) (**MCP1318M-4.6**).




FIGURE 2-14: I_{DD} vs. V_{DD} (Reset Powerup Timer Active or Watchdog Timer Active) (**MCP1319-2.9**).




FIGURE 2-15: I_{DD} vs. V_{DD} (Reset Powerup Timer Active or Watchdog Timer Active) (**MCP1316-2.0**).

Note: Unless otherwise indicated, all limits are specified for $V_{DD} = 1V$ to 5.5V, $R_{PU} = 100 \text{ k}\Omega$ (only MCP1316; see Figure 4-1), $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$.




FIGURE 2-16: V_{TRIP} and V_{HYST} vs.Temperature (MCP1318M-4.6).




FIGURE 2-17: V_{TRIP} and V_{HYST} vs. Temperature (**MCP1319-2.9**).






FIGURE 2-18: V_{TRIP} and V_{HYST} vs. Temperature (**MCP1316-2.0**).








FIGURE 2-20: V_{OL} vs. I_{OL} (MCP1319-2.9).





FIGURE 2-21: V_{OL} vs. I_{OL} (MCP1316-2.0).



Note: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (**only MCP1316**; see **Figure 4-1**), T_A = -40°C to +125°C.






FIGURE 2-23: V_{OL} vs. Temperature (**MCP1319-2.9** @ V_{DD} = 2.7V).




FIGURE 2-24: V_{OL} vs. Temperature (**MCP1316-2-0** @ V_{DD} = 1.8V).




FIGURE 2-25: V_{OH} vs. I_{OH} (MCP1318M-4.6 @ +25°C).




FIGURE 2-26: V_{OH} vs. I_{OH} (MCP1319-2.9 @ +25°C).





FIGURE 2-27: V_{OH} vs. I_{OH} (**MCP1316-2.0** @ +25°C).

Note: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (only MCP1316; see Figure 4-1), T_A = -40°C to +125°C.








FIGURE 2-29: *t*_{RPD} vs. Temperature (**MCP1319-2.9**).




FIGURE 2-30: t_{RPD} vs. Temperature (MCP1316-2.0).




FIGURE 2-31: t_{RPU} vs. Temperature (MCP1318M-4.6).




FIGURE 2-32: t_{RPU} vs. Temperature (**MCP1319-2.9**).




FIGURE 2-33: t_{RPU} vs. Temperature (*MCP1316-2.0*).

Note: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (only MCP1316; see Figure 4-1), T_A = -40°C to +125°C.




FIGURE 2-34: Transient Duration vs. V_{TRIP} (min) – V_{DD} .




FIGURE 2-35: Open-Drain Leakage Current vs. Temperature (MCP1320-2.0).




FIGURE 2-36: MR Low to Reset Propagation Delay (MCP1318M-4.6).




FIGURE 2-37: MR Low to Reset Propagation Delay (MCP1319-2.9).




FIGURE 2-38: MR Low to Reset Propagation Delay (MCP1316-2.0).

Note: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (only MCP1316; see Figure 4-1), T_A = -40°C to +125°C.




FIGURE 2-39: V_{DD} Falling to Reset Propagation Delay vs. Temperature (**MCP1318M-4.6**).




FIGURE 2-40: V_{DD} Falling to Reset Propagation Delay vs. Temperature (**MCP1319-2.9**).




FIGURE 2-41: V_{DD} Falling to Reset Propagation Delay vs. Temperature (**MCP1316-2.0**).




FIGURE 2-42: Normalized Reset Time Out Period vs. Temperature (MCP1318M-4.6).




FIGURE 2-43: Normalized Reset Time Out Period vs. Temperature (MCP1319-2.9).




FIGURE 2-44: Normalized Reset Time Out Period vs. Temperature (MCP1316-2.0).

Note: Unless otherwise indicated, all limits are specified for V_{DD} = 1V to 5.5V, R_{PU} = 100 k Ω (only MCP1316; see **Figure 4-1**), $T_A = -40^{\circ}C$ to +125°C.





FIGURE 2-45: Normalized Watchdog Time Out Period vs. Temperature (MCP1318M-4.6).



Out Period vs. Temperature (MCP1319-2.9).




FIGURE 2-47: Normalized Watchdog Time Out Period vs. Temperature (MCP1316-2.0).




FIGURE 2-48: Max V_{DD} Transient Duration vs. Reset Threshold Overdrive.




FIGURE 2-49: "M" Part Number Pull-up Characteristics (MCP1318M-4.6).

NOTES:

3.0 PIN DESCRIPTION

The descriptions of the pins are listed in Table 3-1.

TABLE 3-1: PIN FUNCTION TABLE

Pin No.			Pin	Buffer/	
SOT23-5	Device	Symbol	Туре	Driver Type	Function
1	MCP1316M ⁽¹⁾ , MCP1318M ⁽¹⁾ , MCP1319M ⁽¹⁾ , MCP1320, MCP1321, MCP1322	RST	0	Open-Drain	 Reset Output (active-low) Goes active (Low) if one of these conditions occurs: 1. If V_{DD} falls below the selected Reset voltage threshold. 2. If the MR pin is forced low. 3. If the WDI pin does not detect an edge transition within the minimum selected time out period. 4. During power-up. V_{DD} Falling: Open-Drain = V_{DD} > V_{TRIP} L = V_{DD} < V_{TRIP} V_{DD} Rising: Open-Drain = V_{DD} > V_{TRIP} + V_{HYS} L = V_{DD} < V_{TRIP} + V_{HYS}
	MCP1316, MCP1318, MCP1319		0	Push-Pull	$V_{DD} Falling:$ $H = V_{DD} > V_{TRIP}$ $L = V_{DD} < V_{TRIP}$ $V_{DD} Rising:$ $H = V_{DD} > V_{TRIP} + V_{HYS}$ $L = V_{DD} < V_{TRIP} + V_{HYS}$
	MCP1317	RST	0	Push-Pull	 Reset Output (active-high) Goes active (High) if one of these conditions occurs: 1. If V_{DD} falls below the selected Reset voltage threshold. 2. If the MR pin is forced low. 3. If the WDI pin does not detect an edge transition within the minimum selected time out period. 4. During power-up. V_{DD} Falling: H = V_{DD} < V_{TRIP} L = V_{DD} > V_{TRIP} V_{DD} Rising: H = V_{DD} < V_{TRIP} + V_{HYS} L = V_{DD} > V_{TRIP} + V_{HYS}
2	All	V _{SS}	—	Р	The ground reference for the device.

Note 1: Open-Drain output with internal pull-up resistor.

TABLE 3-1	-1: PIN FUNCTION TABLE (CONTINUED)							
Pin No. SOT23-5	Device	Symbol	Pin Type	Buffer/ Driver Type	Function			
3	MCP1316, MCP1316M, MCP1317, MCP1320	MR	I	ST	 Manual Reset input for a Reset switch. This input allows a push button switch to be directly connected to the MCP131X/2X MR pin, which can then be used to force a system Reset. This input filters (ignores) noise pulses that occur on the MR pin. L = Switch is depressed (shorted to ground). This forces the RST/RST pins Active. H = Switch is open (internal pull-up resistor pulls signal high). State of the RST/RST pins determined by other system conditions. 			
	MCP1318, MCP1318M, MCP1319, MCP1319M, MCP1321, MCP1322	RST	0	Push-Pull	 Reset Output (active-high) Goes active (High) if one of these conditions occurs: 1. If V_{DD} falls below the selected Reset voltage threshold. 2. If the MR pin is forced low. 3. If the WDI pin does not detect an edge transition within the minimum selected time out period. 4. During power-up. V_{DD} Falling: H = V_{DD} < V_{TRIP} L = V_{DD} > V_{TRIP} V_{DD} Rising: H = V_{DD} < V_{TRIP} + V_{HYS} L = V_{DD} > V_{TRIP} + V_{HYS} 			
4	MCP1316, MCP1316M, MCP1317, MCP1318, MCP1318M, MCP1320, MCP1321	WDI	I	ST	Watchdog Timer Input The WDT period is specified at the time of device order. The Standard WDT period is 1.6s typical. An edge transition on the WDI pin resets the Watchdog Timer counter (no time out). A Falling Edge is required to start the WDT Timer.			
	MCP1319, MCP1319M, MCP1322	MR	I	ST	 Manual Reset input for a Reset switch. This input allows a push button switch to be directly connected to the MCP131X/2X MR pin, which can then be used to force a system Reset. This input filters (ignores) noise pulses that occur on the MR pin. L = Switch is depressed (shorted to ground). This forces the RST/RST pins Active. H = Switch is open (internal pull-up resistor pulls signal high). State of the RST/RST pins determined by other system conditions. 			
5	All	V _{DD}	—	Р	The positive supply for the device.			
	·	•	•					

EUNICTION TABLE (CONTINUE

Note 1: Open-Drain output with internal pull-up resistor.

3.1 Ground Terminal (V_{SS})

 $V_{\mbox{\scriptsize SS}}$ provides the negative reference for the analog input voltage. Typically, the circuit ground is used.

3.2 Supply Voltage (V_{DD})

V_{DD} can be used for power supply monitoring or a voltage level that requires monitoring.

3.3 Reset Output (RST and RST)

There are four types of Reset output pins. These are:

- 1. Open-Drain active-low Reset, External pull-up resistor required
- 2. Open-Drain active-low Reset, Internal pull-up resistor
- 3. Push-Pull active-low Reset
- 4. Push-Pull active-high Reset

Some devices have both an active-low and active-high Reset output.

3.3.1 ACTIVE-LOW (RST) - OPEN-DRAIN, EXTERNAL PULL-UP RESISTOR

The RST open-drain output remains low while V_{DD} is below the Reset voltage threshold (V_{TRIP}). Once the device voltage (V_{DD}) returns to a high level (V_{TRIP} + V_{HYS}), the device will remain in Reset for the Reset delay timer (T_{RST}). After that time expires, the RST pin will float, and an external pull-up resistor is required to bring the output to the high state.

3.3.2 ACTIVE-LOW (RST) - OPEN-DRAIN, INTERNAL PULL-UP RESISTOR

The RST open-drain output remains low while V_{DD} is below the Reset voltage threshold (V_{TRIP}). Once the device voltage (V_{DD}) returns to a high level (V_{TRIP} + V_{HYS}), the device will remain in Reset for the Reset delay timer (T_{RST}). After that time expires, the RST pin will be pulled high by an internal pull-up resistor (typically 4.7 k Ω).

3.3.3 ACTIVE-LOW (RST) - PUSH-PULL

The RST push-pull output remains low while V_{DD} is below the Reset voltage threshold (V_{TRIP}). Once the device voltage (V_{DD}) returns to a high level (V_{TRIP} + V_{HYS}), the device will remain in Reset for the Reset delay timer (T_{RST}). After that time expires, the RST pin will be driven to the high state.

3.3.4 ACTIVE-HIGH (RST) - PUSH-PULL

The RST push-pull output remains high while V_{DD} is below the Reset voltage threshold (V_{TRIP}). Once the device voltage (V_{DD}) returns to a high level (V_{TRIP} + V_{HYS}), the device will remain in Reset for the Reset delay timer (T_{RST}). After that time expires, the RST pin will be driven to the low state.

3.4 Manual Reset Input (MR)

The Manual Reset ($\overline{\text{MR}}$) input pin allows a push button switch to easily be connected to the system. When the push button is depressed, it forces a system Reset. This pin has circuitry that filters noise that may be present on the $\overline{\text{MR}}$ signal.

The $\overline{\text{MR}}$ pin is active-low and has an internal pull-up resistor.

3.5 Watchdog Input

In some systems, it is desirable to have an external Watchdog Timer to monitor the operation of the system. This is done by requiring the embedded controller to "pet" the Watchdog Timer within a predetermined time frame (T_{WD}). If the MCP131X/2X is not "petted" within this time frame, the MCP131X/2X will force the Reset pin(s) active.

The embedded controller "pets" the MCP131X/2X by forcing an edge transition on the WDI pin. The WDT Timer is activated by the first falling edge on the WDI pin.

The standard offering devices have a typical Watchdog Timer period (T_{WD}) of 1.6 s. Table 1-3 shows the available Watchdog Timer periods.

^{© 2005-2012} Microchip Technology Inc.

NOTES:

4.0 OPERATIONAL DESCRIPTION


For many of today's microcontroller applications, care must be taken to prevent low-power conditions that can cause many different system problems. The most common causes are brown-out conditions, where the system supply drops below the operating level momentarily. The second most common cause is when a slowly decaying power supply causes the microcontroller to begin executing instructions without sufficient voltage to sustain volatile memory (RAM), thus producing indeterminate results. Figure 4-1 shows a typical application circuit.


The MCP131X/2X family is voltage supervisor devices designed to keep a microcontroller in Reset until the system voltage has reached and stabilized at the proper level for reliable system operation. These devices also operate as protection from brown-out conditions when the system supply voltage drops below a safe operating level.


Some MCP131X/2X family members include a Watchdog Timer feature that after being enabled (by a falling edge on the WDI pin), monitors the WDI pin for falling or rising edges. If an edge transition is not detected within the expected time frame, the MCP131X/2X devices will force the Reset pin active. This is useful to ensure that the embedded system's Host Controller program is operating as expected.

Some MCP131X/2X family members include a Manual Reset feature that allows a push button switch to be directly connected to the MCP131X/2X devices (on the MR pin). This allows the system to easily be reset from the external control of the push button switch.

A superset block diagram is shown in Figure 4-2, with device specific block diagrams shown in Figure 4-3 through Figure 4-12.









Family Block Diagram.

4.0.1 DEVICE SPECIFIC BLOCK DIAGRAMS











FIGURE 4-5:

MCP1317 Block Diagram.






















4.1 Reset Voltage Trip Point (V_{TRIP}) Operation

The device's Reset voltage trip point (V_{TRIP}) is selected when the device is ordered. As the voltage on the device's V_{DD} pin is above or below this <u>selected</u> trip point, the output of the Reset pin (RST/RST) will be forced to either the inactive or active state.

For the voltage trip point, there is a minimum trip voltage ($V_{TRIPMIN}$) and a maximum trip voltage ($V_{TRIPMAX}$). The voltage that the device "actually" trips at will be referred to as V_{TRIP} . The trip voltage is specified for the falling of the device V_{DD} .

There is also a hysteresis (V_{HYS}) on the trip point. This is so that noise on the device voltage (V_{DD}) does not cause the Reset pin (RST/RST) to "jitter" (change between driving an active and inactive state).

The Reset pin (RST or \overline{RST}) will be forced active if any of the following occurs:

- The Manual Reset input (MR) goes low
- The Watchdog Timer times out
- V_{DD} goes below the threshold
- During device power-up

After the device exits the Reset condition, the delay circuitry will hold the RST and \overline{RST} pins active until the appropriate Reset delay time (t_{RST}) has elapsed.

	State of	RST Pin when:	State of F	RST ⁽³⁾ Pin when:	
Device	V _{DD} < V _{TRIP}	V _{DD} > V _{TRIP} + V _{HYS}	V _{DD} < V _{TRIP}	$V_{DD} > V_{TRIP} + V_{HYS}$	Output Driver
MCP1316	L	Н	_	_	Push-pull
MCP1316M	L	H ⁽²⁾	_	_	Open-drain ⁽²⁾
MCP1317	_	_	н	L	Push-pull
MCP1318	L	Н	Н	L	Push-pull
MCP1318M	L	H ⁽²⁾	Н	L	Open-drain ⁽²⁾
MCP1319	L	Н	Н	L	Push-pull
MCP1319M	L	H ⁽²⁾	Н	L	Open-drain ⁽²⁾
MCP1320	L	H ⁽¹⁾	_	_	Open-drain ⁽¹⁾
MCP1321	L	H (1)	Н	L	Open-drain ⁽¹⁾
MCP1322	L	H (1)	Н	L	Open-drain ⁽¹⁾

TABLE 4-1: RESET PIN STATES

Note 1: Requires External Pull-up resistor.

2: Has Internal Pull-up resistor.

3: The RST pin output is always push-pull.

4.1.1 POWER-UP/RISING V_{DD}

As the device V_{DD} rises, the device's Reset circuit will remain active until the voltage rises above the "actual" trip point (V_{TRIP}) plus the hysteresis (V_{HYS}).

Figure 4-13 shows a power-up sequence and the waveform of the RST and \overline{RST} pins.

As the device powers up, the voltage will start below the valid operating voltage of the device. At this voltage, the Reset output value is not valid. Once the voltage is above the minimum operating voltage (1V) and below the selected V_{TRIP} , the Reset output will be active.

Once the device voltage rises above the "actual" trip point (V_{TRIP}) plus the hysteresis (V_{HYS}), the Reset delay timer (t_{RST}) starts. When the Reset delay timer times out, the Reset output (RST/RST) is driven inactive.




FIGURE 4-13: Reset Pin Operation on a Power-up.

4.1.2 POWER-DOWN/BROWN-OUTS

As the device powers-down/brown-outs, the voltage (V_{DD}) falls from a voltage above the device's trip point (V_{TRIP}) . The device's "actual" trip point voltage (V_{TRIP}) will be between the minimum trip point $(V_{TRIPMIN})$ and the maximum trip point $(V_{TRIPMAX})$. Once the device voltage (V_{DD}) goes below this voltage, the Reset pin(s) will be forced to the active state. There is a hysteresis on this trip point. This is so that noise on the device voltage (V_{DD}) does not cause the Reset pin (RST/RST) to "jitter" (change between driving an active and inactive).

Figure 4-14 shows the waveform of the \overline{RST} pin as determined by the V_{DD} voltage, while Table 4-1 shows the state of the \overline{RST} pin.

4.1.2.1	Operation of \overline{RST} pin with Internal
	Pull-Up Resistor

Note:	Only the MCP1316M, MCP1318M and						
	MCP1319M devices have an open-drain						
	RST output pin with an internal pull-up						
	resistor.						

The internal pull-up resistor has a typical value of 4.7 k Ω . The internal pull-up eliminates the need for an external resistor.

To reduce the current consumption of the device, when the $\overrightarrow{\mathsf{RST}}$ pin is driving low, the resistor is disconnected.




FIGURE 4-14: RST Operation as Determined by the V_{TRIP} and V_{HYS} .

4.2 Reset Delay Timer (t_{RST})

The Reset delay timer ensures that the MCP131X/2X device will "hold" the embedded system in Reset until the system voltage has stabilized. There are several time-out options to better meet the requirements of different applications. These Reset delay timer time outs are shown in Table 4-2. The Standard offering time out is typically 200 ms.

The Reset delay timer (t_{RST}) starts after the device voltage rises above the "actual" trip point (V_{TRIP}) plus the hysteresis (V_{HYS}). When the Reset delay timer times out, the Reset output pin (RST/RST) is driven inactive.

Note:	While	the	Reset	delay	timer	(t _{RST}) is
	active,	add	litional	system	curre	nt is c	con-
	sumed						

TABLE 4-2:	RESET DELAY TIMER
	TIME OUTS ⁽¹⁾

t _{RST}					
Min	Тур	Мах	Units		
1.0	1.4	2.0	ms		
20	30	40	ms		
140	200	280	ms		
1120	1.6	2.24	sec		
↑ This is the minimum time that the Reset delay timer will "hold" the Reset pin active after V _{DD} rises		↑ This is the maximum time that the Reset delay timer will "hold" the Reset pin active after			
above V _{TRIP} + V _{HYS}		V _{DD} rises above V _{TRIP} + V _{HYS}			

Note 1: Shaded rows are custom ordered time outs.

Figure 4-15 illustrates when the Reset delay timer (t_{RST}) is active or inactive.




FIGURE 4-15: Reset Power-up Timer Waveform.

4.2.1 EFFECT OF TEMPERATURE ON RESET POWER-UP TIMER (T_{RPU})

The Reset delay timer time out period (t_{RST}) determines how long the device remains in the Reset condition. This time out is affected by both the device V_{DD} and temperature. Typical responses for different V_{DD} values and temperatures are shown in Figures 2-33, 2-32 and 2-31.

4.3 Negative Going V_{DD} Transients

The minimum pulse width (time) required to cause a Reset may be an important criteria in the implementation of a Power-on Reset (POR) circuit. This time is referred to as transient duration. The MCP131X/2X devices are designed to reject a level of negative-going transients (glitches) on the power supply line.

Transient duration is the amount of time needed for these supervisory devices to respond to a drop in V_{DD}. The transient duration time (t_{TRAN}) is dependant on the magnitude of V_{TRIP} – V_{DD} (overdrive). Any combination of duration and overdrive that lies under the duration/overdrive curve will not generate a Reset signal. Generally speaking, the transient duration time decreases with and increases in the V_{TRIP} – V_{DD} voltage. Combinations of duration and overdrive curve are detected as a brown-out or power-down condition.

Figure 4-16 shows a typical transient duration vs. Reset comparator overdrive, for which the MCP131X/2X will not generate a Reset pulse. It shows that the farther below the trip point the transient pulse goes, the duration of the pulse required to cause a Reset gets shorter. Figure 4-16 shows the transient response characteristics for the MCP131X/2X.

Transient immunity can be improved by adding a bypass capacitor (typically 0.1 $\mu F)$ as close as possible to the V_{DD} pin of the MCP131X/2X device.




FIGURE 4-16: Example of Typical Transient Duration Waveform.

4.4 Manual Reset Input

The Manual Reset input pin ($\overline{\text{MR}}$) allows the Reset pins (RST/RST) to be manually forced to their active states. The MR pin has circuitry to filter noise pulses that may be present on the pin. Figure 4-17 shows a block diagram for using the MCP131X/2X with a push-button switch. To minimize the required external components, the MR input has an internal pull-up resistor.

A mechanical push button or active logic signal can drive the $\overline{\text{MR}}$ input.

Once $\overline{\text{MR}}$ has been low for a time, t_{MRD} (the Manual Reset delay time), the Reset output pins are forced active. The Reset output pins will remain in their active states for the Reset delay timer time out period (t_{RST}).

Figure 4-18 shows a waveform for the Manual Reset switch input and the Reset pins output.





FIGURE 4-17: Push Button Reset and Watchdog Timer.



4.4.1 NOISE FILTER

The noise filter filters out noise spikes (glitches) on the Manual Reset pin (\overline{MR}). Noise spikes less than 100 ns (typical) are filtered.

4.5 Watchdog Timer

The purpose of the Watchdog Timer (WDT) is to increase system reliability. The Watchdog Timer feature can be used to detect when the Host Controller's program flow is not as expected. The Watchdog Timer monitors for activity on the Watchdog Input pin (WDI). The WDI pin is expected to be strobed within a given time frame. When this time frame is exceeded, without an edge transition on the WDI pin, the Reset pin is driven active to reset the system. This stops the Host Controller from continuing its erratic behavior ("run-away" code execution).

The Watchdog Timer is external to the main portion of the control system and monitors the operation of the system. This feature is enabled by a falling edge on the WDI pin (after device POR). Monitoring is then done by requiring the embedded controller to force an edge transition (falling or rising) on the WDI pin ("pet the Watchdog") within a predetermined time frame (T_{WD}). If the MCP131X/2X does not detect an edge on the WDI pin within the expected time frame, the MCP131X/2X device will force the Reset pin active.

The Watchdog Timer is in the disabled state when:

- The Device Powers up
- A POR event occurred
- A WDT event occurred
- A Manual Reset (MR) event occurred

When the Watchdog Timer is in the disabled state, the WDI pin has an internal smart pull-up resistor enabled. This pull-up resistor has a typical value of 52 k Ω . This pull-up resistor holds the WDI signal in the high state, until it is forced to another state.

After the embedded controller has initialized, if the Watchdog Timer feature is to be used, then the embedded controller can force the WDI pin low (V_{IL}). This also enables the Watchdog Timer feature and disables the WDI pull-up resistor. Disabling the pull-up resistor reduces the device's current consumption. The pull-up resistor will remain disconnected until the device has a power-on, a Reset event occurs, or after the WDT time out.

Once the Watchdog Timer has been enabled, the Host Controller must force an edge transition (falling or rising) on the WDI pin before the minimum Watchdog Timer time out to ensure that the Watchdog Timer does not force the Reset pins (RST/RST) to the active state.


If an edge transition does not occur before the maximum time out occurs, then the MCP131X/2X will force the Reset pins to their active state.

The MCP131X/2X supports four time outs. The standard offering devices have a typical Watchdog Timer period (T_{WDT}) of 1.6 s. Table 4-3 shows the available Watchdog Timer periods. The t_{WDT} time out is a function of the device voltage and temperature. Figure 4-19 shows a block diagram for using the MCP131X/2X with a $\text{PIC}^{\textcircled{R}}$ microcontroller (MCU) and the Watchdog input.

TABLE 4-3:	WATCHDOG TIMER
	PERIODS ⁽¹⁾

	Units		
Min	Тур	Max	Units
4.3	6.3	9.3	ms
71	102	153	ms
1.12	1.6	2.4	sec
17.9	25.6	38.4	sec
↑ If the time between WDI edges is less than this, it ensures that the MCP131X/2X never forces a reset		↑ If the time between WDI edges is greater than this, it ensures that the MCP131X/2X always forces a reset	

Note 1: Shaded rows are custom ordered Watchdog Timer Periods (t_{WDT}) time outs. For information on ordering devices with these t_{WDT} time outs, please contact your local Microchip sales office. Minimum purchase volumes are required.





The software routine that strobes WDI is critical. The code must be in a section of software that is executed frequently enough so the time between edge transitions is less than the Watchdog time out period. One common technique controls the Host Controllers I/O line from two sections of the program. The software might set the I/O line high while operating in the Foreground mode and set it low while in the Background or Interrupt modes. If both modes do not execute correctly, the Watchdog Timer issues reset pulses.

5.0 APPLICATION INFORMATION

This section shows application related information that may be useful for your particular design requirements.

5.1 Supply Monitor Noise Sensitivity

The MCP131X/2X devices are optimized for fast response to negative-going changes in V_{DD}. Systems with an inordinate amount of electrical noise on V_{DD} (such as systems using relays) may require a 0.01 μ F or 0.1 μ F bypass capacitor to reduce detection sensitivity. This capacitor should be installed as close to the MCP131X/2X as possible to keep the capacitor lead length short.




FIGURE 5-1: Typical Application Circuit with Bypass Capacitor.

5.2 Conventional Voltage Monitoring

Figure 5-2 and Figure 5-3 show the MCP131X/2X in conventional voltage monitoring applications.




FIGURE 5-2:

Battery Voltage Monitor.





FIGURE 5-3:

Power Good Monitor.

5.3 Using in PIC[®] Microcontroller, ICSP™ Applications

Note: This operation can only be done using the device with the Open-Drain RST pin (MCP1320, MCP1321, and MCP1322). Devices that have the internal pull-up resistor are not recommended due to the current path of the internal pull-up resistor.

Figure 5-4 shows the typical application circuit for using the MCP132X for a voltage supervisory function when the PIC[®] microcontroller will be programmed via the In-Circuit Serial ProgrammingTM (ICSPTM) feature. Additional information is available in TB087, *"Using Voltage Supervisors with PIC[®] Microcontroller Systems which Implement In-Circuit Serial ProgrammingTM*" (DS91087).






FIGURE 5-4: Typical Application Circuit for $PIC^{\mathbb{R}}$ Microcontroller with the ICSPTM Feature.

5.4 Modifying The Trip Point, V_{TRIP}

Although the MCP131X/2X device has a fixed voltage trip point (V_{TRIP}), it is sometimes necessary to make custom adjustments. This can be accomplished by connecting an external resistor divider to the MCP131X/2X V_{DD} pin. This causes the V_{SOURCE} voltage to be at a higher voltage than when the MCP131X/2X input equals its V_{TRIP} voltage (Figure 5-5).

To maintain detector accuracy, the bleeder current through the divider should be significantly higher than the 10 μ A maximum operating current required by the MCP131X/2X. A reasonable value for this bleeder current is 1 mA (100 times the 10 μ A required by the MCP131X/2X). For example, if V_{TRIP} = 2V and the desired trip point is 2.5V, the value of R₁ + R₂ is 2.5 kΩ (2.5V/1 mA). The value of R₁ + R₂ can be rounded to the nearest standard value and plugged into the equation of Figure 5-5 to calculate values for R₁ and R₂. 1% tolerance resistors are recommended.





FIGURE 5-5: Modify Trip-Point using External Resistor Divider.

5.5 MOSFET Low-Drive Protection

Low operating power and small physical size make the MCP131X/2X series ideal for many voltage detector applications. Figure 5-6 shows a low-voltage gate drive protection circuit that prevents overheating of the logic-level MOSFET due to insufficient gate voltage. When the input signal is below the threshold of the MCP131X/2X, its output grounds the gate of the MOSFET.



5.6 Low-Power Applications

In some low-power applications, the longer that the microcontroller (such as a $PIC^{\textcircled{R}}MCU$) can be in the "Sleep mode", the lower the average system current consumption will be.

The WDT feature can be used to "wake-up" the PIC MCU at a regular interval to service the required tasks before returning to sleep. This "wake-up" occurs after the PIC MCU detects a MCLR reset during Sleep mode (for midrange family; POR = '1', BOR = '1', TO = '1', and PD = '1').

5.7 Controllers and Processors With Bidirectional I/O Pins

Some microcontrollers have bidirectional Reset pins. Depending on the current drive capability of the controller pin, an indeterminate logic level may result if there is a logic conflict. This can be avoided by adding a 4.7 k Ω resistor in series with the output of the MCP131X/2X (Figure 5-7). If there are other components in the system that require a Reset signal, they should be buffered so as not to load the Reset line. If the other components are required to follow the Reset I/O of the microcontroller, the buffer should be connected as shown with the solid line.




FIGURE 5-7: Interfacing the MCP131X/2X Push-Pull Outputs to a Bidirectional Reset I/O.

5.8 RESET Signal Integrity During Power-Down

The MCP131X/2X Reset output is valid to $V_{DD} = 1.0V$. Below this 1.0V, the output becomes an "open circuit" and does not sink or source current. This means CMOS logic inputs to the microcontroller will be floating at an undetermined voltage. Most digital systems are completely shut down well above this voltage. However, in situations where the Reset signal must be maintained valid to $V_{DD} = 0V$, external circuitry is required.

For devices where the Reset signal is active-low, a pulldown resistor must be connected from the MCP131X/2X Reset pin(s) to ground to discharge stray capacitances and hold the output low (Figure 5-8).

Similarly, for devices where the Reset signal is activehigh, a pull-up resistor to V_{DD} is required to ensure a valid high Reset signal for V_{DD} below 1.0V.

This resistor value, though not critical, should be chosen such that it does not appreciably load the Reset pin(s) under normal operation (100 k Ω will be suitable for most applications).




FIGURE 5-8: Ensuring a Valid Active-low Reset Pin Output State as V_{DD} Approaches 0V.

6.0 STANDARD DEVICE OFFERINGS

Table 6-1 shows the standard devices that are available and their respective configuration. The configuration includes the:

- Voltage Trip Point (V_{TRIP})
- Reset Time Out (t_{RST})
- Watchdog Time Out (t_{WDT})

 Table 6-1 also shows the order number for that given device configuration.

6.1 Custom Configurations

Table 6-2 shows the codes that specify the desired Reset time out (t_{RST}) and Watchdog Timer time out (t_{WDT}) for custom devices.

The voltage trip point (V_{TRIP}) is specified by the two digits of the desired typical trip point voltage. As an example, if the desired V_{TRIP} selection has a typical V_{TRIP} of 2.7V, the code is 27.

Device	Reset	Reset Time	Out (ms)	Watchdog Ti	me Out (s)	
Device	Threshold (V)	Minimum Typical		Minimum	Typical	Order Number
MCP1316	2.90	140	200	1.12	1.6	MCP1316T-29LE/OT
MCP1316	4.60	140	200	1.12	1.6	MCP1316T-46LE/OT
MCP1316M	2.90	140	200	1.12	1.6	MCP1316MT-29LE/OT
MCP1316M	4.60	140	200	1.12	1.6	MCP1316MT-46LE/OT
MCP1317	2.90	140	200	1.12	1.6	MCP1317T-29LE/OT
MCP1317	4.60	140	200	1.12	1.6	MCP1317T-46LE/OT
MCP1318	2.90	140	200	1.12	1.6	MCP1318T-29LE/OT
MCP1318	4.60	140	200	1.12	1.6	MCP1318T-46LE/OT
MCP1318M	2.90	140	200	1.12	1.6	MCP1318MT-29LE/OT
MCP1318M	4.60	140	200	1.12	1.6	MCP1318MT-46LE/OT
MCP1319	2.90	140	200		—	MCP1319T-29LE/OT
MCP1319	4.60	140	200		—	MCP1319T-46LE/OT
MCP1319M	2.90	140	200	_	—	MCP1319MT-29LE/OT
MCP1319M	4.60	140	200		—	MCP1319MT-46LE/OT
MCP1320	2.90	140	200	1.12	1.6	MCP1320T-29LE/OT
MCP1320	4.60	140	200	1.12	1.6	MCP1320T-46LE/OT
MCP1321	2.90	140	200	1.12	1.6	MCP1321T-29LE/OT
MCP1321	4.60	140	200	1.12	1.6	MCP1321T-46LE/OT
MCP1322	2.90	140	200	_	_	MCP1322T-29LE/OT
MCP1322	4.60	140	200	_	—	MCP1322T-46LE/OT

TABLE 6-1: STANDARD VERSIONS

TABLE 6-2: DELAY TIME OUT ORDERING CODES

	Typical Delay	/ Time (ms)			Typical Delay Time (ms)		
Code	Reset	WDT	Comment	Code	Reset	WDT	Comment
А	1.6	6.3	Note 1	J	200.0	6.3	Note 1
В	1.6	102.0	Note 1	К	200.0	102.0	Note 1
С	1.6	1600.0	Note 1	L	200.0	1600.0	Delay timings for standard device offerings
D	1.6	25600.0	Note 1	М	200.0	25600.0	Note 1
E	30.0	6.3	Note 1	Ν	1600.0	6.3	Note 1
F	30.0	102.0	Note 1	Р	1600.0	102.0	Note 1
G	30.0	1600.0	Note 1	Q	1600.0	1600.0	Note 1
Н	30.0	25600.0	Note 1	R	1600.0	25600.0	Note 1

Note 1: This delay timing combination is not the standard offering. For information on ordering devices with these delay times, contact your local Microchip sales office. Minimum purchase volumes are required.

7.0 DEVELOPMENT TOOLS

7.1 Evaluation/Demonstration Boards

The SOT-23-5/6 Evaluation Board (VSUPEV2) can be used to evaluate the characteristics of the MCP131X/2X devices.

This blank PCB has footprints for:

- Pull-up Resistor
- Pull-down Resistor
- Loading Capacitor
- In-line Resistor

There is also a power supply filtering capacitor.

For evaluating the MCP131X/2X devices, the selected device should be installed into the Option A footprint.





FIGURE 1: SOT-23-5/6 Voltage Supervisor Evaluation Board (VSUPEV2).


This board may be purchased directly from the Microchip web site at www.microchip.com.

8.0 PACKAGING INFORMATION

8.1 Package Marking Information




Part Number	SOT-23
MCP1316T-29LE/OT	QANN
MCP1316MT-29LE/OT	QBNN
MCP1317T-29LE/OT	QCNN
MCP1318T-29LE/OT	QDNN
MCP1318MT-29LE/OT	QENN
MCP1319T-29LE/OT	QFNN
MCP1319MT-29LE/OT	QGNN
MCP1320T-29LE/OT	QHNN
MCP1321T-29LE/OT	QJNN
MCP1322T-29LE/OT	QKNN
MCP1316T-46LE/OT	QLNN
MCP1316MT-46LE/OT	QMNN
MCP1317T-46LE/OT	QPNN
MCP1318T-46LE/OT	QQNN
MCP1318MT-46LE/OT	QRNN
MCP1319T-46LE/OT	QSNN
MCP1319MT-46LE/OT	QTNN
MCP1320T-46LE/OT	QUNN
MCP1321T-46LE/OT	QVNN
MCP1322T-46LE/OT	QWNN





Legend	: XXX Y YY WW NNN @3 *	Customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.
Note:	be carrie	nt the full Microchip part number cannot be marked on one line, it will d over to the next line, thus limiting the number of available s for customer-specific information.


5-Lead Plastic Small Outline Transistor (OT) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging









	Units		MILLIMETERS				
Dimensi	ion Limits	MIN	NOM	MAX			
Number of Pins	Ν		5				
Lead Pitch	е		0.95 BSC				
Outside Lead Pitch	e1		1.90 BSC				
Overall Height	Α	0.90	-	1.45			
Molded Package Thickness	A2	0.89	-	1.30			
Standoff	A1	0.00	-	0.15			
Overall Width	E	2.20	-	3.20			
Molded Package Width	E1	1.30	-	1.80			
Overall Length	D	2.70	-	3.10			
Foot Length	L	0.10	-	0.60			
Footprint	L1	0.35	-	0.80			
Foot Angle	¢	0°	-	30°			
Lead Thickness	С	0.08	-	0.26			
Lead Width	b	0.20	-	0.51			

Notes:


- 1. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.127 mm per side.
- 2. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-091B

5-Lead Plastic Small Outline Transistor (OT) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Ν	MILLIMETERS			
Dimension	Dimension Limits			MAX	
Contact Pitch	E		0.95 BSC		
Contact Pad Spacing	С		2.80		
Contact Pad Width (X5)	X		0.6		
Contact Pad Length (X5)	Y	1.1			
Distance Between Pads	G	1.70			
Distance Between Pads	GX	0.35			
Overall Width	Z	3.9			

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2091A

8.2 Product Tape and Reel Specifications





FIGURE 8-1: EMBOSSED CARRIER DIMENSIONS (8 MM TAPE ONLY)

TABLE 8-1: CARRIER TAPE/CAVITY DIMENSIONS

Case	Packag	e	Car Dimer	rier nsions	D	Cavity Dimensions		Output Quantity	Reel Diameter in
Outline	Outline Type		W mm	P mm	A0 mm	B0 mm	K0 mm	Units	mm
ОТ	SOT-23	3L	8	4	3.23	3.17	1.37	3000	180

FIGURE 8-2: 5-LEAD SOT-23 DEVICE TAPE AND REEL SPECIFICATIONS



APPENDIX A: REVISION HISTORY

Revision C (February 2012)

The following is the list of modifications:

- 1. Updated package temperature in the **Temperature Characteristics** table.
- 2. Corrected text in Section 4.0, Operational Description.
- Updated package specification in Section 8.0, Packaging Information to show all drawings available.
- 4. Other minor typographical corrections.

Revision B (October 2007)

The following is the list of modifications:

1. Clarified that devices with a Voltage Trip Point ≤ 2.4 V are tested from -40° C to $+85^{\circ}$ C. Devices with a Voltage Trip Point ≥ 2.5 V are tested from -40° C to $+125^{\circ}$ C.

Revision A (November 2005)

• Original Release of this Document.

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO.	<u> xx</u>	<u>×</u>	<u>× /</u>	<u>xx</u>	Exa	mples:	
Device Tape	/Reel V _{TRIP}	Time Out T Options	emperature Range	Package	a) b) c) d)	MCP1316T-29LE/OT: MCP1316T-46LE/OT: MCP1316MT-29LE/OT: MCP1316MT-29LE/OT:	5-Lead SOT-23-5 5-Lead SOT-23-5 5-Lead SOT-23-5 5-Lead SOT-23-5
Device:	MCP1316T:	MicroPower Volta (Tape and Reel)	age Detector		a)	MCP1317T-29LE/OT:	5-Lead SOT-23-5
	MCP1316MT:	MicroPower Volta (Tape and Reel)	age Detector		b) a)	MCP1317T-46LE/OT: MCP1318T-29LE/OT:	5-Lead SOT-23-5 5-Lead SOT-23-5
	MCP1317T:	MicroPower Volta (Tape and Reel)	age Detector		b) c) d)	MCP1318MT-29LE/OT: MCP1318T-46LE/OT: MCP1318MT-46LE/OT:	5-Lead SOT-23-5
	MCP1318T:	MicroPower Volta (Tape and Reel)	age Detector		a)	MCP1319T-29LE/OT:	5-Lead SOT-23-5
	MCP1318MT:	MicroPower Volta (Tape and Reel)	age Detector		b) c)	MCP1318MT-29LE/OT: MCP1319T-46LE/OT:	5-Lead SOT-23-5
	MCP1319T:	MicroPower Volta (Tape and Reel)	age Detector		d) a)	MCP1318MT-46LE/OT: MCP1320T-29LE/OT:	5-Lead SOT-23-5 5-Lead SOT-23-5
	MCP1319MT:	MicroPower Volta (Tape and Reel)	age Detector		b)	MCP1320T-46LE/OT:	5-Lead SOT-23-5
	MCP1320T:	MicroPower Volta (Tape and Reel)	age Detector		a) b)	MCP1321T-29LE/OT: MCP1321T-46LE/OT:	5-Lead SOT-23-5 5-Lead SOT-23-5
	MCP1321T:	MicroPower Volta (Tape and Reel)	age Detector		a) b)	MCP1322T-29LE/OT: MCP1322T-46LE/OT:	5-Lead SOT-23-5 5-Lead SOT-23-5
	MCP1322T:	MicroPower Volta (Tape and Reel)					
V _{TRIP} Options: (Note 1)	29 = 2.90V 46 = 4.60V						
Time Out Options: (Note 1)		= 200 ms (typ.), = 1.6 s (typ.)					
Temperature Range	$E = -40^{\circ}C$	to +85°C for trip points 2.0' to +125°C ip point \geq 2.5V)	V to 2.4V)				
Package:	OT = SOT-2	23, 5-lead					
conta	om ordered voltage ct your local Microo num purchase volu	chip sales office for	or additional in				

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

Trademarks

The Microchip name and logo, the Microchip logo, dsPIC, KEELOQ, KEELOQ logo, MPLAB, PIC, PICmicro, PICSTART, PIC³² logo, rfPIC and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.


FilterLab, Hampshire, HI-TECH C, Linear Active Thermistor, MXDEV, MXLAB, SEEVAL and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, HI-TIDE, In-Circuit Serial Programming, ICSP, Mindi, MiWi, MPASM, MPLAB Certified logo, MPLIB, MPLINK, mTouch, Omniscient Code Generation, PICC, PICC-18, PICDEM, PICDEM.net, PICkit, PICtail, REAL ICE, rfLAB, Select Mode, Total Endurance, TSHARC, UniWinDriver, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2005-2012, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.



ISBN: 978-1-62076-078-9

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEEL0Q® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and mulfacture of development systems is ISO 9001:2000 certified.



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Cleveland Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

Toronto Mississauga, Ontario, Canada Tel: 905-673-0699 Fax: 905-673-6509

ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon Hong Kong Tel: 852-2401-1200 Fax: 852-2401-3431 Australia - Sydney

Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

China - Chengdu Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Hangzhou Tel: 86-571-2819-3187 Fax: 86-571-2819-3189

China - Hong Kong SAR Tel: 852-2401-1200 Fax: 852-2401-3431

China - Nanjing Tel: 86-25-8473-2460

Fax: 86-25-8473-2470 China - Qingdao Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen Tel: 86-755-8203-2660 Fax: 86-755-8203-1760

China - Wuhan Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

China - Xiamen Tel: 86-592-2388138 Fax: 86-592-2388130

China - Zhuhai Tel: 86-756-3210040 Fax: 86-756-3210049

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

Japan - Osaka Tel: 81-66-152-7160 Fax: 81-66-152-9310

Japan - Yokohama Tel: 81-45-471- 6166 Fax: 81-45-471-6122

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-536-4818 Fax: 886-7-330-9305

Taiwan - Taipei Tel: 886-2-2500-6610 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

UK - Wokingham Tel: 44-118-921-5869 Fax: 44-118-921-5820