

Sonos Sounder Beacon - Fire

Electronic sounder beacon certified to EN54.

With the TimeSaver base, connections are made to the base during the initial wiring phase which results in faster and more reliable installation. The sounder head 'twists and clicks' into the base on commissioning, avoiding the wiring and connection problems associated with traditional sounders.

With a choice of 32 tones including all the major international standards, the Sonos Sounder Beacon has universal acceptance.


Features

- Low current LED beacon
- Simple 'First Fix' installation
- Weatherproof to IP65 (deep base units)
- Choice of lens colours
- Tone and volume can be preset or adjusted off-base - 20dB


Lens Colour Options



Deep Base



Shallow Base



Specifications

Combined Part No.	Base Part No.	Head Part No.	Audibility at 1m	Tones	Voltage	Sounder Current
PSC-0047	PSO-0001 Red shallow base	PSC-0045 Red lens	Up to 106dB (A)	32	17-60V DC	9-50mA
PSC-0050	PSO-0001 Red shallow base	PSC-0054 Amber lens	Up to 106dB (A)	32	17-60V DC	9-50mA
PSC-0042	PSO-0003 Red deep base	PSC-0045 Red lens	Up to 106dB (A)	32	17-60V DC	9-50mA
PSC-0049	PSO-0003 Red deep base	PSC-0054 Amber lens	Up to 106dB (A)	32	17-60V DC	9-50mA
PSC-0059	PSO-0007 White deep base	PSC-0051 Clear lens, Red LED	Up to 106dB (A)	32	17-60V DC	9-50mA

Other colours/combinations are available on request

IP Rating: IP65 (deep base) IP21 (shallow base) **Operating Temp:** -25°C to +70°C **Construction:** Flame Retardant Polycarbonate

Cable Entries: Deep Base: 2 x 20mm cable glands **Weight:** 0.22kg (shallow base) 0.25kg (deep base)

Compliance: EN54 3 Type A (shallow base) EN54 3 Type B (deep base)