



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A		
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	PROD COMPLIANCE ENGINEER		
<b>Company Unique ID</b>	-	<b>Response Date</b>	2013-05-28	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	(86)21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5530843-3	<b>Amount</b>	8399.86252578	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>REACH-0209</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	9-646054-8				18.0	73.47460321	mg	
Material	2	Tin Plate				18.0	0.215	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	18.0	2.1478E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	18.0	0.21479	mg	
Material	2	Phos Bronze				18.0	72.5	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	18.0	68.64554	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	18.0	0.0145	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	18.0	0.00725	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	18.0	3.2625	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	18.0	0.010875	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	18.0	0.00725	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	18.0	0.0725	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	18.0	7.25E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	18.0	0.2175	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	18.0	0.0725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	18.0	0.0725	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	18.0	0.00725	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	18.0	0.03625	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	18.0	0.0725	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	18.0	3.625E-4	mg	
Material	2	Nickel Plate				18.0	0.751	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	18.0	0.001502	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	18.0	7.51E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	18.0	0.74875	mg	
Material	2	Gold Plate				18.0	0.00860321	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	18.0	0.0085774	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	18.0	2.580963E-5	mg	
Sub-Item	1	532082-3				1.0	5754.6	mg	
Material	2	PBT-GF30FR(17)				1.0	5754.6	mg	

Substance	3	Carbonic dichloride, polymer with 4,4'-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	1726.38	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	1899.018	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	57.546	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	57.546	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	287.73	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1726.38	mg	
Sub-Item	1	9-646054-1				18.0	73.484426	mg	
Material	2	Tin Plate				18.0	0.215326	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	18.0	2.1511E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	18.0	0.21511	mg	
Material	2	Phos Bronze				18.0	72.5	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	18.0	68.64554	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	18.0	0.0145	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	18.0	0.00725	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	18.0	3.2625	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	18.0	0.010875	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	18.0	0.00725	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	18.0	0.0725	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	18.0	7.25E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	18.0	0.2175	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	18.0	0.0725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	18.0	0.0725	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	18.0	0.00725	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	18.0	0.03625	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	18.0	0.0725	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	18.0	3.625E-4	mg	
Material	2	Nickel Plate				18.0	0.7519	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	18.0	0.0015038	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	18.0	7.519E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	18.0	0.74964	mg	
Material	2	Gold Plate				18.0	0.0172	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	18.0	0.0171484	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	18.0	5.16E-5	mg	