



short-stroke cylinder

AEVC-16-25-I-P

Part number: 188101

★ Core product range

FESTO



Data sheet

| Feature | Value |
|--|---|
| Stroke | 25 mm |
| Piston diameter | 16 mm |
| Spring return force, retracted | 5 N |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Mode of operation | single-acting pushing action |
| Design structure | Piston Piston rod |
| Position detection | No |
| Operating pressure | 1.5 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Ambient temperature | -20 ... 80 °C |
| Theoretical force at 6 bar, advance stroke | 105 N |
| Moving mass | 19 g |
| Product weight | 150 g |
| Mounting type | Optional with through hole with accessories |
| Pneumatic connection | M5 |
| Materials note | Free of copper and PTFE |
| Material cover | Wrought Aluminium alloy Anodised |
| Material seals | NBR TPE-U(PU) |
| Material housing | Wrought Aluminium alloy Anodised |
| Material piston rod | High alloy steel |