Plastic Darlington Complementary Silicon Power Transistors

These devices are designed for general-purpose amplifier and low-speed switching applications.

Features

- High DC Current Gain $h_{FE} = 2000$ (Typ) @ I_C = 2.0 Adc
- Monolithic Construction with Built-in Base-Emitter Resistors to Limit Leakage – Multiplication
- Choice of Packages MJE700 and MJE800 Series
- These Devices are Pb-Free and are RoHS Compliant*

MAXIMUM RATINGS

| Rating | Symbol | Value | Unit |
|--|-----------------------------------|-------------|------------|
| Collector-Emitter Voltage MJE700G, MJE800G MJE702G, MJE703G, MJE802G, MJE803G | V _{CEO} | 60 80 | Vdc |
| Collector–Base Voltage MJE700G, MJE800G MJE702G, MJE703G, MJE802G, MJE803G | V _{CB} | 60 80 | Vdc |
| Emitter-Base Voltage | V _{EB} | 5.0 | Vdc |
| Collector Current | I _C | 4.0 | Adc |
| Base Current | I _B | 0.1 | Adc |
| Total Power Dissipation @ T _C = 25°C Derate above 25°C | P _D | 40 0.32 | W mW/°C |
| Operating and Storage Junction Temperature Range | T _J , T _{stg} | -55 to +150 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS


| Characteristic | Symbol | Max | Unit |
|---|-----------------|------|------|
| Thermal Resistance, Junction-to-Case | $R_{\theta JC}$ | 3.12 | °C/W |
| Thermal Resistance, Junction-to-Ambient | $R_{\theta JA}$ | 83.3 | °C/W |



ON Semiconductor®


http://onsemi.com

4.0 AMPERE DARLINGTON POWER TRANSISTORS COMPLEMENTARY SILICON 40 WATT





MARKING DIAGRAM



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

^{*}For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

| Characteristic | Symbol | Min | Max | Unit |
|---|-----------------------|-------------------|-------------------|------|
| OFF CHARACTERISTICS | - | | • | |
| Collector–Emitter Breakdown Voltage (Note 1) (I _C = 50 mAdc, I _B = 0) MJE700G, MJE800G MJE702G, MJE703G, MJE802G, MJE803G | V _(BR) CEO | 60 80 | _ _ | Vdc |
| Collector Cutoff Current (V _{CE} = 60 Vdc, I _B = 0) MJE700G, MJE800G (V _{CE} = 80 Vdc, I _B = 0) MJE702G, MJE703G, MJE802G, MJE803G | I _{CEO} | - | 100 100 | μAdc |
| Collector Cutoff Current $(V_{CB} = Rated BV_{CEO}, I_E = 0)$ $(V_{CB} = Rated BV_{CEO}, I_E = 0, T_C = 100^{\circ}C)$ | Ісво | _ _ _ | 100 500 | μAdc |
| Emitter Cutoff Current (V _{BE} = 5.0 Vdc, I _C = 0) | I _{EBO} | - | 2.0 | mAdc |
| ON CHARACTERISTICS | | | | • |
| DC Current Gain (Note 1) $ \begin{array}{l} (I_C = 1.5 \; \text{Adc, V}_{CE} = 3.0 \; \text{Vdc}) \\ \text{MJE700G, MJE702G, MJE800G, MJE802G} \\ (I_C = 2.0 \; \text{Adc, V}_{CE} = 3.0 \; \text{Vdc}) \\ \text{MJE703G, MJE803G} \\ (I_C = 4.0 \; \text{Adc, V}_{CE} = 3.0 \; \text{Vdc}) \\ \text{All devices} \end{array} $ | h _{FE} | 750 750 100 | - - - | - |
| Collector–Emitter Saturation Voltage (Note 1) ($I_C = 1.5 \text{ Adc}$, $I_B = 30 \text{ mAdc}$) MJE700G, MJE702G, MJE800G, MJE802G ($I_C = 2.0 \text{ Adc}$, $I_B = 40 \text{ mAdc}$) MJE703G, MJE803G ($I_C = 4.0 \text{ Adc}$, $I_B = 40 \text{ mAdc}$) All devices | V _{CE(sat)} | - - - | 2.5 2.8 3.0 | Vdc |
| | V _{BE(on)} | - - - | 2.5 2.5 3.0 | Vdc |
| DYNAMIC CHARACTERISTICS | | | 1 | 1 |
| Small–Signal Current Gain (I _C = 1.5 Adc, V _{CE} = 3.0 Vdc, f = 1.0 MHz) | h _{fe} | 1.0 | _ | - |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Pulse Test: Pulse Width \leq 300 µs, Duty Cycle \leq 2.0%.




Figure 1. Power Derating




Figure 2. Switching Times Test Circuit

Figure 3. Switching Times






Figure 4. Thermal Response (MJE700, 800 Series)

ACTIVE-REGION SAFE-OPERATING AREA



There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.



The data of Figures 5 and 6 are based on $T_{J(pk)}=150^{\circ}C$; T_C is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(pk)}$ < $150^{\circ}C$. $T_{J(pk)}$ may be calculated from the data in Figure 4. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.




Figure 7. DC Current Gain




Figure 8. Collector Saturation Region





Figure 9. "On" Voltages

ORDERING INFORMATION

| Device | Package | Shipping |
|---------|---------------------|-----------------|
| MJE700G | TO-225 (Pb-Free) | 50 Units / Bulk |
| MJE702G | TO-225 (Pb-Free) | 50 Units / Bulk |
| MJE703G | TO-225 (Pb-Free) | 50 Units / Bulk |
| MJE800G | TO-225 (Pb-Free) | 50 Units / Bulk |
| MJE802G | TO-225 (Pb-Free) | 50 Units / Bulk |
| MJE803G | TO-225 (Pb-Free) | 50 Units / Bulk |


MECHANICAL CASE OUTLINE




TO-225 CASE 77-09 **ISSUE AD**

DATE 25 MAR 2015

SCALE 1:1






SIDE VIEW

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: MILLIMETERS. 3. NUMBER AND SHAPE OF LUGS OPTIONAL.

| | MILLIMETERS | | | |
|-----|-------------|-------|--|--|
| DIM | MIN | MAX | | |
| Α | 2.40 | 3.00 | | |
| A1 | 1.00 | 1.50 | | |
| b | 0.60 | 0.90 | | |
| b2 | 0.51 | 0.88 | | |
| С | 0.39 | 0.63 | | |
| D | 10.60 | 11.10 | | |
| E | 7.40 | 7.80 | | |
| е | 2.04 2.54 | | | |
| L | 14.50 | 16.63 | | |
| L1 | 1.27 | 2.54 | | |
| P | 2.90 3.30 | | | |
| Q | 3.80 4.20 | | | |

GENERIC MARKING DIAGRAM*



= Year ww = Work Week XXXXX = Device Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

2., 4. DRAIN 3. GATE

= Pb-Free Package

| | EMITTER COLLECTOR BASE | 2., 4. | CATHODE ANODE GATE | STYLE 3: PIN 1. 2., 4. 3. | COLLECTOR | , | ANODE 1 ANODE 2 GATE | STYLE 5: PIN 1. 2., 4. 3. | |
|--------------------|------------------------------|--------------------|--------------------------|------------------------------------|-----------|--------------------|----------------------------|------------------------------------|--------|
| STYLE 6: PIN 1. | CATHODE | STYLE 7: PIN 1. | MT 1 | STYLE 8: PIN 1. | SOURCE | STYLE 9: PIN 1. | GATE | STYLE 10: PIN 1. | SOURCE |

2., 4. GATE 3. DRAIN

DRAIN

2., 4. 3. DRAIN

2., 4. GATE 3. MT 2

| DOCUMENT NUMBER: | 98ASB42049B | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. | | |
|------------------|-------------|---|-------------|--|
| DESCRIPTION: | TO-225 | | PAGE 1 OF 1 | |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

2., 4. 3. GATE

ANODE

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative