

## 391A.CPE - ELECTRICIANS DIAGONAL CUTTERS



### Standards :

NF ISO 5749, ISO 5749, DIN ISO 5749, ASME B107.500

### Description :

- Snipe nose for confined space (electrical cabinets, wiring).
- Semi-flush cutting edges, designed to cleanly cut through all types of wire: piano wires, thin copper wires, modern materials.
- Long lever arm, offset pivot for minimum cutting effort.
- High durability Chrome-Molybdenum-Vanadium steel, very hard cutting edges 61/63 HRc.
- Ergonomic grips resistant to chemical agents.
- Return spring.
- Finish: chromed.

### References :

	B [MM]	B1 [MM]	C [MM]	D MAXI [MM]	E [MM]	L [MM]	L1 [MM]	CU - Ø MAX [MM <sup>2</sup> ]	[G]
391A.14VE	21,5	14	15,5	1,4	9,5	145	9	0,7 - 3,0	190
391A.16CPE	19	15	21	1,6	10	165	9		190
391A.14CPE	21,5	14	15,5		9,5	145	9		160