





# MLF1608A3R3JT000

Applications	 Commercial Grade
Feature	 Multilayer
	 Magnetic Shield
	 Ferrite Core
Series	MLF Series / MLF1608 Type
Status	Production



Size	
Length(L)	1.60mm +/-0.15mm
Width(W)	0.80mm +/-0.15mm
Thickness(T)	0.80mm +/-0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.


Electrical Characteristics	
Inductance	3.3uH +/-5% at 10MHz
Rated Current	30mA
Self-Resonant Frequency [Min.]	65MHz
Self-Resonant Frequency [Typ.]	100MHz
Q [Min.]	35 at 10MHz
Q [Typ.]	60 at 10MHz
DC Resistance [Nom.]	550mΩ
DC Resistance [Max.]	1.3Ω

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.
Weight	0.004g


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# MLF1608A3R3JT000


**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




**MLF1608A3R3JT000**



**MLF1608A3R3JT000**



**MLF1608A3R3JT000**





**MLF1608A3R3JT000**

•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# MLF1608A3R3JT000

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.  
•All specifications are subject to change without notice.