





MLF2012C180KT000

Applications	 Commercial Grade
Feature	 Multilayer
	 Magnetic Shield
	 Ferrite Core
Series	MLF Series / MLF2012 Type
Status	Production



Size	
Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	1.25mm +/-0.20mm
Recommended Land Pattern (A)	0.80mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	1.20mm Nom.


Electrical Characteristics	
Inductance	18uH +/-10% at 1MHz
Rated Current	5mA
Self-Resonant Frequency [Min.]	20MHz
Self-Resonant Frequency [Typ.]	38MHz
Q [Min.]	30 at 1MHz
Q [Typ.]	45 at 1MHz
DC Resistance [Nom.]	380mΩ
DC Resistance [Max.]	800mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 85degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.014g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

MLF2012C180KT000


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLF2012C180KT000



MLF2012C180KT000



MLF2012C180KT000






MLF2012C180KT000

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

MLF2012C180KT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.
•All specifications are subject to change without notice.