


# 1.5KExxA, 1.5KExxCA

# Datasheet

1500 W TVS in DO-201



#### Product status link

## Features

- Peak pulse power:
  - 1500 W (10/1000 μs)
  - up to 10 kW (8/20 μs)
- Stand-off voltage range from 5 V to 376 V
- Unidirectional and bidirectional types
- Operating T<sub>i</sub> max: 175 °C
- High power capability at T<sub>i</sub> max.: up to 1100 W (10/1000 μs)
- Lead finishing: matte tin plating

## Complies with the following standards

- UL94, V0
- J-STD-020 MSL level 1
- J-STD-002, JESD 22-B102 E3 and MIL-STD-750, method 2026
- JESD-201 class 2 whisker test
- UL 497B file number: QVGQ2.E136224
  - IEC 61000-4-4 level 4:
  - 4 k V
- IEC 61000-4-2, C = 150 pF, R = 330 Ω exceeds level 4:
  - 30 kV (air discharge)
  - 30 kV (contact discharge)

# **Description**

The 1.5KE TVS series is designed to protect sensitive equipment against electrostatic discharges according to IEC 61000-4-2, MIL STD 883 Method 3015, and electrical overstress such as IEC 61000-4-4 and 5. They are used for surges below 1500 W 10/1000  $\mu$ s.

This planar technology makes it compatible with high-end equipment and SMPS where low leakage current and high junction temperature are required to provide reliability and stability over time.




# 1 Characteristics


Table 1	Absoluto	maximum	ratinge	(T 25 °C)	`
Table 1.	Absolute	maximum	raungs	$(T_{amb} = 25 °C)$	)

Symbol	Parameter	Value	Unit			
		IEC 61000-4-2 (C = 150 pF, R = 330 Ω)				
V <sub>PP</sub>	Peak pulse voltage	Contact discharge	30	kV		
		Air discharge	30			
P <sub>PP</sub>	Peak pulse power dissipation	10/1000 μs, T <sub>j</sub> initial = T <sub>amb</sub>	1500	W		
I <sub>FSM</sub>	Non repetitive surge peak forward current for unidirectional types	t <sub>p</sub> = 10 ms, T <sub>j</sub> initial = T <sub>amb</sub>	200	А		
T <sub>stg</sub>	Storage temperature range	-65 to +175	°C			
Tj	Operating junction temperature range	-55 to +175	°C			
TL	T <sub>L</sub> Maximum lead temperature for soldering during 10 s at 5 mm from case					

#### Figure 1. Electrical characteristics - parameter definitions







		-4.34			• (1)		10 /	/ 1000 μ	S	8	/ 20µs		
	I <sub>RM</sub> max	at v <sub>RM</sub>		V <sub>BR</sub> at	BR (")		V <sub>CL</sub> <sup>(2)(3)</sup>	I <sub>PP</sub> <sup>(4)</sup>	R <sub>D</sub>	V <sub>CL</sub> <sup>(2)(3)</sup>	I <sub>PP</sub> <sup>(4)</sup>	R <sub>D</sub>	αΤ
Туре	25 °C		Min.	Тур.	Max.		Max.		Max.	Max.		Max.	Max.
	μA	v		v		mA	v	A	Ω	v	A	Ω	10 <sup>-4</sup> /°C
1.5KE6V8A/CA	1000	5.8	6.45	6.8	7.14	10	10.5	143	0.023	13.4	746	0.008	5.7
1.5KE10A/CA	10	8.55	9.5	10	10.5	1	14.5	100	0.040	18.6	538	0.015	7.3
1.5KE12A/CA	5	10.2	11.4	12	12.6	1	16.7	90	0.046	21.7	461	0.020	7.8
1.5KE15A/CA	1	12.8	14.3	15	15.8	1	21.2	71	0.076	27.2	368	0.031	8.4
1.5KE18A/CA	1	15.3	17.1	18	18.9	1	25.2	59.5	0.106	32.5	308	0.044	8.8
1.5KE24A/CA	1	20.5	22.8	24	25.2	1	33.2	45	0.178	42.8	234	0.075	9.4
1.5KE27A/CA	1	23.1	25.7	27	28.4	1	37.5	40	0.228	48.3	207	0.096	9.6
1.5KE30A/CA	1	25.6	28.5	30	31.5	1	41.5	36	0.278	53.5	187	0.118	9.7
1.5KE33A/CA	1	28.2	31.4	33	34.7	1	45.7	33	0.333	59	169	0.144	9.8
1.5KE36A/CA	1	30.8	34.2	36	37.8	1	49.9	30	0.403	64.3	156	0.170	9.9
1.5KE39A/CA	1	33.3	37.1	39	41	1	53.9	28	0.461	69.7	143	0.201	10.0
1.5KE47A/CA	1	40.2	44.7	47	49.4	1	64.8	23.2	0.664	84	119	0.291	10.1
1.5KE56A/CA	1	47.8	53.2	56	58.8	1	77	19.5	0.933	100	100	0.412	10.3
1.5KE62A/CA	1	53.0	58.9	62	65.1	1	85	17.7	1.12	111	90	0.510	10.4
1.5KE68A/CA	1	58.1	64.6	68	71.4	1	92	16.3	1.26	121	83	0.598	10.4
1.5KE82A/CA	1	70.1	77.9	82	86.1	1	113	13.3	2.02	146	69	0.868	10.5
1.5KE100A/CA	1	85.5	95.0	100	105	1	137	11	2.91	178	56	1.30	10.6
1.5KE120A/CA	1	102	114	120	126	1	165	9.1	4.29	212	47	1.83	10.7
1.5KE150A/CA	1	128	143	150	158	1	207	7.2	6.81	265	38	2.82	10.8
1.5KE180A/CA	1	154	171	180	189	1	246	6.1	9.34	317	31.5	4.06	10.8
1.5KE200A/CA	1	171	190	200	210	1	274	5.5	11.6	353	28	5.11	10.8
1.5KE220A/CA	1	188	209	220	231	1	328	4.6	21.1	388	26	6.04	10.8
1.5KE250A/CA	1	213	237	250	263	1	344	5.0	16.2	442	23	7.78	11
1.5KE300A/CA	1	256	285	300	315	1	414	5.0	19.8	529	19	11.3	11
1.5KE350A/CA	1	299	332	350	368	1	482	4.0	28.5	618	16	15.6	11
1.5KE400A/CA	1	342	380	400	420	1	548	4.0	32.0	706	14	20.4	11
1.5KE440A/CA	1	376	418	440	462	1	603	3.5	40.3	776	13	24.2	11

## Table 2. Electrical characteristics - parameter values (T<sub>amb</sub> = 25 °C, unless otherwise specified)

1. To calculate  $V_{BR}$  versus  $T_j$ :  $V_{BR}$  at  $T_j = V_{BR}$  at 25 °C x (1 +  $\alpha T x (T_j - 25)$ )

2. To calculate  $V_{CL}$  versus  $T_j$ :  $V_{CL}$  at  $T_j = V_{CL}$  at 25 °C x (1 +  $\alpha T$  x ( $T_j$  - 25))

3. To calculate  $V_{CL}$  max versus  $I_{PPappli}$ :  $V_{CLmax} = V_{CL} - R_D x (I_{PP} - I_{PPappli})$  where  $I_{PP appli}$  is the surge current in the application

4. Surge capability given for both directions for unidirectional (A type) and bidirectional (CA type) devices



#### **Characteristics (curves)** 1.1








Figure 5. Maximum peak pulse current versus clamping voltage























57

# 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.


# 2.1 DO-201 package information


#### Figure 13. DO-201 package outline




			Dimer	nsions					
Ref.		Millimeters		Inches (for reference only)					
	Min.	Тур.	Max.	Min.	Тур.	Max.			
A	8.50	-	9.50	0.334	-	0.374			
В	25.4	-		1.000	-				
С	4.80	-	5.30	0.189	-	0.209			
D	0.96	-	1.06	0.038	-	0.042			








## Figure 18. Ammopack dimension values (mm)



	36 - Rev 5
Downloaded from	Arrow.com.

## Figure 19. Tape outline



Dimensions are not to scale


Unidirectional components are oriented with red tape on the cathode and white tape on the anode. Bidirectional components have red tape on both sides.

### Table 4. Tape dimension values

		Dimensions	
Ref.		Millimeters	
	Min.	Тур.	Max.
A	9.5	10	10.5
В	51	53	55
С	63	65	67

# 2.2 Reflow profile

Figure 20. ST ECOPACK recommended soldering reflow profile for PCB mounting



*Note:* Minimize air convection currents in the reflow oven to avoid component movement. Maximum soldering profile corresponds to the latest IPC/JEDEC J-STD-020.



# **3** Ordering information

## Table 5. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
1.5KExxARL/CARL <sup>(1)</sup>	Equal to order code (without RL suffix)	DO-201	0.876 a	1900	Reel
1.5KExxA/CA	Equal to order code	00-201	0.070 g	600	Ammopack

1. Where xx is nominal value of  $V_{BR}$  and A or CA indicates unidirectional or bidirectional version.

# **Revision history**

### Table 6. Document revision history

Date	Revision	Changes
Feb -2002	3A	Last issue.
12-Mar-2012	4	Added UL statement, Table 5 and ordering information.
28-Sep-2022	5	Updated package information. Minor text changes.

#### IMPORTANT NOTICE - READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics – All rights reserved