

**VPU AC I O 300/12.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

**General ordering data**

Version	Spare arrester, Surge protection, $U_p(L/N-PE) \leq 1.5$ kV
Order No.	<a href="#">2591370000</a>
Type	VPU AC I O 300/12.5
GTIN (EAN)	4050118599565
Qty.	1 pc(s).

Creation date May 19, 2022 11:56:33 AM CEST

Catalogue status 06.05.2022 / We reserve the right to make technical changes.

## VPU AC I 0 300/12.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	80 mm	Depth (inches)	3.15 inch
Height	45 mm	Height (inches)	1.772 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	112 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

## Probability of failure

MTBF	15 Years		
------	----------	--	--

## Rated data UL

Rated Voltage $U_N$	240 V	MCOV (L/N-PE)	300 V
SCCR	150 kA	$I_n$	20 kA
Category	SPD TYPE 1CA	Certificate No. (cURus)	E354261
MODE	L-N, L-G	VPR (L-N)	900 V
VPR (L-PE)	900 V	Voltage type	AC

## General data

Colour	orange	Operating altitude	≤ 4000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20 in installed state
Segment	Power distribution	UL 94 flammability rating	V-0
Version	Surge protection		

## Rated data IEC / EN

Discharge current $I_{max}$ (8/20 $\mu$ s) wire-PE	50 kA	Discharge current $I_n$ (8/20 $\mu$ s) wire-PE	20 kA
Energy coordination (≤10 m)	Type I, Type II, Type III	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	No Fuse necessary ≤315 A gG, 250 A gG @50 kA I <sub>sc</sub> , 315 A gG @25 kA I <sub>sc</sub>
Leakage current at $U_n$	0.6 mA	Lightning test current $I_{imp}$ (10/350 $\mu$ s) (L-PE)	12.5 kA
Mains voltage	240 V	Max. continuous voltage, $U_c$ (AC)	300 V
Number of poles	1	Protection level $U_p$ (typ.)	≤ 1.5 kV
Rated voltage (AC)	230 V	Requirements category acc. to IEC 61643-11	Type I, Type II
Requirements class, acc. to EN 61643-11	T1, T2	Response time	≤ 25 ns
Standards	IEC61643-11, EN61643-11, UL 1449	Voltage type	AC

## Connection data

Type of connection	Plug-in connection		
--------------------	--------------------	--	--

Creation date May 19, 2022 11:56:33 AM CEST

Catalogue status 06.05.2022 / We reserve the right to make technical changes.

2

## VPU AC I 0 300/12.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Ratings IECEx/ATEX/cUL

Certificate no. (cULus) E354261

## Guarantee

Time interval 5 years

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

## Approvals

Approvals



ROHS Conform

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC VPU SERIES</a> <a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel / Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

VPU AC I O 300/12.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

Electric symbol

