





# MLF2012C101KT000

Applications		Commercial Grade
Feature		Multilayer
		Magnetic Shield
		Ferrite Core
Series	MLF Series / MLF2012 Type	
Status	Production	



Size	
Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	1.25mm +/-0.20mm
Recommended Land Pattern (A)	0.80mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	1.20mm Nom.


Electrical Characteristics	
Inductance	100uH +/-10% at 1MHz
Rated Current	2mA
Self-Resonant Frequency [Min.]	7MHz
Self-Resonant Frequency [Typ.]	12MHz
Q [Min.]	25 at 1MHz
Q [Typ.]	45 at 1MHz
DC Resistance [Nom.]	2.5Ω
DC Resistance [Max.]	3.1Ω

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 85degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.014g


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# MLF2012C101KT000


**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




**MLF2012C101KT000**



**MLF2012C101KT000**



**MLF2012C101KT000**






**MLF2012C101KT000**

•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# MLF2012C101KT000

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.  
•All specifications are subject to change without notice.