




2.4 GHz low pass filter matched to STM32WB55Cx/Rx, STM32WB50Cx, STM32WB35Cx and STM32WB30Cx



Top view (pads down)



Product status link

MLPF-WB55-01E3

Features

- Integrated impedance matching to STM32WB55Cx/Rx, STM32WB50Cx, STM32WB35Cx and STM32WB30Cx
- LGA footprint compatible
- 50 Ω nominal impedance on antenna side
- · Deep rejection harmonics filter
- · Low insertion loss
- · Small footprint
- Low thickness ≤ 450 µm
- · High RF performance
- · RF BOM and area reduction
- ECOPACK2 compliant

Applications

- Bluetooth 5
- OpenThread
- Zigbee®
- IEEE 802.15.4
- Optimized for STM32WB55Cx/Rx, STM32WB50Cx, STM32WB35Cx and STM32WB30Cx

Description

The MLPF-WB55-01E3 integrates an impedance matching network and harmonics filter. The matching impedance network has been tailored to maximize the RF performance of STM32WB. This device uses STMicroelectronics IPD technology on non-conductive glass substrate which optimizes RF performance.



1 Characteristics

Table 1. Absolute ratings (T_{amb} = 25 °C)

Symbol	Parameter	Value	Unit
P _{IN}	Input power RF _{IN}	10	dBm
V _{ESD}	ESD ratings human body model (JESD22-A114-C), all I/O one at a time while others connected to GND	2000	V
	ESD ratings machine model, all I/O	200	
T _{OP}	Maximum operating temperature	-40 to +105	°C

Table 2. Impedances(T_{amb} = 25 °C)

Symbol	Parameter		Unit		
Symbol	raiailletei	Min.	Тур.	Max.	Oiiit
			matched to		
			71		
Z _{IN}	STM32WB55xx single-ended	_	STM32WB50Cx,		Ω
∠IN	impedance	-	STM32WB35Cx,	-	
			and		
			STM32WB30Cx		
Z _{OUT}	Antenna impedance	-	50	-	Ω


Table 3. Electrical characteristics and RF performance (T_{amb} = 25 °C)

Symbol	Parameter		Value			Unit
Symbol			Min.	Тур.	Max.	Oilit
f	Frequency range	Frequency range			2500	MHz
IL	Insertion loss IS ₂₁ I			0.90	1.1	dB
RL _{IN}	Input return loss IS ₁₁ I		14	22		dB
RL _{OUT}	Output return loss IS ₂₂ I		16	24		dB
	Harmonic Att rejection levels IS ₂₁ I	Attenuation at 2fo	38	40		dB
A++		Attenuation at 3fo	43	45		dB
Att		Attenuation at 4fo	41	46		dB
		Attenuation at 5fo	35	42		dB


DS12804 - Rev 3 page 2/13





1.1 RF measurement
















DS12804 - Rev 3 page 3/13







DS12804 - Rev 3 page 4/13



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 Bumpless CSP package information

Figure 9. Bumpless CSP package outline





Table 4. Bumpless CSP package mechanical data

Parameter	Description	Min.	Тур.	Max.	Unit
Х	X dimension of the die	975	1000	1025	μm
Y	Y dimension of the die	1575	1600	1625	μm
Α	X pitch		500		μm
В	Y pitch		587		μm
A1	Distance from bump to edge of die on X axis		250		μm
B1	Distance from pad to edge of die on Y axis		213		μm
а	Pad dimension		200		μm
Т	Substrate thickness	375	400	425	μm

DS12804 - Rev 3 page 5/13






More packing information is available in the application note:

AN2348 Flip-Chip: "Package description and recommendations for use

Figure 12. Tape and reel outline



Note: Pocket dimensions are not on scale Pocket shape may vary depending on package

DS12804 - Rev 3 page 6/13



Table 5. Tape and reel mechanical data

	Dimensions				
Ref	Millimeters				
	Min	Тур	Max		
A0	1.04	1.09	1.14		
В0	1.64	1.69	1.74		
K0	0.47	0.52	0.57		
P1	3.9	4.0	4.1		
P0	3.9	4.0	4.1		
Ø D0	1.4	1.5	1.6		
Ø D1	0.35	0.40	0.45		
F	3.45	3.50	3.55		
P2	1.95	2.00	2.05		
W	7.9	8.0	8.3		

Table 6. Pad description top view (pads down)

Pad ref	Pad name	Description
A1	OUT	Antenna
A2	GND4	Ground
A3	IN	STM32WB55 RF out
B1	GND3	Ground
B2	GND2	Ground
В3	GND1	Ground

DS12804 - Rev 3 page 7/13



3 Recommendation on PCB assembly

3.1 Land pattern




Figure 13. PCB land pattern recommendations

Transmission line between MLPF and antenna is dimensioned to 50 ohms characteristic impedance.

Transmission line between STM32 and MLPF is dimensioned to 62 ohms characteristic impedance.

Theses transmission line characteristics impedances have to be followed as close as possible.

Moreover, lines physical dimensions will have to be tuned according to specific PCB stack up if different from the one presented in datasheet to keep expected characteristic impedance values.



Figure 14. PCB stack-up recommendations

DS12804 - Rev 3 page 8/13



3.2 Stencil opening design

Top_Layer Stencil_Opening (Stencil opening aligned with footprint dimensions)

Figure 15. Stencil opening recommendations

3.3 Solder paste

- 1. 100 µm solder stencil thickness is recommended to be drunk
- 2. Halide-free flux qualification ROL0 according to ANSI/J-STD-004.
- 3. "No clean" solder paste is recommended.
- 4. Offers a high tack force to resist component movement during PCB movement.
- 5. Solder paste with fine particles: powder particle size is 20-45 μ m.

3.4 Placement

- 1. Manual positioning is not recommended.
- 2. It is recommended to use the lead recognition capabilities of the placement system, not the outline centering
- 3. Standard tolerance of ±0.05 mm is recommended.
- 4. 1.0 N placement force is recommended. Too much placement force can lead to squeezed out solder paste and cause solder joints to short. Too low placement force can lead to insufficient contact between package and solder paste that could cause open solder joints or badly centered packages.
- 5. To improve the package placement accuracy, a bottom side optical control should be performed with a high resolution tool.
- 6. For assembly, a perfect supporting of the PCB (all the more on flexible PCB) is recommended during solder paste printing, pick and place and reflow soldering by using optimized tools.

DS12804 - Rev 3 page 9/13



3.5 PCB design preference

- 1. To control the solder paste amount, the closed via is recommended instead of open vias.
- 2. The position of tracks and open vias in the solder area should be well balanced. A symmetrical layout is recommended, to avoid any tilt phenomena caused by asymmetrical solder paste due to solder flow away.

DS12804 - Rev 3 page 10/13



4 Ordering information

Figure 16. Ordering information scheme




Table 7. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
MLPF-WB55-01E3	TS	Bumpless CSP	1.546 mg	5000	Tape and reel (7")

DS12804 - Rev 3 page 11/13



Revision history

Table 8. Document revision history

Date	Version	Changes
12-Dec-2018	1	Initial release.
10-Sep-2020	2	Inserted STM32WB50Cx, STM32WB35Cx and STM32WB30Cx product.
25-Nov-2022	3	Added Section 3.1 Land pattern.

DS12804 - Rev 3 page 12/13



IMPORTANT NOTICE - READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics - All rights reserved

DS12804 - Rev 3 page 13/13