

VPU I 0 280V/12,5KA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Spare arrester Type I

Weidmüller VPU I surge protection products protect low-voltage consumer installations and electronic devices against overvoltages that can occur as a result of atmospheric discharges (thunderstorms) or switching operations (transients). The VPU I series meets the Type I and Type II requirements acc. to IEC 61643-11 and the Type 1 and Type 2 requirements acc. to EN 61643-11. The spare arresters are coded and can only be inserted into suitable bases.

General ordering data

Version	Surge voltage arrester, Low voltage, Accessories, Spare arrester
Order No.	1352120000
Type	VPU I 0 280V/12,5KA
GTIN (EAN)	4050118158120
Qty.	1 pc(s).

Creation date May 19, 2022 11:57:47 AM CEST

Catalogue status 06.05.2022 / We reserve the right to make technical changes.

VPU I 0 280V/12,5KA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	52 mm	Height (inches)	2.047 inch
Width	17.8 mm	Width (inches)	0.701 inch
Net weight	122 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Humidity	5 - 95% rel. humidity		

General data

Colour	orange	Design	Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Segment	Power distribution	UL 94 flammability rating	V-0
Version	Spare arrester		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	IV
--------------------	---	------------------------	----

Rated data IEC / EN

Discharge current I_{max} (8/20 μ s) wire-PE	50 kA	Discharge current I_n (8/20 μ s) wire-PE	25 kA
Follow-on current extinguishing capability I_{fi}	Not available due for technical reasons	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	No Fuse necessary \leq 250 A gG, 250 A gL (if back up fuse > 250 A)
Leakage current at U_n	100 μ A	Lightning test current I_{imp} (10/350 μ s) (L-PE)	12.5 kA
Max. continuous voltage, U_c (AC)	280 V	Number of poles	1
Protection level U_p at I_N (L/N-PE)	\leq 1.4 kV	Rated voltage (AC)	230 V
Requirements category acc. to IEC 61643-11	Type I, Type II	Requirements class, acc. to EN 61643-11	T1, T2
Response time	\leq 25 ns	Short-circuit current rating I_{SCCR}	25 kA
Standards	IEC61643-11, EN61643-11	Temporary surge voltage (over-voltage) - TOV	438 V
Voltage type	AC		

Connection data

Type of connection	pluggable
--------------------	-----------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

Data sheet

VPU I O 280V/12,5KA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Tender specification sheets

Long specification	Spare arrester for VPU I 280 V-series surge voltage arrester with 12.5 kA. The pluggable high-performance varistors made from V0 material can be replaced by trained personnel following a failure. Rated voltage: 280 V Type: Weidmüller VPU I O 280 V/12.5 kA Order No.: 1352120000	Short specification	Spare arrester for VPU I 280 V-series surge voltage arrester with 12.5 kA. The pluggable high-performance varistors can be replaced by trained personnel following a failure. Rated voltage: 280 V Type: Weidmüller VPU I O 280 V/12.5 kA Order No.: 1352120000
--------------------	---	---------------------	---

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	EAC VPU SERIES EU_Konformitätserklärung / EU_Declaration_of_Conformity
Engineering Data	EPLAN, WSCAD
User Documentation	Beipackzettel / Instruction sheet
Catalogues	Catalogues in PDF-format

Electric symbol

