




# MMZ1608Y300BTA00

Applications	 Commercial Grade
Feature	 High Speed Signal Line
Series	MMZ Series / MMZ1608 Type
Status	Production



Size	
Length(L)	1.60mm +/-0.15mm
Width(W)	0.80mm +/-0.15mm
Thickness(T)	0.80mm +/-0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.


Electrical Characteristics	
Impedance at 100MHz	30Ω +/-25%
Rated Current	1.5A
DC Resistance [Max.]	50mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.
Weight	0.004g


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# MMZ1608Y300BTA00

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)



MMZ1608Y300BTA00(Z) MMZ1608Y300BTA00(R) MMZ1608Y300BTA00(X)



MMZ1608Y300BTA00

Temperature Rise by DC
no data available

Derating
no data available

- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.