
BES 12,0-KH-2S Order code: BAM00E0

Mounting clamp





Basic data

Application Scope of delivery

Use with sensors Ø12mm and M12 Clamp holder (1x) Nut DIN 1763 M16x1 (2x)

Mechanical data

Dimensions Mounting type Tightening torque
Tightening torque for clamping 22.0 mm x 34.0 mm screwing/clamping 20 Nm 1.5 Nm

Material Surface protection CuZn Nickel-plated

Remarks

The fixed stop may alter the switching distance of the proximity switch.

The proximity switch is inserted into the clamp holder up to the fixed stop and secured using a pressure screw. For proximity switches from fixing length 30 mm

Definitions see general catalog

Subject to change without notice.

00000000000/552166/00000000

Internet **Balluff Germany** Balluff USA **Balluff China**

: www.balluff.com : +49 (0) 7158 173-0, 173-370 : 1-800-543-8390 : +86 (0) 21-50 644131