





MLP2520S100MT0S1

| | |
|--------------|--|
| Applications |  Commercial Grade |
| Feature |  Multilayer |
| |  Magnetic Shield |
| |  Ferrite Core |
| Series | MLP Series / MLP2520 Type |
| Status | Production |



| Size | |
|------------------------------|------------------|
| Length(L) | 2.50mm +/-0.15mm |
| Width(W) | 2.00mm +/-0.15mm |
| Thickness(T) | 0.85mm +/-0.15mm |
| Recommended Land Pattern (A) | 0.70mm Nom. |
| Recommended Land Pattern (B) | 1.40mm Nom. |
| Recommended Land Pattern (C) | 2.00mm Nom. |


| Electrical Characteristics | |
|---|---------------------|
| Inductance | 10uH +/-20% at 2MHz |
| Rated Current (Temperature Rise) [Max.] | 700mA (40degC Rise) |
| DC Resistance [Nom.] | 280mΩ |
| DC Resistance [Max.] | 364mΩ |

| Other | |
|---|--------------------------------------|
| Operating Temp. Range (Including Self-Temp. Rise) | -40 to 125degC |
| Soldering Method | Reflow, Iron Soldering |
| AEC Q200 | No |
| Packing | Blister (Plastic)Taping [180mm Reel] |
| Package Quantity | 3000Pcs Min. |
| Weight | 0.015g |


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

MLP2520S100MT0S1


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLP2520S100MT0S1



MLP2520S100MT0S1



MLP2520S100MT0S1





MLP2520S100MT0S1

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

MLP2520S100MT0S1

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.
•All specifications are subject to change without notice.