



Micro Commercial Components 20736 Marilla Street Chatsworth CA 91311

Phone: (818) 701-4933 Fax: (818) 701-4939 **MMBT3904**

Features

- Halogen free available upon request by adding suffix "-HF"
- Capable of 350mWatts of Power Dissipation and 200mA lc.
- Operating and Storage Junction Temperatures: -55[°]C to 150[°]C
- Surface Mount SOT-23 Package
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisure Sensitivity Level 1
- Marking Code:1AM
- Thermal Resistance Junction to Ambient: 357 °C/W
- Thermal Resistance Junction to Case: 185 °C/W

Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Max	Units
OFF CHARA	OFF CHARACTERISTICS			
V _{(BR)CEO}	Collector-Emitter Breakdown Voltage* (I _C =1.0mAdc, I _B =0)	40		Vdc
V _{(BR)CBO}	Collector-Base Breakdown Voltage (I _C =10μAdc, I _E =0)	60		Vdc
V _{(BR)EBO}	Emitter-Base Breakdown Voltage (I _E =10μAdc, I _C =0)	6.0		Vdc
I _{CBO}	Collector Cutoff Current (V _{CB} =30Vdc, V _{BE} =3.0Vdc)		50	nAdc
I _{CEX}	Collector Cutoff Current (V _{CE} =30Vdc, V _{BE} =3.0Vdc)		50	nAdc

ON CHARACTERISTICS

OII OIIMIIM	ON OHAHAUTEHIOTIOO				
h _{FE}	DC Current Gain*				
	$(I_C=0.1 \text{mAdc}, V_{CE}=1.0 \text{Vdc})$	40			
	(I _C =1.0mAdc, V _{CE} =1.0Vdc)	70			
	$(I_C=10\text{mAdc}, V_{CE}=1.0\text{Vdc})$	100	300	300	
	$(I_C=50 \text{mAdc}, V_{CE}=1.0 \text{Vdc})$	60			
	$(I_C=100 \text{mAdc}, V_{CE}=1.0 \text{Vdc})$	30			
V _{CE(sat)}	Collector-Emitter Saturation Voltage				
	$(I_C=10\text{mAdc}, I_B=1.0\text{mAdc})$		0.2	Vdc	
	$(I_C=50 \text{mAdc}, I_B=5.0 \text{mAdc})$		0.3		
V _{BE(sat)}	Base-Emitter Saturation Voltage				
. ,	(I _C =10mAdc, I _B =1.0mAdc)	0.65	0.85	Vdc	
	(I _C =50mAdc, I _B =5.0mAdc)		0.95		

SMALL-SIGNAL CHARACTERISTICS


f_T	Current Gain-Bandwidth Product			
	$(I_C=10\text{mAdc}, V_{CE}=20\text{Vdc}, f=100\text{MHz})$	300		MHz
C _{obo}	Output Capacitance			
	$(V_{CB}=5.0Vdec, I_{E}=0, f=1.0MHz)$		4.0	pF
C_{ibo}	Input Capacitance			
	$(V_{BE}=0.5Vdc, I_{C}=0, f=1.0MHz)$		8.0	pF
NF	Noise Figure			
	(I_C =100μAdc, V_{CE} =5.0Vdc, R_S =1.0k Ω		5.0	dB
	f=10Hz to 15.7kHz)			


SWITCHING CHARACTERISTICS

t_{d}	Delay Time	$(V_{CC}=3.0Vdc, V_{BE}=0.5Vdc$	35	ns
t _r	Rise Time	I _C =10mAdc, I _{B1} =1.0mAdc)	35	ns
ts	Storage Time	(V _{CC} =3.0Vdc, I _C =10mAdc	200	ns
t _f	Fall Time	$I_{B1} = I_{B2} = 1.0 \text{mAdc}$	50	ns

*Pulse Width $\leq 300 \mu s$, Duty Cycle $\leq 2.0\%$


NPN General Purpose Amplifier





DIMENSIONS					
	INCHES		MM		
DIM	MIN	MAX	MIN	MAX	NOTE
Α	.110	.120	2.80	3.04	
В	.083	.104	2.10	2.64	
O	.047	.055	1.20	1.40	
D	.035	.041	.89	1.03	
Е	.070	.081	1.78	2.05	
F	.018	.024	.45	.60	
Ð	.0005	.0039	.013	.100	
Τ	.035	.044	.89	1.12	
٦	.003	.007	.085	.180	
K	.015	.020	.37	.51	


Suggested Solder Pad Layout



MMBT3904





Typical Characteristics





MMBT3904







Ordering Information:

Device	Packing
Part Number-TP	Tape&Reel 3Kpcs/Reel

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.