

# EMLP (17X7)R - Label

0826844

<https://www.phoenixcontact.com/us/products/0826844>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 17 x 7 mm, Number of individual labels: 500

## Your advantages

- The EMLP ... self-adhesive markers are particularly suited to marking electrical components, devices, and buttons
- The markers meet the same standards as the engraved labels, they provide high-quality visuals
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers in accordance with your requirements

## Commercial Data

Item number	0826844
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	BG16
Product Key	BG2411
Catalog Page	Page 328 (C-3-2019)
GTIN	4046356365888
Weight per Piece (including packing)	102.3 g
Weight per Piece (excluding packing)	83.5 g
Customs tariff number	39269097
Country of origin	DE

## Technical Data

### Product properties

Product type	Device marking
--------------	----------------

### Marking

Number of individual labels	500
Number of individual labels per row	2

### Marking technology

Device	0804501 THERMOMARK ROLLMASTER 300
	0804663 THERMOMARK ROLLMASTER 600
	1085260 THERMOMARK ROLL 2.0
	1285306 THERMOMARK E.300
	1285310 THERMOMARK E.600
Ink ribbon	5145384 THERMOMARK-RIBBON 110 0800687 THERMOMARK-RIBBON 110/50
Printability	Thermal transfer

### Mounting

Mounting type	adhesive
---------------	----------

### Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white
Material	Polyester
Components	Silicone-free

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

#### UV resistance

# EMLP (17X7)R - Label



0826844

<https://www.phoenixcontact.com/us/products/0826844>

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Specification	ISO 175:2010 (following)
Test duration	168 h

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (storage/transport)	4 °C ... 38 °C
Ambient temperature (assembly)	> 18 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

## Dimensions

Width	17 mm
Length	7 mm

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# EMLP (17X7)R - Label



0826844

<https://www.phoenixcontact.com/us/products/0826844>

## Classifications

### ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

### ETIM

ETIM 8.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EMLP (17X7)R - Label

0826844

<https://www.phoenixcontact.com/us/products/0826844>



## Accessories

### THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/us/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

---

### THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/us/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

# EMLP (17X7)R - Label

0826844

<https://www.phoenixcontact.com/us/products/0826844>



## THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/us/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

---

## THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/us/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

# EMLP (17X7)R - Label

0826844

<https://www.phoenixcontact.com/us/products/0826844>



## THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/us/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

---

## THERMOMARK-RIBBON 110 - Ink ribbon

5145384

<https://www.phoenixcontact.com/us/products/5145384>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., roll length: 300 m, width: 110 mm, color: black

# EMLP (17X7)R - Label

0826844

<https://www.phoenixcontact.com/us/products/0826844>



## THERMOMARK-RIBBON 110/50 - Ink ribbon

0800687

<https://www.phoenixcontact.com/us/products/0800687>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., roll length: 50 m, width: 110 mm, color: black

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)