

AMESP350U-277JZ





The AMESP350U-277JZ series is an efficient, enclosed, fan less, and semi-potted 350W AC-DC power supply module. Offering a wide commercial input voltage range of 85-305VAC, output voltage ranges from 5-48V, low power consumption, high efficiency, high reliability, and safer isolation.

This new series offers great operating temperatures, from -40°C to +85°C with full power up to 50°C and features an isolation of 4000VAC with improved reliability and system safety. Additionally, it has operating altitude of 5000m. Furthermore, a high MTBF of 300,000h, output short circuit protection (OSCP), output over-current protection (OCP), output overvoltage protection (OVP) and an over-temperature protection (OTP) come standard with the

The AMESP350U-277JZ is great for street lighting controls, grid power, instrumentation, industrial controls, communication, and civil applications.

1000

Isolation

(VAC)

AMESP350U-277JZ

1000

350.4

300

Power

(W)

125

85

-40

Temp. range

(°C)

125

50

-40

Derating

(°C)

Features



- Universal Input: 85 305VAC/120 430VDC
- Operating Temp: -40°C to +85°C
- High isolation voltage: 4000VAC
- Active PFC > 0.95
- Output short circuit, over-current, over-voltage, over temperature protection
- Efficiency up to 94%
- 150% peak load output for 1 second
- Operating altitude up to 5000m
- Certified: UL/EN/BS EN 62368-1
- Designed to meet: EN 60335-1, EN 61558-1, GB4943.1 standards



Training











Input voltage Output voltage

(V)

Summary

528

305

85


(VAC)

Applications





Coming Soon!



Application Notes







Power Grid


Industrial

Telecom



Models & Specifications





Input Specifications					
Parameters	Conditions	Typical	Minimum	Maximum	Units
Innest comment	115VAC			4	А
Input current	230VAC			2	А
Inrush current	Cold Start, 115VAC	16.7			Α
	Cold Start, 230VAC	42.3			А
Leakage	240VAC, 50Hz			0.5	mA RMS
Input Frequency			47	63	Hz
Power Factor	Full Load, 115VAC	0.98			
	Full Load, 230VAC	0.98			
Input Voltage Range	AC Input		85	305	VAC
	DC Input		120	430	VDC
Hot Plug	Unavailable				

Output Specifications				
Parameters	Conditions	Typical	Maximum	Units
Voltago accuracy	Full Load, 5V	±2		%
Voltage accuracy	Full Load, 12V/24V/36V/48V			%
Line regulation	Rated Load, 5V	±0.5		%
	Rated Load, 12V/24V/36V/48V	±0.3		%
Load Regulation	0%-100% load, 5V	±1		%
	0%-100% load, 12V/24V/36V/48V	±0.5		%
Ripple & Noise*	20MHz bandwidth (peak to peak value), 5V/12V		200	mV p-p
	20MHz bandwidth (peak to peak value), 24V/36V/48V		240	mV p-p
Hald on time	115VAC	12		ms
Hold up time	230VAC	12		ms

Note: *The "Tip and barrel method" is used for ripple and noise test, output parallel 47uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to Enclosed Switching Power Supply Application Notes for specific information.



Isolation Specification				
Parameters	Conditions	Minimum	Maximum	Units
Tested Input-GND		2000		VAC
Tested I/O voltage	60 sec, leakage ≤ 5mA	4000		VAC
Tested Output-GND voltage		1500		VAC
Resistance	500VDC	50		ΜΩ


Parameters	Conditions	Typical	Minimum	Maximum	Units
Safety class	Class I				
Over current protection	230VAC, rated load at room/high temperature, 110%-200%lo, delay protection, delay time 1s, self-recovery after the abnormality is removed				
Ter carrent protection	230VAC, rated load at low temperature, ≥110%lo, delay protection, delay time 1s, self-recovery after the abnormality is removed				
	5Vout, hiccup, self-recovery			6.5	VDC
	12Vout, hiccup, self-recovery			15.6	VDC
Over voltage protection	24Vout, hiccup, self-recovery			31.2	VDC
	36Vout, hiccup, self-recovery			46.8	VDC
	48Vout, hiccup, self-recovery			62.4	VDC
Over temperature protection	Output voltage turn off, self-re	covery after the	temperature d	rops	
	5V, Hiccup mode, constant current (200%lo-300%lo) works 200ms, turn off 10s, continuous, self-recovery Recovery time <10s after the short circuit disappear.				
hort circuit protection	12V/24V/36V/48V, Hiccup mode, constant current (200%lo-300%lo) works 1s, turn off 10s, continuous, self-recover Recovery time <10s after the short circuit disappear.				
Operating temperature					
	See derating graph	-40 to +85			°C
	See derating graph	-40 to +85 -40 to +85			°C
	See derating graph 55 °C to 85 °C, with aluminum plate		2.33		
itorage temperature			2.33		°C
	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output				°C %/°C
torage temperature	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output		2		°C %/°C %/°C
	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output		2 1.33		°C %/°C %/°C %/°C
torage temperature	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 70 °C to 85 °C, 230VAC, 12V/24V/36V/48V output		2 1.33 3.33		°C %/°C %/°C %/°C %/°C
torage temperature	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 70 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate		2 1.33 3.33 1.33		°C %/°C %/°C %/°C %/°C %/°C
torage temperature	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 70 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 110VAC, without aluminum plate 80VAC ~ 100VAC input voltage		2 1.33 3.33 1.33 1.33		°C %/°C %/°C %/°C %/°C
torage temperature ower Derating cooling	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 70 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 110VAC, without aluminum plate 80VAC ~ 100VAC input voltage	-40 to +85	2 1.33 3.33 1.33 1.33	95	°C %/°C %/°C %/°C %/°C %/°C
torage temperature Power Derating Cooling Iumidity	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 70 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 110VAC, without aluminum plate 80VAC ~ 100VAC input voltage Free air	-40 to +85	2 1.33 3.33 1.33 1.33 2	95	°C %/°C %/°C %/°C %/°C %/VAC
torage temperature Power Derating Cooling Humidity Case material	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 70 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 110VAC, without aluminum plate 80VAC ~ 100VAC input voltage Free air	-40 to +85	2 1.33 3.33 1.33 1.33 2	95	°C %/°C %/°C %/°C %/°C %/VAC % RH
torage temperature Power Derating Cooling Iumidity	55 °C to 85 °C, with aluminum plate 55 °C to 70 °C, 230VAC, 5V output without aluminum plate 70 °C to 85 °C, 230VAC, 5V output without aluminum plate 55 °C to 70 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 70 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 230VAC, 12V/24V/36V/48V output without aluminum plate 55 °C to 85 °C, 110VAC, without aluminum plate 80VAC ~ 100VAC input voltage Free air	-40 to +85 convection L6063, SGCC) 680	2 1.33 3.33 1.33 1.33 2	95	°C %/°C %/°C %/°C %/°C %/°C %/VAC


NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.




Safety Specifications			
Parameters			
Agency approvals	pprovals UL/EN/BS EN62368-1		
	Information technology Equipment	Designed to meet EN60335-1, EN61558-1, GB4943.1	
	EMC - Conducted and radiated emission	CISPR32 / EN55032, class B	
	Harmonic Current	IEC/EN61000-3-2 CLASS A	
	Voltage flicker	IEC/EN6100-3-3	
Standards	Electrostatic Discharge Immunity	IEC/EN 61000-4-2 Contact ±6KV, Air ±8KV, Criteria A	
Standards	RF, Electromagnetic Field Immunity	IEC/EN 61000-4-3 10V/m, Criteria A	
	Electrical Fast Transient/Burst Immunity	IEC/EN 61000-4-4 ±2KV, Criteria A with the recommended EMC circuit	
	Surge Immunity	IEC/EN 61000-4-5 L-L ±2KV, L-GND ±4KV, Criteria A	
	RF, Conducted Disturbance Immunity	IEC/EN 61000-4-6 10Vr.m.s, Criteria A	
	Voltage dips, Short Interruptions Immunity	IEC/EN 61000-4-11 0%, 70%, Criteria B	

Derating












Efficiency vs input voltage











Note:

- 1. That is a schematic diagram of side installation, install with M3x6 combination screws, derating refer to without aluminum plate curve.
- 2. That is the schematic diagram of the bottom installation, install with M3×4 round head screws, it is necessary to apply thermal grease on the bottom of the product, derating refer to with aluminum plate curve.

NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. **2.** Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. **3.** Mechanical drawings and specifications are for reference only. **4.** All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. **5.** Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. **6.** This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. **7.** Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.