MUR805G, MUR810G, MUR815G, MUR820G, MUR840G, MUR860G, MURF860G, SUR8820G, SUR8840G

Switch-mode Power Rectifiers

This series is designed for use in switching power supplies, inverters and as free wheeling diodes.

Features

- Ultrafast 25 and 50 Nanosecond Recovery Time
- 175°C Operating Junction Temperature
- Epoxy Meets UL 94 V−0 @ 0.125 in
- Low Forward Voltage
- Low Leakage Current
- Reverse Voltage to 600 V
- ESD Ratings:
  - Machine Model = C (> 400 V)
  - Human Body Model = 3B (> 16,000 V)
- SUR8 Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC−Q101 Qualified and PPAP Capable
- These Devices are Pb−Free and are RoHS Compliant*

Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 1.9 Grams (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max for 10 Seconds

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor®

http://onsemi.com

ULTRAFAST RECTIFIERS
8.0 AMPERES, 50−600 VOLTS





TO−220AC
CASE 221B
STYLE 1



TO−220 FULLPAK
CASE 221AG
STYLE 1

MARKING DIAGRAMS





A = Assembly Location
Y = Year
WW = Work Week
U8XX = Device Code
xx = 05, 10, 15, 20, 40, or 60
G = Pb−Free Package
KA = Diode Polarity

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 7 of this data sheet.

MAXIMUM RATINGS

Rating	Symbol	MUR/SUR8 805	810	815	820	840	860	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V_{RRM} V_{RWM} V_R	50	100	150	200	400	600	V
Average Rectified Forward Current Total Device, (Rated V_R), T_C = 150°C	$I_{F(AV)}$	8.0						A
Peak Repetitive Forward Current (Rated V_R, Square Wave, 20 kHz), T_C = 150°C	I_{FM}	16						A
Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz)	I_{FSM}	100						A
Operating Junction Temperature and Storage Temperature Range	T_J, T_{stg}	−65 to +175						°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Characteristic	Symbol	MUR/SUR8 805	810	815	820	840	860	Unit
Maximum Thermal Resistance, Junction−to−Case	$R_{\theta JC}$	3.0				2.0		°C/W
Thermal Resistance, Junction−to−Case MURF860	$R_{\theta JC}$	4.75						°C/W
Thermal Resistance, Junction−to−Ambient	$R_{\theta JA}$	73						°C/W
Thermal Resistance, Junction−to−Ambiente MURF860	$R_{\theta JA}$	75						°C/W

ELECTRICAL CHARACTERISTICS

Characteristic	Symbol	MUR/SUR8 805	810	815	820	840	860	Unit
Maximum Instantaneous Forward Voltage (Note 1) (i_F = 8.0 A, T_C = 150°C) (i_F = 8.0 A, T_C = 25°C)	v_F	0.895 0.975				1.00 1.30	1.20 1.50	V
Maximum Instantaneous Reverse Current (Note 1) (Rated DC Voltage, T_J = 150°C) (Rated DC Voltage, T_J = 25°C)	i_R	250 5.0				500 10		μA
Maximum Reverse Recovery Time (I_F = 1.0 A, di/dt = 50 A/μs) (I_F = 0.5 A, i_R = 1.0 A, I_{REC} = 0.25 A)	t_{rr}	35 25				60 50		ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Pulse Test: Pulse Width = 300 μs, Duty Cycle ≤ 2.0%.

MUR805G, MUR810G, MUR815G, MUR820G, SUR8820G



Figure 1. Typical Forward Voltage



Figure 2. Typical Reverse Current*

* The curves shown are typical for the highest voltage device in the grouping. Typical reverse current for lower voltage selections can be estimated from these same curves if V_R is sufficiently below rated V_R.



Figure 3. Current Derating, Case



Figure 4. Current Derating, Ambient



Figure 5. Power Dissipation



Figure 6. Typical Forward Voltage



Figure 7. Typical Reverse Current*

* The curves shown are typical for the highest voltage device in the grouping. Typical reverse current for lower voltage selections can be estimated from these same curves if V_R is sufficiently below rated V_R.



Figure 8. Current Derating, Case



Figure 9. Current Derating, Ambient



Figure 10. Power Dissipation

MUR860G, MURF860G



Figure 11. Typical Forward Voltage



Figure 12. Typical Reverse Current*

* The curves shown are typical for the highest voltage device in the grouping. Typical reverse current for lower voltage selections can be estimated from these same curves if V_R is sufficiently below rated V_R.



Figure 13. Current Derating, Case



Figure 14. Current Derating, Ambient



Figure 15. Power Dissipation



Figure 16. Typical Non−Repetitive Surge Current

* Typical performance based on a limited sample size. ON Semiconductor does not guarantee ratings not listed in the Maximum Ratings table.



Figure 17. Thermal Response



Figure 18. Thermal Response, (MURF860G) Junction−to−Case ($R_{\theta JC}$)



Figure 19. Thermal Response, (MURF860G) Junction−to−Ambient ($R_{\theta JA}$)



Figure 20. Typical Capacitance

ORDERING INFORMATION

Device	Package	Shipping
MUR805G	TO−220AC (Pb−Free)	50 Units / Rail
MUR810G	TO−220AC (Pb−Free)	50 Units / Rail
MUR815G	TO−220AC (Pb−Free)	50 Units / Rail
MUR820G	TO−220AC (Pb−Free)	50 Units / Rail
SUR8820G	TO−220AC (Pb−Free)	50 Units / Rail
MUR840G	TO−220AC (Pb−Free)	50 Units / Rail
SUR8840G	TO−220AC (Pb−Free)	50 Units / Rail
MUR860G	TO−220AC (Pb−Free)	50 Units / Rail
MURF860G	TO−220FP (Pb−Free)	50 Units / Rail

TO−220 FULLPACK, 2−LEAD
CASE 221AG
ISSUE B

DATE 27 AUG 2015



SCALE 1:1



TOP VIEW



SIDE VIEW



ALTERNATE CONSTRUCTION

SECTION D−D



SECTION A−A

NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. CONTOUR UNCONTROLLED IN THIS AREA.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH AND GATE PROTRUSIONS. MOLD FLASH AND GATE PROTRUSIONS NOT TO EXCEED 0.13 PER SIDE. THESE DIMENSIONS ARE TO BE MEASURED AT OUTERMOST EXTREME OF THE PLASTIC BODY.
5. DIMENSION b2 DOES NOT INCLUDE DAMBAR PROTRUSION. LEAD WIDTH INCLUDING PROTRUSION SHALL NOT EXCEED 2.00.

	MILLIMETERS	
DIM	MIN	MAX
A	4.30	4.70
A1	2.50	2.90
A2	2.50	2.90
b	0.54	0.84
b2	1.10	1.40
c	0.49	0.79
D	14.22	15.88
E	9.65	10.67
e	2.54 BSC	
e1	5.08 BSC	
H1	6.40	6.90
L	12.70	14.73
L1	---	2.80
P	3.00	3.40
Q	2.80	3.20

GENERIC MARKING DIAGRAM*



A = Assembly Location
WL = Wafer Lot
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “ ▪”, may or may not be present.

DOCUMENT NUMBER:	**98AON52563E**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**TO−220 FULLPACK, 2−LEAD**	**PAGE 1 OF 1**

MECHANICAL CASE OUTLINE
PACKAGE DIMENSIONS

ON Semiconductor®

TO−220, 2−LEAD
CASE 221B−04
ISSUE F

DATE 12 APR 2013



SCALE 1:1



NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
A	0.595	0.620	15.11	15.75
B	0.380	0.405	9.65	10.29
C	0.160	0.190	4.06	4.82
D	0.025	0.039	0.64	1.00
F	0.142	0.161	3.61	4.09
G	0.190	0.210	4.83	5.33
H	0.110	0.130	2.79	3.30
J	0.014	0.025	0.36	0.64
K	0.500	0.562	12.70	14.27
L	0.045	0.060	1.14	1.52
Q	0.100	0.120	2.54	3.04
R	0.080	0.110	2.04	2.79
S	0.045	0.055	1.14	1.39
T	0.235	0.255	5.97	6.48
U	0.000	0.050	0.000	1.27

STYLE 1:
PIN 1. CATHODE
2. N/A
3. ANODE
4. CATHODE

STYLE 2:
PIN 1. ANODE
2. N/A
3. CATHODE
4. ANODE

DOCUMENT NUMBER:	**98ASB42149B**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	**TO−220, 2−LEAD**		**PAGE 1 OF 1**

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT
North American Technical Support:
Voice Mail: 1 800−282−9855 Toll Free USA/Canada
Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:
Phone: 00421 33 790 2910
For additional information, please contact your local Sales Representative

◊