

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### **General Description**

The MAX481, MAX483, MAX485, MAX487–MAX491, and MAX1487 are low-power transceivers for RS-485 and RS-422 communication. Each part contains one driver and one receiver. The MAX483, MAX487, MAX488, and MAX489 feature reduced slew-rate drivers that minimize EMI and reduce reflections caused by improperly terminated cables, thus allowing error-free data transmission up to 250kbps. The driver slew rates of the MAX481, MAX485, MAX490, MAX491, and MAX1487 are not limited, allowing them to transmit up to 2.5Mbps.

These transceivers draw between  $120\mu$ A and  $500\mu$ A of supply current when unloaded or fully loaded with disabled drivers. Additionally, the MAX481, MAX483, and MAX487 have a low-current shutdown mode in which they consume only 0.1 $\mu$ A. All parts operate from a single 5V supply.

Drivers are short-circuit current limited and are protected against excessive power dissipation by thermal shutdown circuitry that places the driver outputs into a high-impedance state. The receiver input has a fail-safe feature that guarantees a logic-high output if the input is open circuit.

The MAX487 and MAX1487 feature quarter-unit-load receiver input impedance, allowing up to 128 MAX487/ MAX1487 transceivers on the bus. Full-duplex communications are obtained using the MAX488–MAX491, while the MAX481, MAX483, MAX485, MAX487, and MAX1487 are designed for half-duplex applications.

#### **Applications**

Low-Power RS-485 Transceivers Low-Power RS-422 Transceivers

Level Translators

Transceivers for EMI-Sensitive Applications

Industrial-Control Local Area Networks

#### Next Generation Device Features

- For Fault-Tolerant Applications MAX3430: ±80V Fault-Protected, Fail-Safe, 1/4 Unit Load, +3.3V, RS-485 Transceiver MAX3440E–MAX3444E: ±15kV ESD-Protected, ±60V Fault-Protected, 10Mbps, Fail-Safe, RS-485/J1708 Transceivers
- For Space-Constrained Applications MAX3460-MAX3464: +5V, Fail-Safe, 20Mbps, Profibus RS-485/RS-422 Transceivers MAX3362: +3.3V, High-Speed, RS-485/RS-422 Transceiver in a SOT23 Package MAX3280E-MAX3284E: ±15kV ESD-Protected, 52Mbps, +3V to +5.5V, SOT23, RS-485/RS-422, True Fail-Safe Receivers MAX3293/MAX3294/MAX3295: 20Mbps, +3.3V, SOT23, RS-485/RS-422 Transmitters
- For Multiple Transceiver Applications MAX3030E–MAX3033E: ±15kV ESD-Protected, +3.3V, Quad RS-422 Transmitters
- For Fail-Safe Applications MAX3080–MAX3089: Fail-Safe, High-Speed (10Mbps), Slew-Rate-Limited RS-485/RS-422 Transceivers
- For Low-Voltage Applications MAX3483E/MAX3485E/MAX3486E/MAX3488E/ MAX3490E/MAX3491E: +3.3V Powered, ±15kV ESD-Protected, 12Mbps, Slew-Rate-Limited, True RS-485/RS-422 Transceivers

Ordering Information appears at end of data sheet.

#### **Selection Table**

PART NUMBER	HALF/FULL DUPLEX	DATA RATE (Mbps)	SLEW-RATE LIMITED	LOW- POWER SHUTDOWN	RECEIVER/ DRIVER ENABLE	QUIESCENT CURRENT (µA)	NUMBER OF RECEIVERS ON BUS	PIN COUNT
MAX481	Half	2.5	No	Yes	Yes	300	32	8
MAX483	Half	0.25	Yes	Yes	Yes	120	32	8
MAX485	Half	2.5	No	No	Yes	300	32	8
MAX487	Half	0.25	Yes	Yes	Yes	120	128	8
MAX488	Full	0.25	Yes	No	No	120	32	8
MAX489	Full	0.25	Yes	No	Yes	120	32	14
MAX490	Full	2.5	No	No	No	300	32	8
MAX491	Full	2.5	No	No	Yes	300	32	14
MAX1487	Half	2.5	No	No	Yes	230	128	8

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at www.maximintegrated.com.

## Low-Power, Slew-Rate-Limited **RS-485/RS-422 Transceivers**

#### **ABSOLUTE MAXIMUM RATINGS**

Supply Voltage (V <sub>CC</sub> )	
Control Input Voltage (RE, DE)	
Driver Input Voltage (DI)	-0.5V to (V <sub>CC</sub> + 0.5V)
Driver Output Voltage (A, B)	8V to +12.5V
Receiver Input Voltage (A, B)	8V to +12.5V
Receiver Output Voltage (RO)	-0.5V to (V <sub>CC</sub> + 0.5V)
Continuous Power Dissipation (TA	= +70°C)

8-Pin Plastic DIP (derate 9.09mW/°C above +70°C) ....727mW 14-Pin Plastic DIP (derate 10.00mW/°C above +70°C) ..800mW 8-Pin SO (derate 5.88mW/°C above +70°C)......471mW

14-Pin SO (derate 8.33mW/°C above +70°C)667mW 8-Pin μMAX (derate 4.1mW/°C above +70°C)830mW 8-Pin CERDIP (derate 8.00mW/°C above +70°C)640mW
14-Pin CERDIP (derate 9.09mW/°C above +70°C)727mW
Operating Temperature Ranges
MAX4C/MAX1487C_A0°C to +70°C
MAX4E/MAX1487E_ A40°C to +85°C
MAX4M_/MAX1487MJA55°C to +125°C
Storage Temperature Range65°C to +160°C
Lead Temperature (soldering, 10sec)+300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### DC ELECTRICAL CHARACTERISTICS

(V<sub>CC</sub> = 5V  $\pm$ 5%, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted.) (Notes 1, 2)

PARAMETER	SYMBOL	CONDITIONS		MIN	ТҮР	MAX	UNITS
Differential Driver Output (no load)	Vod1					5	V
Differential Driver Output	VOD2	R = 50Ω (RS-422)		2			V
(with load)	VOD2	R = $27\Omega$ (RS-485), Figure 4		1.5		5	
Change in Magnitude of Driver Differential Output Voltage for Complementary Output States	ΔV <sub>OD</sub>	R = $27\Omega$ or $50\Omega$ , Figure 4				0.2	V
Driver Common-Mode Output Voltage	Voc	R = $27\Omega$ or $50\Omega$ , Figure 4				3	V
Change in Magnitude of Driver Common-Mode Output Voltage for Complementary Output States	ΔVod	R = $27\Omega$ or $50\Omega$ , Figure 4				0.2	V
Input High Voltage	Vih	DE, DI, RE		2.0			V
Input Low Voltage	VIL	DE, DI, RE				0.8	V
Input Current	lin1	DE, DI, RE	DE, DI, RE			±2	μA
	l <sub>IN2</sub>	$\begin{array}{l} DE = OV;\\ V_{CC} = OV \text{ or } 5.25V, \end{array}$	V <sub>IN</sub> = 12V			1.0	mA
Input Current (A, B)		all devices except MAX487/MAX1487	VIN = -7V			-0.8	
		MAX487/MAX1487,	$V_{IN} = 12V$			0.25	mA
		$DE = 0V, V_{CC} = 0V \text{ or } 5.25V$	$V_{IN} = -7V$			-0.2	
Receiver Differential Threshold Voltage	Vth	$-7V \le V_{CM} \le 12V$		-0.2		0.2	V
Receiver Input Hysteresis	Δντη	$V_{CM} = 0V$			70		mV
Receiver Output High Voltage	Voh	$I_{O} = -4mA, V_{ID} = 200mV$		3.5			V
Receiver Output Low Voltage	Vol	$I_{O} = 4mA$ , $V_{ID} = -200mV$				0.4	V
Three-State (high impedance) Output Current at Receiver	I <sub>OZR</sub>	$0.4V \le V_{O} \le 2.4V$				±1	μA
Receiver Input Resistance	RIN	-7V $\leq$ V <sub>CM</sub> $\leq$ 12V, all devices except MAX487/MAX1487		12			kΩ
		$-7V \le V_{CM} \le 12V, MAX487/MA$	48			kΩ	

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### DC ELECTRICAL CHARACTERISTICS (continued)

(V<sub>CC</sub> = 5V  $\pm$ 5%, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted.) (Notes 1, 2)

PARAMETER	SYMBOL	CONDITIONS			MIN	ТҮР	MAX	UNITS
		MAX488/MAX489, DE, DI, RE = 0V or V <sub>CC</sub>				120	250	
		MAX490/MAX491, DE, DI, RE = 0V or V <sub>CC</sub>				300	500	
No. Lood Currenty Current		MAX481/MAX485,	DE = V <sub>CC</sub>			500	900	
No-Load Supply Current (Note 3)	Icc	$\overline{RE} = 0V \text{ or } V_{CC}$	DE = 0V			300	500	μA
(		$\frac{MAX1487,}{RE} = 0V \text{ or } V_{CC}$	DE = V <sub>CC</sub>			300	500	
			DE = 0V			230	400	
		$\frac{MAX483/MAX487}{RE} = 0V \text{ or } V_{CC}$	DE = 5V	MAX483		350	650	
			DE = 5V	MAX487		250	400	
			DE = 0V			120	250	
Supply Current in Shutdown	ISHDN	MAX481/483/487, DE	$=$ 0V, $\overline{RE} = V$	'cc		0.1	10	μA
Driver Short-Circuit Current, $V_O = High$	IOSD1	$-7V \le V_0 \le 12V$ (Note 4)			35		250	mA
Driver Short-Circuit Current, $V_O = Low$	IOSD2	$-7V \le V_O \le 12V$ (Note 4)			35		250	mA
Receiver Short-Circuit Current	IOSR	$0V \le V_O \le V_{CC}$			7		95	mA

#### SWITCHING CHARACTERISTICS—MAX481/MAX485, MAX490/MAX491, MAX1487

 $(V_{CC} = 5V \pm 5\%, T_A = T_{MIN}$  to  $T_{MAX}$ , unless otherwise noted.) (Notes 1, 2)

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
Driver Input to Output	t <sub>PLH</sub>	Figures 6 and 8, R	Figures 6 and 8, RDIFF = $54\Omega$ ,		30	60	ns
Driver input to Output	<b>t</b> PHL	$C_{L1} = C_{L2} = 100 pF$	-	10	30	60	115
Driver Output Skew to Output	tskew	Figures 6 and 8, RD	IFF = $54\Omega$ , CL1 = CL2 = 100pF		5	10	ns
		Figures 6 and 8,	MAX481, MAX485, MAX1487	3	15	40	
Driver Rise or Fall Time	tR, tF	$R_{DIFF} = 54\Omega$ ,	MAX490C/E, MAX491C/E	5	15	25	ns
		$C_{L1} = C_{L2} = 100 pF$	MAX490M, MAX491M	3	15	40	
Driver Enable to Output High	tzh	Figures 7 and 9, C	L = 100pF, S2 closed		40	70	ns
Driver Enable to Output Low	tzl	Figures 7 and 9, C	L = 100pF, S1 closed		40	70	ns
Driver Disable Time from Low	tLZ	Figures 7 and 9, C	L = 15pF, S1 closed		40	70	ns
Driver Disable Time from High	t <sub>HZ</sub>	Figures 7 and 9, C	L = 15pF, S2 closed		40	70	ns
	tplh, tphl	Figures 6 and 10,	MAX481, MAX485, MAX1487	20	90	200	
Receiver Input to Output			MAX490C/E, MAX491C/E	20	90	150	ns
			MAX490M, MAX491M	20	90	200	
l tpLH - tpHL l Differential Receiver Skew	tskd	Figures 6 and 10, $I C_{L1} = C_{L2} = 100 p F$			13		ns
Receiver Enable to Output Low	tzl	Figures 5 and 11, (	C <sub>RL</sub> = 15pF, S1 closed		20	50	ns
Receiver Enable to Output High	tzH	Figures 5 and 11, (	C <sub>RL</sub> = 15pF, S2 closed		20	50	ns
Receiver Disable Time from Low	tLZ	Figures 5 and 11, C <sub>RL</sub> = 15pF, S1 closed			20	50	ns
Receiver Disable Time from High	t <sub>HZ</sub>	Figures 5 and 11, C <sub>RL</sub> = 15pF, S2 closed			20	50	ns
Maximum Data Rate	fmax			2.5			Mbps
Time to Shutdown	<b>t</b> SHDN	MAX481 (Note 5)		50	200	600	ns

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### SWITCHING CHARACTERISTICS—MAX481/MAX485, MAX490/MAX491, MAX1487 (continued)

(V\_CC = 5V  $\pm$ 5%, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted.) (Notes 1, 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	MAX	UNITS
Driver Enable from Shutdown to Output High (MAX481)	tzh(SHDN)	Figures 7 and 9, $C_L$ = 100pF, S2 closed		40	100	ns
Driver Enable from Shutdown to Output Low (MAX481)	tzl(SHDN)	Figures 7 and 9, $C_L = 100pF$ , S1 closed		40	100	ns
Receiver Enable from Shutdown to Output High (MAX481)	tzh(shdn)	Figures 5 and 11, $C_L$ = 15pF, S2 closed, A - B = 2V		300	1000	ns
Receiver Enable from Shutdown to Output Low (MAX481)	tzl(SHDN)	Figures 5 and 11, $C_L$ = 15pF, S1 closed, B - A = 2V		300	1000	ns

#### SWITCHING CHARACTERISTICS—MAX483, MAX487/MAX488/MAX489

 $(V_{CC} = 5V \pm 5\%, T_A = T_{MIN}$  to  $T_{MAX}$ , unless otherwise noted.) (Notes 1, 2)


PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Driver Input to Output	t <sub>PLH</sub>	Figures 6 and 8, $R_{DIFF} = 54\Omega$ ,	250	800	2000	20
Driver input to Output	<b>t</b> PHL	$C_{L1} = C_{L2} = 100 pF$	250	800	2000	ns
Driver Output Skew to Output	<b>t</b> SKEW	Figures 6 and 8, $R_{DIFF} = 54\Omega$ , $C_{L1} = C_{L2} = 100 pF$		100	800	ns
Driver Rise or Fall Time	t <sub>R</sub> , t <sub>F</sub>	Figures 6 and 8, $R_{DIFF} = 54\Omega$ , $C_{L1} = C_{L2} = 100 pF$	250		2000	ns
Driver Enable to Output High	tzH	Figures 7 and 9, $C_L$ = 100pF, S2 closed	250		2000	ns
Driver Enable to Output Low	tzl	Figures 7 and 9, $C_L$ = 100pF, S1 closed	250		2000	ns
Driver Disable Time from Low	t <sub>LZ</sub>	Figures 7 and 9, $C_L = 15 pF$ , S1 closed	300		3000	ns
Driver Disable Time from High	t <sub>HZ</sub>	Figures 7 and 9, $C_L = 15 pF$ , S2 closed	300		3000	ns
	t <sub>PLH</sub>	Figures 6 and 10, $R_{DIFF} = 54\Omega$ ,	250		2000	50
Receiver Input to Output	t <sub>PHL</sub>	$C_{L1} = C_{L2} = 100 pF$	250		2000	ns
l t <sub>PLH</sub> - t <sub>PHL</sub> l Differential Receiver Skew	tskd	Figures 6 and 10, $R_{DIFF} = 54\Omega$ , $C_{L1} = C_{L2} = 100 pF$		100		ns
Receiver Enable to Output Low	tzL	Figures 5 and 11, C <sub>RL</sub> = 15pF, S1 closed		20	50	ns
Receiver Enable to Output High	tzн	Figures 5 and 11, C <sub>RL</sub> = 15pF, S2 closed		20	50	ns
Receiver Disable Time from Low	t <sub>LZ</sub>	Figures 5 and 11, $C_{RL}$ = 15pF, S1 closed		20	50	ns
Receiver Disable Time from High	tHZ	Figures 5 and 11, C <sub>RL</sub> = 15pF, S2 closed		20	50	ns
Maximum Data Rate	fMAX	tPLH, tPHL < 50% of data period	250			kbps
Time to Shutdown	tshdn	MAX483/MAX487 (Note 5)	50	200	600	ns
Driver Enable from Shutdown to Output High	tzh(shdn)	MAX483/MAX487, Figures 7 and 9, $C_L = 100pF$ , S2 closed			2000	ns
Driver Enable from Shutdown to Output Low	tzl(SHDN)	MAX483/MAX487, Figures 7 and 9, $C_L = 100 pF$ , S1 closed			2000	ns
Receiver Enable from Shutdown to Output High	tzh(shdn)	MAX483/MAX487, Figures 5 and 11, $C_L = 15pF$ , S2 closed			2500	ns
Receiver Enable from Shutdown to Output Low	tzl(SHDN)	MAX483/MAX487, Figures 5 and 11, $C_L = 15pF$ , S1 closed			2500	ns

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### NOTES FOR ELECTRICAL/SWITCHING CHARACTERISTICS

- **Note 1:** All currents into device pins are positive; all currents out of device pins are negative. All voltages are referenced to device ground unless otherwise specified.
- Note 2: All typical specifications are given for  $V_{CC} = 5V$  and  $T_A = +25^{\circ}C$ .
- Note 3: Supply current specification is valid for loaded transmitters when DE = 0V.
- Note 4: Applies to peak current. See Typical Operating Characteristics.
- Note 5: The MAX481/MAX483/MAX487 are put into shutdown by bringing RE high and DE low. If the inputs are in this state for less than 50ns, the parts are guaranteed not to enter shutdown. If the inputs are in this state for at least 600ns, the parts are guaranteed to have entered shutdown. See *Low-Power Shutdown Mode (MAX481/MAX483/MAX487)* section.

#### **Typical Operating Characteristics**



# \AX481/MAX483/MAX485/MAX487-MAX491/MAX148

## Low-Power, Slew-Rate-Limited **RS-485/RS-422** Transceivers

MAX483/MAX487; DE =  $\overline{\text{RE}}$  = 0, MAX488/MAX489; DE =  $\overline{\text{RE}}$  = X

MAX483/MAX487; DE = 0, RE = V<sub>CC</sub>

0 25 50 TEMPERATURE (°C)

75 100 125

200

100

0

-50 -25

#### **Typical Operating Characteristics (continued)** $(V_{CC} = 5V, T_A = +25^{\circ}C, unless otherwise noted.)$ **OUTPUT CURRENT** vs. **OUTPUT CURRENT** vs. MAX481/MAX485/MAX490/MAX491 **DRIVER OUTPUT HIGH VOLTAGE SUPPLY CURRENT vs. TEMPERATURE DRIVER OUTPUT LOW VOLTAGE** 140 -120 600 MAX481/MAX485; DE = V<sub>CC</sub>, RE = X 120 -100 500 SUPPLY CURRENT (µA) 100 OUTPUT CURRENT (mA) -80 400 80 -60 300 60 MAX485; DE = 0, $\overline{RE} = X$ , MAX481; $DE = \overline{RE} = 0$ MAX490/MAX491; $DE = \overline{RE} = X$ -40 200 40 -20 100 20 MAX481; DE = 0, $\overline{RE} = V_{CC}$ 0 0 0 -7 -6 -5 -4 -3 -2 -1 0 1 4 5 0 2 4 6 8 10 12 2 3 -50 -25 0 50 75 100 125 25 OUTPUT LOW VOLTAGE (V) OUTPUT HIGH VOLTAGE (V) TEMPERATURE (°C) MAX483/MAX487-MAX489 **MAX1487 SUPPLY CURRENT vs. TEMPERATURE SUPPLY CURRENT vs. TEMPERATURE** 600 600 500 500 SUPPLY CURRENT (µA) SUPPLY CURRENT (µA) 400 400 MAX483; $DE = V_{CC}$ , $\overline{RE} = X$ //AX1487; DE = V<sub>GC</sub>, RE = X 300 300 MAX487; DE = $V_{CC}$ , $\overline{RE}$ = X

200

100

0

-60 -40 -20

MAX1487 DF =  $0V \overline{BF} = X$ 

0 20 40 60 80 100 120 140

TEMPERATURE (°C)

MAX481/MAX483/MAX485/MAX487–MAX491/MAX1487

OUTPUT CURRENT (mA)

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### Pin Description

		PIN				
MAX485/	IAX481/MAX483/ IAX485/MAX487/ MAX1487		(488/ (490			FUNCTION
DIP/SO	μΜΑΧ	DIP/SO	μΜΑΧ	DIP/SO		
1	3	2	4	2	RO	Receiver Output: If A > B by 200mV, RO will be high; If A < B by 200mV, RO will be low.
2	4			3	RE	Receiver Output Enable. RO is enabled when $\overline{\text{RE}}$ is low; RO is high impedance when $\overline{\text{RE}}$ is high.
3	5	_	_	4	DE	Driver Output Enable. The driver outputs, Y and Z, are enabled by bringing DE high. They are high impedance when DE is low. If the driver outputs are enabled, the parts function as line drivers. While they are high impedance, they function as line receivers if $\overline{\text{RE}}$ is low.
4	6	3	5	5	DI	Driver Input. A low on DI forces output Y low and output Z high. Similarly, a high on DI forces output Y high and output Z low.
5	7	4	6	6, 7	GND	Ground
	_	5	7	9	Y	Noninverting Driver Output
		6	8	10	Z	Inverting Driver Output
6	8				А	Noninverting Receiver Input and Noninverting Driver Output
		8	2	12	А	Noninverting Receiver Input
7	1			_	В	Inverting Receiver Input and Inverting Driver Output
	_	7	1	11	В	Inverting Receiver Input
8	2	1	3	14	Vcc	Positive Supply: $4.75V \le V_{CC} \le 5.25V$
				1, 8, 13	N.C.	No Connect—not internally connected




Figure 1. MAX481/MAX483/MAX485/MAX487/MAX1487 Pin Configuration and Typical Operating Circuit

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers




Figure 2. MAX488/MAX490 Pin Configuration and Typical Operating Circuit




Figure 3. MAX489/MAX491 Pin Configuration and Typical Operating Circuit

#### **Applications Information**

The MAX481/MAX483/MAX485/MAX487–MAX491 and MAX1487 are low-power transceivers for RS-485 and RS-422 communications. The MAX481, MAX485, MAX490, MAX491, and MAX1487 can transmit and receive at data rates up to 2.5Mbps, while the MAX483, MAX487, MAX488, and MAX489 are specified for data rates up to 250kbps. The MAX489–MAX491 are full-duplex transceivers while the MAX481, MAX483, MAX485, MAX487, and MAX1487 are half-duplex. In addition, Driver Enable (DE) and Receiver Enable (RE) pins are included on the MAX481, MAX483, MAX487, MAX481, MAX483, MAX487, MAX481, MAX

#### MAX487/MAX1487: 128 Transceivers on the Bus

The 48k $\Omega$ , 1/<sub>4</sub>-unit-load receiver input impedance of the MAX487 and MAX1487 allows up to 128 transceivers on a bus, compared to the 1-unit load (12k $\Omega$  input impedance) of standard RS-485 drivers (32 transceivers maximum). Any combination of MAX487/MAX1487 and other RS-485 transceivers with a total of 32 unit loads or less can be put on the bus. The MAX481/MAX483/MAX485 and MAX488–MAX491 have standard 12k $\Omega$  Receiver Input impedance.

#### Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### **Test Circuits**




Figure 4. Driver DC Test Load




Figure 6. Driver/Receiver Timing Test Circuit



The MAX483 and MAX487–MAX489 are slew-rate limited, minimizing EMI and reducing reflections caused by improperly terminated cables. Figure 12 shows the driver output waveform and its Fourier analysis of a 150kHz signal transmitted by a MAX481, MAX485, MAX490, MAX491, or MAX1487. High-frequency har-




Figure 5. Receiver Timing Test Load




Figure 7. Driver Timing Test Load

monics with large amplitudes are evident. Figure 13 shows the same information displayed for a MAX483, MAX487, MAX488, or MAX489 transmitting under the same conditions. Figure 13's high-frequency harmonics have much lower amplitudes, and the potential for EMI is significantly reduced.

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers






Figure 8. Driver Propagation Delays








Figure 9. Driver Enable and Disable Times (except MAX488 and MAX490)




Figure 11. Receiver Enable and Disable Times (except MAX488 and MAX490)

#### Function Tables (MAX481/MAX483/MAX485/MAX487/MAX1487)

#### Table 1. Transmitting

	INPUTS	OUTPUTS		
RE	DE	DI	z	Y
Х	1	1	0	1
Х	1	0	1	0
0	0	Х	High-Z	High-Z
1	0	х	High-Z*	High-Z*

X = Don't care

High-Z = High impedance

\*Shutdown mode for MAX481/MAX483/MAX487

#### Table 2. Receiving

	OUTPUT		
RE	DE	A-B	RO
0	0	≥ +0.2V	1
0	0	≤ -0.2V	0
0	0	Inputs open	1
1	0	Х	High-Z*

X = Don't care

*High-Z = High impedance* 

\*Shutdown mode for MAX481/MAX483/MAX487

#### \_Switching Waveforms

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers




Figure 12. Driver Output Waveform and FFT Plot of MAX481/ MAX485/MAX490/MAX491/MAX1487 Transmitting a 150kHz Signal

#### Low-Power Shutdown Mode (MAX481/MAX483/MAX487)

A low-power shutdown mode is initiated by bringing both  $\overline{RE}$  high and DE low. The devices will not shut down unless both the driver and receiver are disabled. In shutdown, the devices typically draw only 0.1µA of supply current.

 $\overline{\text{RE}}$  and DE may be driven simultaneously; the parts are guaranteed not to enter shutdown if  $\overline{\text{RE}}$  is high and DE is low for less than 50ns. If the inputs are in this state for at least 600ns, the parts are guaranteed to enter shutdown.

For the MAX481, MAX483, and MAX487, the t<sub>ZH</sub> and t<sub>ZL</sub> enable times assume the part was not in the low-power shutdown state (the MAX485/MAX488–MAX491 and MAX1487 can not be shut down). The t<sub>ZH(SHDN)</sub> and t<sub>ZL(SHDN)</sub> enable times assume the parts were shut down (see *Electrical Characteristics*).

It takes the drivers and receivers longer to become enabled from the low-power shutdown state (tZH(SHDN), tZL(SHDN)) than from the operating mode (tZH, tZL). (The parts are in operating mode if the  $\overline{RE}$ , DE inputs equal a logical 0,1 or 1,1 or 0, 0.)




Figure 13. Driver Output Waveform and FFT Plot of MAX483/ MAX487–MAX489 Transmitting a 150kHz Signal

#### **Driver Output Protection**

Excessive output current and power dissipation caused by faults or by bus contention are prevented by two mechanisms. A foldback current limit on the output stage provides immediate protection against short circuits over the whole common-mode voltage range (see *Typical Operating Characteristics*). In addition, a thermal shutdown circuit forces the driver outputs into a high-impedance state if the die temperature rises excessively.

#### **Propagation Delay**

Many digital encoding schemes depend on the difference between the driver and receiver propagation delay times. Typical propagation delays are shown in Figures 15–18 using Figure 14's test circuit.

The difference in receiver delay times, I tPLH - tPHL I, is typically under 13ns for the MAX481, MAX485, MAX490, MAX491, and MAX1487 and is typically less than 100ns for the MAX483 and MAX487–MAX489.

The driver skew times are typically 5ns (10ns max) for the MAX481, MAX485, MAX490, MAX491, and MAX1487, and are typically 100ns (800ns max) for the MAX483 and MAX487–MAX489.

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers




Figure 14. Receiver Propagation Delay Test Circuit




Figure 15. MAX481/MAX485/MAX490/MAX491/MAX1487 Receiver tPHL




Figure 17. MAX483, MAX487–MAX489 Receiver tPHL




Figure 16. MAX481/MAX485/MAX490/MAX491/MAX1487 Receiver tPLH




Figure 18. MAX483, MAX487–MAX489 Receiver tPLH

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### Line Length vs. Data Rate

The RS-485/RS-422 standard covers line lengths up to 4000 feet. For line lengths greater than 4000 feet, see Figure 23.

Figures 19 and 20 show the system differential voltage for the parts driving 4000 feet of 26AWG twisted-pair wire at 110kHz into  $120\Omega$  loads.

#### **Typical Applications**

The MAX481, MAX483, MAX485, MAX487–MAX491, and MAX1487 transceivers are designed for bidirectional data communications on multipoint bus transmission lines.




Figure 19. MAX481/MAX485/MAX490/MAX491/MAX1487 System Differential Voltage at 110kHz Driving 4000ft of Cable

Figures 21 and 22 show typical network applications circuits. These parts can also be used as line repeaters, with cable lengths longer than 4000 feet, as shown in Figure 23.

To minimize reflections, the line should be terminated at both ends in its characteristic impedance, and stub lengths off the main line should be kept as short as possible. The slew-rate-limited MAX483 and MAX487–MAX489 are more tolerant of imperfect termination.




Figure 20. MAX483, MAX487–MAX489 System Differential Voltage at 110kHz Driving 4000ft of Cable




Figure 21. MAX481/MAX483/MAX485/MAX487/MAX1487 Typical Half-Duplex RS-485 Network

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers




Figure 22. MAX488–MAX491 Full-Duplex RS-485 Network




Figure 23. Line Repeater for MAX488–MAX491

#### **Isolated RS-485**

For isolated RS-485 applications, see the MAX253 and MAX1480 data sheets.

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### **Ordering Information**

PART	TEMP RANGE	PIN-PACKAGE
MAX481CPA	0°C to +70°C	8 Plastic DIP
MAX481CSA	0°C to +70°C	8 SO
MAX481CUA	0°C to +70°C	8 µMAX
MAX481C/D	0°C to +70°C	Dice*
MAX481EPA	-40°C to +85°C	8 Plastic DIP
MAX481ESA	-40°C to +85°C	8 SO
MAX481MJA	-55°C to +125°C	8 CERDIP
MAX483CPA	0°C to +70°C	8 Plastic DIP
MAX483CSA	0°C to +70°C	8 SO
MAX483CUA	0°C to +70°C	8 µMAX
MAX483C/D	0°C to +70°C	Dice*
MAX483EPA	-40°C to +85°C	8 Plastic DIP
MAX483ESA	-40°C to +85°C	8 SO
MAX483MJA	-55°C to +125°C	8 CERDIP
MAX485CPA	0°C to +70°C	8 Plastic DIP
MAX485CSA	0°C to +70°C	8 SO
MAX485CUA	0°C to +70°C	8 μΜΑΧ
MAX485C/D	0°C to +70°C	Dice*
MAX485EPA	-40°C to +85°C	8 Plastic DIP
MAX485ESA	-40°C to +85°C	8 SO
MAX485MJA	-55°C to +125°C	8 CERDIP
MAX487CPA	0°C to +70°C	8 Plastic DIP
MAX487CSA	0°C to +70°C	8 SO
MAX487CUA	0°C to +70°C	8 µMAX
MAX487C/D	0°C to +70°C	Dice*
MAX487EPA	-40°C to +85°C	8 Plastic DIP
MAX487ESA	-40°C to +85°C	8 SO
MAX487MJA	-55°C to +125°C	8 CERDIP
MAX488CPA	0°C to +70°C	8 Plastic DIP
MAX488CSA	0°C to +70°C	8 SO
MAX488CUA	0°C to +70°C	8 µMAX
MAX488C/D	0°C to +70°C	Dice*
MAX488EPA	-40°C to +85°C	8 Plastic DIP
MAX488ESA	-40°C to +85°C	8 SO
MAX488MJA	-55°C to +125°C	8 CERDIP
MAX489CPD	0°C to +70°C	14 Plastic DIP
MAX489CSD	0°C to +70°C	14 SO
MAX489C/D	0°C to +70°C	
MAX489EPD	-40°C to +85°C	14 Plastic DIP
MAX489ESD	-40°C to +85°C	14 SO
MAX489MJD	-55°C to +125°C	14 CERDIP

#### **Ordering Information (continued)**

PART	TEMP RANGE	PIN-PACKAGE
MAX490CPA	0°C to +70°C	8 Plastic DIP
MAX490CSA	0°C to +70°C	8 SO
MAX490CUA	0°C to +70°C	8 μΜΑΧ
MAX490C/D	0°C to +70°C	Dice*
MAX490EPA	-40°C to +85°C	8 Plastic DIP
MAX490ESA	-40°C to +85°C	8 SO
MAX490MJA	-55°C to +125°C	8 CERDIP
MAX491CPD	0°C to +70°C	14 Plastic DIP
MAX491CSD	0°C to +70°C	14 SO
MAX491C/D	0°C to +70°C	Dice*
MAX491EPD	-40°C to +85°C	14 Plastic DIP
MAX491ESD	-40°C to +85°C	14 SO
MAX491MJD	-55°C to +125°C	14 CERDIP
MAX491MSD/PR	-55°C to +125°C	14 CERDIP
MAX491MSD/PR-T	-55°C to +125°C	14 CERDIP
<b>MAX1487</b> CPA	0°C to +70°C	8 Plastic DIP
MAX1487CSA	0°C to +70°C	8 SO
MAX1487CUA	0°C to +70°C	8 µMAX
MAX1487C/D	0°C to +70°C	Dice*
MAX1487EPA	-40°C to +85°C	8 Plastic DIP
MAX1487ESA	-40°C to +85°C	8 SO
MAX1487MJA	-55°C to +125°C	8 CERDIP

\*Contact factory for dice specifications.

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### **Package Information**

For the latest package outline information and land patterns, go to <u>www.maximintegrated.com/packages</u>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	OUTLINE NO.	LAND PATTERN NO.
8 PDIP	P8-1	<u>21-0043</u>	_
8 SO	S8-2	<u>21-0041</u>	<u>90-0096</u>
8 µMAX	U8-1	<u>21-0036</u>	<u>90-0092</u>
8 CERDIP	J8-2	<u>21-0045</u>	_
14 PDIP	P14-3	<u>21-0043</u>	_
14 SO	S14-1	<u>21-0041</u>	<u>90-0112</u>
14 CERDIP	J14-3	<u>21-0045</u>	—

## Low-Power, Slew-Rate-Limited RS-485/RS-422 Transceivers

#### **Revision History**

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	1/93	Initial release.	
9	9/09	Changed column name in Selection Table to "Number of Receivers on Bus."	1
10	9/14	Added MAX491MSD/PR and MAX491MSD/PR-T to data sheet. Updated <i>Absolute Maximum Ratings</i> .	2, 15



Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.

#### Maxim Integrated 160 Rio Robles, San Jose, CA 95134 USA 1-408-601-1000

© 2014 Maxim Integrated Products, Inc.

Maxim Integrated and the Maxim Integrated logo are trademarks of Maxim Integrated Products, Inc.

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Analog Devices Inc.:

MAX487CPA+ MAX487CSA+ MAX487CUA+ MAX487EPA+ MAX487ESA+ MAX487CSA+T MAX487CUA+T MAX487ESA+T MAX487MJA