



NOTES:

1. METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 and A2
5. UL APPROVED UNDER E228329
6. CONNECTOR IS PART MARKED: 3007W2PCM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					tolerance	dim. in mm	scale: 2:1 (5:1)			
					date		name	material: SEE NOTES		
					drawn	08.05.02	title:			
					appd.	08.05.02	D-SUB COMBINATION MALE			
					norm		7W2P SOLDER CUP			
					3 x c	Ä3935	15.03.2011	K.H.	d-old	dwg no: Inventor 10
				1 x b	Ä3231	19.12.2008	Lehmen		13K1A562	sh: 1
				a	Origin					
				rev.	description	date	name			part no: 3007W2PCM99A10X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[3007W2PCM99A10X](#)