



FL Series Quartz Crystal Legacy NKS3 Series 3.2 x 2.5mm

# Miniature Quartz Crystal Ceramic SMD



3.2 x 2.5mm Ceramic SMD

# **Product Description**

The 4-pad FL series seam seal devices incorporate a sub-miniature AT-cut crystal resonator housed in a standard 3.2 x 2.5mm ceramic package.

These compact crystals are ideal for surface mounting in densely populated or small formfactor PCB applications.


## **Product Features**


- Rugged AT-cut crystal construction
- Miniature 3.2 x 2.5mm ceramic package
- Available on tape & reel; 8mm tape, 3000 units per reel
- Pb-free and RoHS/Green compliant


# **Typical Applications**

- GSM, CDMA, GPRS
- PCMCIA Cards
- Portable / hand-held PCs
- Notebook PC
- HDD
- GPS
- Bluetooth
- Wireless LAN
- UWB
- ZigBee
- Digital Tuner

## Package: (Scale: none; dimensions are in mm)








# **Pin Functions:**

1 2 0.9 0.9 0.7 0.7 0.7 0.1	<del> </del>	.2
4 3	1	0.9
	P777777777	0.7
V/ U.1	4	3 0.1

Function
Xtal
Case
Xtal
Case

### **Part Ordering Information:**



Following the above format, Saronix-eCera part numbers will be assigned upon confirmation of exact customer requirements.

© Diodes Incorporated

• US: +1-408-232-9100 TW: +886-3-4518888 • www.diodes.com



A product Line of Diodes Incorporated PERICOM\*

FL Series Quartz Crystal Legacy NKS3 Series | 3.2 x 2.5mm

#### **Frequency Range:**

• 8 MHz to 66.0000 MHz (Fundamental)

# Characteristics at 25°C ±2°C:

- Frequency Calibration Tolerance: ±10ppm, ±20ppm, or ±30ppm
- Load Capacitance: 8 to 32pF or Series Resonance
- Effective Series Resistance (ESR):

 $500\Omega$  max (8 to 11.9 MHz)

 $80\Omega$  max (12 to 19.9 MHz)

 $60\Omega$  max (20 to 29.9 MHz)

 $40\Omega$  max (30 to 66 MHz)

- Drive Level:  $10\mu W$  typ.  $(100\mu W \text{ max})$
- Shunt Capacitance: 5pF Max

## **Temperature Range:**

- Operating: -20 to  $+70^{\circ}\text{C}$  or -40 to  $+85^{\circ}\text{C}$  or -40 to  $+125^{\circ}\text{C}$
- Storage: -55 to +125°C

## **Temperature Stability:**

- ±10ppm, ±20ppm, ±30ppm, or ±50ppm (–20 to +70°C)
- $\pm 30$ ppm, or  $\pm 50$ ppm (-40 to +85°C)
- ±50ppm, or ±70ppm (-40 to 125°C)

#### Aging at 25°C, First Year:

• ±3ppm Max

#### **Reflow Temperature:**

• 260°C Max, 10 seconds Max

#### Mechanical

•Shock: JESD22-B104 Condition B

•Solderability: J-STD-002

Terminal Strength: MIL-STD-883 Method 2004

•Vibration: JESD22-B103

Solvent Resistance: JESD22-B107

• Resistance to Soldering Heat: J-STD-020C Table 5-2 Pb-free devices (3 cycles max)

#### **Environmental**


• Gross Test Leak: JESD22-A109, Condition C

• Fine Test Leak: JESD22-A109, Condition A1

Moisture Resistance: JESD22-A113

•Insulation Resistance: 500 MΩ min (100 VDC)

# **Legacy Ordering Information - For Reference Only:**



Part Number Example:

 $Spec: Freq\ 18.1234MHz,\ \pm 30ppm\ calib,\ \pm 30ppm\ stab,\ -20\ to\ +70^{\circ}C,\ 16pF,\ T\&R\ =\ NKS3NAD1-18.1234-16(T)$ 

© Diodes Incorporated • US: +1-408-232-9100 TW: +886-3-4518888

www.diodes.com