



NC4MBV

4 pole male XLR receptacle, grounding: separate ground contact to mating connector shell and front panel, vertical PCB mount

Same as A series with exception of a metal mounting flange featuring continuous circumferential ground contact to chassis for best EMC practice.

Features & Benefits

- Smallest XLR receptacles, highest packing density
 - Metal mounting flange featuring continuous circumferential ground contact to chassis for best EMC and RF protection
-
- Housing flammability UL 94 V-0

Technical Information

Product	
Title	NC4MBV
Connection Type	XLR
Gender	male

Electrical	
Capacitance between contacts	$\leq 7 \text{ pF}$
Contact resistance	$\leq 6 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	6 A
Rated voltage	$< 50 \text{ V}$
Grounding Options	Separate ground contact connected to mating connector shell and front panel, no connection to Pin 1

Mechanical	
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	
Wiring	vertical PCB mount
Locking device	Latch lock
Mounting direction	Rear mounting
Chassis shape	B
Mounting	A-Screw

Material	
Contacts	Brass (CuZn35Pb2)
Insert	Polyamide (PA66)
Locking element	Steel Ck67
Ring	Zinc diecast (ZnAl4Cu1)
Flange	Metal

Environmental	
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C