



## NC4MXX-B

4 pole male cable connector with black metal housing and gold contacts.

The next generation of the worldwide accepted standard of XLR cable connectors. The successor of the X series offers several new features which make it more reliable, easier to assemble and improves contact integrity as well cable strain relief.

### Features & Benefits

- Male connector with improved locking recess without "window", more stringent housing increases durability
- Boot with polyurethane gland gives high protection to cable bending stresses
- Sleek and ergonomic design - valuable and handy
- Internal thread on shell is well protected against any damage
- Improved chuck type strain relief provides higher pull-out force and makes assembly easier and faster
- Colored rings and boots available for coding or identification
- Rugged zinc diecast shell, long lasting and dependable

**Technical Information**

Product	
Title	NC4MXX-B
Connection Type	XLR
Gender	male

Electrical	
Capacitance between contacts	$\leq 7$ pF
Contact resistance	$\leq 3$ m $\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10$ G $\Omega$ (initial)
Rated current per contact	10 A
Rated voltage	$< 50$ V

Mechanical	
Cable O.D.	3.5 - 8.0 mm
Insertion force	$\leq 20$ N
Withdrawal force	$\leq 20$ N
Lifetime	$> 1000$ mating cycles
Wiresize	max. 1.5 mm <sup>2</sup>
Wiresize	max. 16 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
<b>Boot</b>	Polyurethan
<b>Contacts</b>	Brass (CuZn39Pb3)
<b>Insert</b>	Polyamide (PA66)
<b>Locking element</b>	Zinc diecast (ZnAl4Cu1)
<b>Shell</b>	Zinc diecast (ZnAl4Cu1)
<b>Shell plating</b>	Black chromium
<b>Strain relief</b>	Polyacetal (POM)

Environmental	
<b>Flammability</b>	UL 94 V-0
<b>Standard compliance</b>	IEC 61076-2-103
<b>Protection class</b>	IP 40
<b>Solderability</b>	Complies with IEC 68-2-20
<b>Temperature range</b>	-30 °C to +80 °C