





WINSLOW ADAPTICs

Data Sheet QFN to PGA Generic Adapters


These adapters allow the prototyping of QFN, DFN and UTDFN devices on a 2.54mm pitch development board.

The top of the adapter has surface mount pads to which the surface mount device can be soldered.

The underside of the adapter has male PGA pins on 2.54mm pitch. These can either be soldered into a PCB or mated with any standard PGA socket.



Exploded View



Adapter Dimension Table

Part Number	Body Size	Number of Pins	A	B	C (lead pitch)	D	E	D1	E1	F	G
WA13062DQAET	3 x 3	4(2x2)	7.62	7.62	0.4mm	3.75	1.65	3.75	1.65	1.25	1.25
WA13041DQAET		6(3x2)	7.62	7.62	0.4mm	1.40	0.20	1.40	0.20	NP*	NP*
WA13028DQAET		8(4x2)	10.16	7.62	1.27mm	6.85	3.85	6.85	3.85	NP*	NP*
WA13082DQAET	2 x 2	8	7.62	7.62	0.5mm	2.80	1.20	2.80	1.20	0.80	0.80
WA13088DQAET	3 x 3	8	7.62	7.62	0.65mm	3.80	2.20	3.80	2.20	1.80	1.80
WA13024DQAET	3 x 3	8	7.62	7.62	0.8mm	4.55	2.65	4.55	2.65	NP*	NP*
WA13063DQAET	4 x 5	10	10.16	12.7	0.8mm	4.85	2.75	5.85	3.75	2.30	3.30
WA13046DQAET	4 x 4	12	10.16	10.16	0.8mm	4.85	2.75	4.85	2.75	2.25	2.25
WA13083DQAET	3 x 3	12	10.16	10.16	0.5mm	3.80	2.20	3.80	2.20	1.80	1.80
WA13084DQAET	4 x 4	12	10.16	10.16	0.65mm	4.80	3.20	4.80	3.20	2.8	2.8
WA13064DQAET	3 x 3	14	10.16	10.16	0.5mm	4.85	2.75	4.85	2.75	2.3	2.3
WA13094DQAET	4 x 4	14	10.16	10.16	0.8mm	4.85	2.75	4.85	2.75	2.3	2.3
WA13102DQAET	3 x 3	16	12.70	12.70	0.5mm	3.75	2.05	3.75	2.05	1.25	1.25
WA13089DQAET	4 x 4	16	12.70	12.70	0.65mm	4.75	2.65	4.75	2.65	2.25	2.25
WA13095DQAET	5 x 5	16	12.70	12.70	0.8mm	5.75	4.05	5.75	4.05	3.20	3.20
WA13065DQAET	5 x 4	18	12.70	12.70	0.65mm	4.75	2.65	5.75	3.65	2.25	3.25
WA13096DQAET	6 x 5	18	12.70	12.70	0.8mm	5.75	3.65	6.75	4.65	3.25	4.25
WA13023DQAET	4 x 4	20	17.78	17.78	0.5mm	4.75	2.65	4.75	2.65	2.25	2.25
WA13090DQAET	5 x 5	20	17.78	17.78	0.65mm	5.75	3.65	5.75	3.65	3.00	3.00
WA13097DQAET	6 x 6	20	17.78	17.78	0.8mm	6.75	4.65	6.75	4.65	4.25	4.25
WA13066DQAET	6 x 5	22	15.24	15.24	0.65mm	5.75	3.65	6.75	4.65	3.25	4.25
WA13039DQAET	4 x 4	24	15.24	15.24	0.5mm	4.80	3.00	4.80	3.00	2.25	2.25
WA13052DQAET	5 x 4	24	17.78	17.78	0.5mm	4.80	3.00	5.80	4.00	2.25	3.25
WA13091DQAET	5 x 5	24	12.70	12.70	0.65mm	5.80	4.00	5.80	4.00	3.25	3.25
WA13098DQAET	6 x 6	24	12.70	12.70	0.8mm	6.85	4.75	6.85	4.75	4.30	4.30
WA13076DQAET	4 x 4	28	12.70	12.70	0.4mm	4.75	3.05	4.75	3.05	2.25	2.25
WA13038DQAET	6 x 6	28	12.70	12.70	0.65mm	6.80	5.20	6.80	5.20	4.80	4.80
WA13077DQAET	5 x 5	28	12.70	12.70	0.5mm	5.75	3.65	5.75	3.65	3.25	3.25
WA13099DQAET	7 x 7	28	17.78	17.78	0.8mm	7.75	5.65	7.75	5.65	5.25	5.25
WA13020DQAET	5 x 5	32	17.78	17.78	0.5mm	5.80	4.00	5.80	4.00	3.25	3.25
WA13092DQAET	7 x 7	32	17.78	17.78	0.65mm	7.80	5.60	7.80	5.60	4.85	4.85
WA13100DQAET	8 x 8	32	20.32	20.32	0.8mm	8.75	6.65	8.75	6.65	6.25	6.25

WA13067DQAET	6 x 6	36	17.78	17.78	0.5mm	6.75	4.65	6.75	4.65	4.00	4.00
WA13093DQAET	8 x 8	36	20.32	20.32	0.65mm	8.80	7.20	8.80	7.20	6.80	6.80
WA13101DQAET	9 x 9	36	20.32	20.32	0.8mm	9.80	7.60	9.80	7.60	NP*	NP*
WA13026DQAET	5 x 7	38	17.78	17.78	0.5mm	5.70	4.10	7.70	6.10	NP*	NP*
WA13068DQAET	5 x 5	40	17.78	17.78	0.4mm	5.75	4.05	5.75	4.05	3.40	3.40
WA13075DQAET	6 x 6	40	17.78	17.78	0.5mm	6.80	4.90	6.80	4.90	4.20	4.20
WA13085DQAET	8 x 8	40	20.32	20.32	0.65mm	8.75	6.65	8.75	6.65	6.25	6.25
WA13054DQAET	7 x 7	44	17.78	17.78	0.5mm	7.80	5.60	7.80	5.60	4.85	4.85
WA13086DQAET	9 x 9	44	20.32	20.32	0.65mm	9.80	8.20	9.80	8.20	NP*	NP*
WA13069DQAET	6 x 6	48	17.78	17.78	0.4mm	6.75	4.85	6.75	4.85	4.40	4.40
WA13078DQAET	7 x 7	48	17.78	17.78	0.5mm	7.75	6.05	7.75	6.05	5.25	5.25
WA13087DQAET	9 x 9	48	20.32	20.32	0.65mm	9.80	8.20	9.80	8.20	7.80	7.80
WA13070DQAET	8 x 8	52	20.32	20.32	0.5mm	8.75	6.65	8.75	6.65	6.25	6.25
WA13071DQAET	7 x 7	56	20.32	20.32	0.4mm	7.75	5.85	7.75	5.85	5.40	5.40
WA13079DQAET	8 x 8	56	20.32	20.32	0.5mm	8.80	7.00	8.80	7.00	6.25	6.25
WA13080DQAET	9 x 9	60	20.32	20.32	0.5mm	9.80	8.20	9.80	8.20	7.80	7.80
WA13072DQAET	9 x 9	64	22.86	22.86	0.5mm	9.80	8.00	9.80	8.00	7.45	7.45
WA13081DQAET	10 x 10	68	25.40	25.40	0.5mm	10.75	8.65	10.75	8.65	7.85	7.85
WA13103DQAET	10 x 10	72	27.54	27.54	0.5mm	10.80	9.00	10.80	9.00	8.45	8.45
WA13074DQAET	12 x 12	80	30.48	30.48	0.5mm	12.75	10.65	12.75	10.65	10.25	10.25

NP* - Adapter contains no central GND pad

Dimensions are provisional and may be subject to change

<i>US Office</i>		<i>European Office</i>	
Address	Winslow Adaptics Inc Venetia Bay Boulevard Suite 212 Venice FL 34292	Address	Winslow Adaptics Ltd Brecon Enterprise Park Brecon Powys UK LD3 8EF
Telephone	1866 WINSLOW (Toll free)	Telephone	44 (0) 1874 625555
Fax	941 483 3209	Fax	44 (0) 1874 625500
Email	sales@winslowadaptics.com	Email	sales@winslowadaptics.co.uk
Web	www.winslowadaptics.com	Web	www.winslowadaptics.co.uk