

KEMET Part Number: MMK22.5475K100D15L4TRAY
(F601DM475K100C, MMK22,5475K100D15L4TRAY)

MMK/F601, Film, Metallized Polyester, General Purpose, 4.7 uF, 10%, 100 VDC, 85°C, Lead Spacing = 22.5mm



General Information	
Supplier:	KEMET
Series:	MMK/F601
Dielectric:	Metallized Polyester
Style:	Radial
Features:	DC Multipurpose Applications
RoHS:	Yes
Lead:	Wire Leads
Notes:	Not For New Design, Please Check Possible Alternative Parts (AltPart)

Dimensions	
L	26mm MAX
H	18.5mm MAX
T	9mm MAX
S	22.5mm +/-0.4mm
LL	5mm NOM
F	0.8mm NOM

Packaging Specifications	
Packaging:	Bulk, Tray
Packaging Quantity:	308

Specifications	
Capacitance:	4.7 uF
Capacitance Tolerance:	10%
Voltage AC:	63 VAC
Voltage DC:	100 VDC, 77.5 VDC (100C)
Temperature Range:	-55/+100C
Rated Temperature:	85°C
Dissipation Factor:	1.00% 1kHz
Insulation Resistance:	1.0638 GOhms
Max dV/dt:	5 V/us
Inductance:	6 nH