

T350, Tantalum, MnO2 Tantalum, Commercial Grade, 10 uF, 10%, 25 VDC, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 2.54mm



General Information	
Supplier:	KEMET
Series:	T350
Dielectric:	MnO2 Tantalum
Style:	Radial
Description:	Radial, Solid Tantalum, Conformal, Dipped
Features:	Low Leakage
RoHS:	Yes
Termination:	Tin
Notes:	Longest Lead Is Positive

Dimensions	
D	5.5mm
H	8.9mm
S	2.54mm +/-0.38mm
LL	12.7mm +/-1.26mm
F	0.5mm +/-0.05mm

Specifications	
Capacitance:	10 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC (85C), 16 VDC (125C), 0.25 VDC (125C Reverse)
Temperature Range:	-55/+125C
Dissipation Factor:	6.00%
Leakage Current:	2 uA

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	1000