Linear Regulator - Low Output Voltage, Ultra-Fast Low Dropout, Enable 1.0 A

NCP5661, NCV5661

The NCP5661/NCV5661 is a high performance, low dropout linear regulator designed for high power applications that require up to 1.0 A current. It is offered in both fixed and adjustable output versions. With output voltages as low as 0.9 V and ultra–fast response times for load transients, the NCP5661/NCV5661 also provides additional features such as Enable and Error Flag (for the fixed output version), increasing the utility of these devices. A thermally robust, 5 pin DPAK or DFN 3x3.3 mm, combined with an architecture that offers low ground current (independent of load), provides for a superior high–current LDO solution.

Features

- Ultra-Fast Transient Response (Settling Time: 1–3 μs)
- Low Noise Without Bypass Capacitor (26 μV_{rms)}
- Low Ground Current Independent of Load (3.0 mA Maximum)
- Fixed/Adjustable Output Voltage Versions
- Enable Function
- Error Flag (Fixed Output Version)
- Current Limit Protection
- Thermal Protection
- 0.9 V Reference Voltage for Ultra-Low Output Operation
- Power Supply Rejection Ratio > 65 dB
- NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable
- These are Pb-Free Devices

Applications

- Servers
- ASIC Power Supplies
- Post Regulation for Power Supplies
- Constant Current Source
- Networking Equipment
- Gaming and STB Modules




ON Semiconductor®

www.onsemi.com





DPAK-5 CENTER LEAD CROP CASE 175AA









x = A for Adjustable Version

B for Fixed 1.2 V

C for Fixed 3.3 V

D for Fixed 1.5 V

E for Fixed 1.8 V

F for Fixed 2.5 V G for Fixed 2.8 V

H for Fixed 3.0 V

zzz = 12 for Fixed 1.2 V

15 for Fixed 1.5 V

18 for Fixed 1.8 V

25 for Fixed 2.5 V

28 for Fixed 2.8 V

30 for Fixed 3.0 V

33 for Fixed 3.3 V

ADJ for Adjustable Version

A = Assembly Location

L = Wafer Lot

Y = Year

WW = Work Week

G = Pb-Free

= Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 10 of this data sheet.

PIN FUNCTION DESCRIPTION

Pin Adj/Fixed DFN6	Pin Adj/Fixed DPAK-5	Pin Name	Description	
1	1	Enable	This pin allows for on/off control of the regulator. To disable the device, connect to Ground. If this function is not in use, connect to V_{in} .	
2,3	2	V _{in}	Positive Power Supply Input Voltage	
4, EPAD	3, TAB	Ground	Power Supply Ground	
5	4	V _{out}	Regulated Output Voltage	
6	5	Adj (Adjustable Version)	This pin is connected to the resistor divider network and programs the output voltage.	
6	5	Error Flag (Fixed Version)	An Error Flag is triggered when the output voltage is out of regulation excluding transient signals that may occur. Requires a pullup resistor ≈ 100 k Ω .	

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Input Voltage	V _{in}	18	V
Output Pin Voltage	V _{out}	-0.3 to Vin +0.3	V
Adjust Pin Voltage	V_{adj}	-0.3 to Vin +0.3	V
Enable Pin Voltage	V _{en}	-0.3 to Vin +0.3	V
Error Flag Voltage	V _{ef}	-0.3 to Vin +0.3	V
Error Flag Current	l _{ef}	3.0	mA
Thermal Characteristics, DPAK-5 (Note 1) Thermal Resistance, Junction-to-Air Thermal Resistance, Junction-to-Case	R _θ JA R _θ JC	100 8.0	°C/W
Thermal Characteristics, DFN6 (Note 2) Thermal Resistance, Junction-to-Air Thermal Resistance, Junction-to-Lead (Note 3)	R _θ JA R _θ JL	82 18	°C/W
Operating Junction Temperature Range	T _J	-40 to +150	°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

NOTE: This device series contains ESD protection and exceeds the following tests:

Human Body Model (HBM) JESD 22-A114-B

Machine Model (MM) JESD 22-A115-A.

The maximum package power dissipation is:

$$P_D = \frac{T_J(max) - T_A}{R_{\theta JA}}$$

The bipolar process employed for this IC is fully characterized and rated for reliable 18 V V_{CCmax} operation. To avoid damaging the part or degrading it's reliability, power dissipation transients should be limited to under 20 W for DPAK.

For open-circuit to short-circuit transient,

- P_{DTransient} = V_{CCmax} * I_{SC}.

 1. 1 oz copper, 0.26 in² copper area (minimum pad)
- 2. 1 oz copper, 1 in² copper area
- 3. Lead 2

ELECTRICAL CHARACTERISTICS

 $(V_{in}-V_{out}=1.5~V, for~typical~values~T_{J}=25^{\circ}C,~for~min/max~values~T_{J}=-40^{\circ}C~to~125^{\circ}C,~C_{in}=C_{out}=150~\mu F~unless~otherwise~noted.)$

Characteristic		Min	Тур	Max	Unit
ADJUSTABLE OUTPUT VERSION					
Input Voltage	V _{in}	2.0	_	9.0	V
Output Noise Voltage (f = 10 Hz to 100 kHz)	V _n	-	26	-	μV_{rms}
Output Voltage Accuracy $T_{J} = 25^{\circ}\text{C (I}_{out} = 10 \text{ mA to 1.0 A)}$ $T_{J} = -20 \text{ to } +125^{\circ}\text{C (I}_{out} = 10 \text{ mA to 1.0 A)}$ $T_{J} = -40 \text{ to } +150^{\circ}\text{C (I}_{out} = 10 \text{ mA to 1.0 A)}$		-1% -1.5% -2%	- 0.9 -	+1% +1.5% +2%	V
Adjustable Pin Input Current	I _{adj}	-	40	-	nA
Line Regulation (I_{out} = 10 mA, V_{out} +1.5 V < V_{in} < 7.0 V)	REG _{line}	-	0.03	-	%
Load Regulation (10 mA < I _{out} < 1.0 A)		-	0.03	-	%
Dropout Voltage (I _{out} = 1.0 A)		-	1.0	1.3	V
Peak Output Current Limit		1.0	=	-	Α
Internal Current Limitation		-	1.5	-	Α
Ripple Rejection (120 Hz) Ripple Rejection (1.0 kHz)		-	70 65	- -	dB
Thermal Shutdown (Guaranteed by Design)	T _{SHD}	-	160	-	°C
Ground Current I _{out} = 1.0 A Disabled State	I _q I _{qds}	- -	1.3 10	3.0 300	mA μA
Enable Input Threshold Voltage Voltage Increasing, On State, Logic High Voltage Decreasing, Off State, Logic Low	V _{en}	1.3 -	- -	- 0.3	V
Enable Input Current $ {\hbox{Enable Pin Voltage}} = 0.3 \ {\hbox{V}_{max}} $ $ {\hbox{Enable Pin Voltage}} = 1.3 \ {\hbox{V}_{min}} $		- -	0.5 0.5	- -	μΑ

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

ELECTRICAL CHARACTERISTICS

 $(V_{in}-V_{out}=1.5~V, for~typical~values~T_{J}=25^{\circ}C,~for~min/max~values~T_{J}=-40^{\circ}C~to~125^{\circ}C,~C_{in}=C_{out}=150~\mu F~unless~otherwise~noted.)$

Characteristic	Symbol	Min	Тур	Max	Unit
FIXED OUTPUT VOLTAGE					
Input Voltage	V _{in}	2.0	-	9.0	V
Output Noise Voltage (V _{out} = 0.9 V)	V _n	-	26	-	μV_{rms}
Output Voltage Accuracy $T_J = 25^{\circ}\text{C (I}_{out} = 10 \text{ mA to } 1.0 \text{ A})$ $T_J = -20 \text{ to } +125^{\circ}\text{C (I}_{out} = 10 \text{ mA to } 1.0 \text{ A})$ $T_J = -40 \text{ to } +150^{\circ}\text{C (I}_{out} = 10 \text{ mA to } 1.0 \text{ A})$	V _{out}	-1% -1.5% -2%	– V _{out} –	+1% +1.5% +2%	V
Line Regulation (I_{out} = 10 mA, V_{out} +1.5 V < V_{in} < 7.0 V)	REG _{line}	_	0.03	-	%
Load Regulation (10 mA < I _{out} < 1.0 A)	REG _{load}	-	0.2	-	%
Dropout Voltage (I _{out} = 1.0 A)	V_{DO}	-	1.0	1.3	V
Peak Output Current Limit	I _{out}	1.0	ı	-	Α
Internal Current Limitation	I _{lim}	-	1.5	-	Α
Ripple Rejection (120 Hz) Ripple Rejection (1.0 kHz)	RR	- -	70 65	-	dB
Thermal Shutdown (Guaranteed by Design)	T _{SHD}	-	160	-	°C
Ground Current I _{out} = 1.0 A Disabled State	I _q I _{qds}	- -	1.3 30	3.0 300	mA μA
Enable Input Threshold Voltage Voltage Increasing, On State, Logic High Voltage Decreasing, Off State, Logic Low	V _{en}	1.3 -	- -	- 0.3	V
Enable Input Current $ \begin{aligned} \text{Enable Pin Voltage} &= 0.3 \text{ V}_{max} \\ \text{Enable Pin Voltage} &= 1.3 \text{ V}_{min} \end{aligned} $	l _{en}	- -	0.5 0.5	- -	μΑ
Error Flag (Fixed Output) 1.2 V Output 1.5 V Output 1.8 V Output 2.5 V Output 2.8 V Output 3.0 V Output 3.3 V Output	V _{eflt}	88 88 88 88 88 88	92 92 92 92 92 92 94	97 97 97 97 97 97 97	% of V _{out}
Error Flag Output Low Voltage Saturation (I _{ef} = 1.0 mA)	V _{efdo}	-	200	-	mV
Error Flag Leakage	l _{efleak}	-	1.0	-	μΑ
Error Flag Blanking Time (Note 4)	T _{ef}	-	50	-	μs

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Error Flag Blanking Time




Figure 1. Typical Schematic, Adjustable Output Version






Figure 2. Typical Schematic, Fixed Output Version



1.00 DROPOUT VOLTAGE (V) 0.95 0.90 0.85 0.80 V_{out} = 2.5 V Adjustable C_{in} = 150 μF V_{D0}, C_{out} = 10 to 150 μF 0.75 $T_J = 25^{\circ}C$ 0.3 0.4 0.0 0.1 0.2 0.5 0.6 8.0 0.7 0.9 I_{out}, OUTPUT CURRENT (A)

Figure 3. Dropout Voltage vs. Temperature

Figure 4. Dropout Voltage vs. Output Current







Figure 5. Ground Current vs. Temperature

Figure 6. Short Circuit Current Limit vs.
Temperature






Figure 7. Output Voltage vs. Input Voltage

Figure 8. Output Voltage vs. Output Load Current




Figure 9. Output Current vs. Input-Output Voltage Differential




Figure 10. Ripple Rejection vs. Frequency




Figure 11. Noise Density vs. Frequency




Figure 12. Noise Density vs. Frequency




Figure 13. 1.2 Volt Output Stability with Output Capacitor ESR




Figure 14. 3.3 Volt Output Stability with Output Capacitor ESR




Figure 15. Load Transient Response




Figure 16. Load Transient Response

APPLICATION INFORMATION

The NCP5661 is a high performance low dropout 1.0 A linear regulator suitable for high power applications, featuring an ultra–fast response time and low noise without a bypass capacitor. It is offered in both fixed and adjustable output versions with voltages as low as 0.9 V. Additional features, such as Enable and Error Flag (fixed output version) increase the utility of the NCP5661. It is thermally robust and includes the safety features necessary during a fault condition, which provide for an attractive high current LDO solution for server, ASIC power supplies, networking equipment applications, and many others.

Input Capacitor

The recommended input capacitor value is a 150 μF OSCON with an Equivalent Series Resistance (ESR) of 50 m Ω . It is especially required if the power source is located more than a few inches from the NCP5661. This capacitor will reduce device sensitivity and enhance the output transient response time. The PCB layout is very important and in order to obtain the optimal solution, the Vin and GND traces should be sufficiently wide to minimize noise and unstable operation.

Output Capacitor

Proper output capacitor selection is required to maintain stability. The NCP5661 is guaranteed to be stable at an output capacitance of $C_{out} > 10~\mu F$. In the case of using electrolytic capacitors, low ESR type (ESR < 300 m Ω) should be used to maintain device stability. Multilayer ceramic capacitors can also be used with this device. For PCB layout considerations, place the recommended ceramic capacitor close to the output pin and keep the leads short. This should help ensure ultra–fast transient response times.

Adjustable Output Operation

The application circuit for the adjustable output version is shown in Figure 1. The reference voltage is $0.9\ V$ and the

adjustable pin current is typically 40 nA. A resistor divider network, R1 and R2, is calculated using the following formula:




Figure 17. To achieve the minimum output voltage, ADJ to V_{out} has to be connected together

Current Limit Operation

As the peak output current increases beyond its limitation, the device is internally clampled to 1.5 A, thus causing the output voltage to decrease and go out of regulation. This allows the device never to exceed the maximum power dissipation.

Error Flag Operation

The Error Flag pin on the NCP5661 will produce a logic Low when it drops below the nominal output voltage. Refer to the electrical characteristics for the threshold values at which point the Error Flag goes Low. When the NCP5661 is above the nominal output voltage, the Error Flag will remain at logic High.

The external pullup resistor needs to be connected between V_{in} (Pin 1) and the Error Flag pin (Pin 5). A resistor of approximately $100~k\Omega$ is recommended to minimize the current consumption. No pullup resistor is required if the Error Flag output is not being used.




Figure 18. DFN6 Thermal Resistance vs. Copper Area




Figure 19. Test Board used for Evaluation

ORDERING INFORMATION

Device	Nominal Output Voltage	Package	Shipping†		
NCP5661DTADJRKG	Adj (Pb-Free)				
NCP5661DT12RKG	Fixed, 1.2 V (Pb-Free)				
NCP5661DT18RKG	Fixed, 1.8 V (Pb-Free)		2500/Tape & Reel		
NCP5661DT25RKG	Fixed, 2.5 V (Pb-Free)				
NCP5661DT33RKG	Fixed, 3.3 V (Pb-Free)	DPAK			
NCV5661DTADJRKG*	Adj (Pb-Free)				
NCV5661DT12RKG*	Fixed, 1.2 V (Pb-Free)				
NCV5661DT18RKG*	Fixed, 1.8 V (Pb-Free)				
NCV5661DT33RKG*	Fixed, 3.3 V (Pb-Free)				
NCP5661MNADJT2G	Adj (Pb-Free)				
NCP5661MN12T2G	Fixed, 1.2 V (Pb-Free)				
NCP5661MN15T2G	Fixed, 1.5 V (Pb-Free)				
NCP5661MN18T2G	Fixed, 1.8 V (Pb-Free)				
NCP5661MN25T2G	Fixed, 2.5 V (Pb-Free)				
NCP5661MN28T2G	Fixed, 2.8 V (Pb-Free)				
NCP5661MN30T2G	Fixed, 3.0 V (Pb-Free)				
NCP5661MN33T2G	Fixed, 3.3 V (Pb-Free)	DFN6			
NCV5661MNADJT2G*	Adj (Pb-Free)	3x3.3 mm	3000/Tape & Reel		
NCV5661MN12T2G*	Fixed, 1.2 V (Pb-Free)				
NCV5661MN15T2G*	Fixed, 1.5 V (Pb-Free)				
NCV5661MN18T2G*	Fixed, 1.8 V (Pb-Free)				
NCV5661MN25T2G*	Fixed, 2.5 V (Pb-Free)				
NCV5661MN28T2G*	Fixed, 2.8 V (Pb-Free)				
NCV5661MN30T2G*	Fixed, 3.0 V (Pb-Free)				
NCV5661MN33T2G*	Fixed, 3.3 V (Pb-Free)				

NOTE: Additional Fix output voltages are available upon request.


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

^{*}NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable



DPAK-5, CENTER LEAD CROP CASE 175AA **ISSUE B**


DATE 15 MAY 2014



- NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- 2. CONTROLLING DIMENSION: INCH.


	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.235	0.245	5.97	6.22
В	0.250	0.265	6.35	6.73
С	0.086	0.094	2.19	2.38
D	0.020	0.028	0.51	0.71
E	0.018	0.023	0.46	0.58
F	0.024	0.032	0.61	0.81
G	0.180	BSC	4.56 BSC	
Н	0.034	0.040	0.87	1.01
J	0.018	0.023	0.46	0.58
K	0.102	0.114	2.60	2.89
L	0.045	BSC	1.14 BSC	
R	0.170	0.190	4.32	4.83
R1	0.185	0.210	4.70	5.33
S	0.025	0.040	0.63	1.01
U	0.020		0.51	
٧	0.035	0.050	0.89	1.27
Z	0.155	0.170	3.93	4.32

RECOMMENDED SOLDERING FOOTPRINT*



^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC MARKING DIAGRAMS*



*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

= Pb-Free Package

DOCUMENT NUMBER:	98AON12855D	Electronic versions are uncontrolled except when accessed directly from the Document Reposi Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	DPAK-5 CENTER LEAD CROP		PAGE 1 OF 1		

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others. TOP VIEW

SIDE VIEW

D2-

BOTTOM VIEW

GENERIC

MARKING DIAGRAM*

XXXXX

XXXXX

AYWW=

DETAIL B

|//||0.10|C

|△|0.08|C|

DETAIL

Α

A

В

С

-6X L

6X b ⊕ 0.10 C A B 0.05 C NOTE 5




PIN DNE **REFERENCE**


DFN6 3.0x3.3, 0.95P CASE 506AX **ISSUE A**


DATE 22 SEP 2020



- DIMENSIONING AND TOLERANCING PER ASME Y14.5M. 2009.
- CONTROLLING DIMENSION: MILLIMETERS
 DIMENSION & APPLIES TO PLATED TERMINALS AND IS
 MEASURED BETWEEN 0.15 AND 0.30MM FROM THE TERMINAL TIP.
 COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL
- AS THE TERMINALS.
- POSITIONAL TOLERANCE APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.









DETAIL A

	2.	15— - I	_6X	0.83
			1	1
1,35-				3.60
1.35				
]	
	0.95 _ PITCH	-	6X	0.50
	RECOM	IMEN]	DED	

For additional information on our Pb-Free strategy and soldering details, please download the IIN Semiconductor Soldering and Mounting Techniques Reference Manual, SDLDERRM/D.

MOUNTING FOOTPRINT

= Pb-Free Package (Note: Microdot may be in either location)

WW

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON21930D	Electronic versions are uncontrolled except when accessed directly from the Document Repos Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	DFN6 3.0X3.3, 0.95P		PAGE 1 OF 1	

XXXX = Specific Device Code = Assembly Location

= Year

= Work Week

ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative