






NLV25T-101J-EF

Applications		Commercial Grade
Feature		Wire Wound
		No Directivity
		Ferrite Core
Series	NLV-EF Series / NLV25-EF Type	
Status	Production	



Size	
Length(L)	2.50mm +/-0.20mm
Width(W)	2.00mm +/-0.10mm
Thickness(T)	1.80mm +/-0.10mm
Recommended Land Pattern (A)	1.00mm Nom.
Recommended Land Pattern (B)	1.50mm Nom.
Recommended Land Pattern (C)	1.50mm Nom.


Electrical Characteristics	
Inductance	100uH +/-5% at 0.796MHz
Rated Current	60mA
Self-Resonant Frequency [Min.]	12MHz
Q [Min.]	15 at 25.2MHz
DC Resistance [Max.]	21Ω

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105degC
Soldering Method	Flow, Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.025g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

NLV25T-101J-EF


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




NLV25T-101J-EF



NLV25T-101J-EF



NLV25T-101J-EF




NLV25T-101J-EF


- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.

NLV25T-101J-EF

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



NLV25T-101J-EF(Amb. Temp. = 20degc)



NLV25T-101J-EF(DC = 0A)

NLV25T-101J-EF(DC = 0.03A)

Temperature Rise by DC
no data available

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.