






# NL453232T-101J-PF

Applications		Commercial Grade
Feature		Wire Wound
		No Directivity
		Ferrite Core
Series	NL Series / NL453232 Type	
Status	Production	



Size	
Length(L)	4.50mm +/-0.30mm
Width(W)	3.20mm +/-0.20mm
Thickness(T)	3.20mm +/-0.20mm
Recommended Land Pattern (A)	1.50mm Nom.
Recommended Land Pattern (B)	3.00mm Nom.
Recommended Land Pattern (C)	2.80mm Nom.


Electrical Characteristics	
Inductance	100uH +/-5% at 0.796MHz
Rated Current	110mA
Self-Resonant Frequency [Min.]	8MHz
Q [Min.]	40 at 0.796MHz
DC Resistance [Max.]	8Ω

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 85degC
Soldering Method	Flow, Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	500Pcs Min.
Weight	0.18g


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# NL453232T-101J-PF


**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




**NL453232T-101J-PF**



**NL453232T-101J-PF**



**NL453232T-101J-PF**




**NL453232T-101J-PF**

- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.

# NL453232T-101J-PF

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.  
•All specifications are subject to change without notice.