






NLCV25T-100K-PF

Applications		Commercial Grade
Feature		Wire Wound
		No Directivity
		Ferrite Core
Series	NLCV-PF Series / NLCV25-PF Type	
Status	Production	



Size	
Length(L)	2.50mm +/-0.20mm
Width(W)	2.00mm +/-0.10mm
Thickness(T)	1.80mm +/-0.10mm
Recommended Land Pattern (A)	1.00mm Nom.
Recommended Land Pattern (B)	1.50mm Nom.
Recommended Land Pattern (C)	1.50mm Nom.


Electrical Characteristics	
Inductance	10uH +/-10% at 2.52MHz
Rated Current	210mA
Self-Resonant Frequency [Min.]	32MHz
Q [Typ.]	30 at 2.52MHz
DC Resistance [Nom.]	1.69Ω
DC Resistance [Max.]	2.197Ω

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105degC
Soldering Method	Flow, Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.025g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

NLCV25T-100K-PF


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




NLCV25T-100K-PF



NLCV25T-100K-PF



NLCV25T-100K-PF




NLCV25T-100K-PF


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

NLCV25T-100K-PF

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




NLCV25T-100K-PF(Amb. Temp. = 20degc)



NLCV25T-100K-PF(DC = 0A)

NLCV25T-100K-PF(DC = 0.105A)



NLCV25T-100K-PF(Amb. Temp. = 20degc)

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.