





NLCV32T-100K-EFR

Applications		Commercial Grade
Feature		Wire Wound
		No Directivity
		Ferrite Core
Series	NLCV-EF Series / NLCV32-EFR Type	
Status	Production	



Size	
Length(L)	3.20mm +/-0.20mm
Width(W)	2.50mm +/-0.20mm
Thickness(T)	2.20mm +/-0.20mm
Recommended Land Pattern (A)	1.20mm Nom.
Recommended Land Pattern (B)	2.00mm Nom.
Recommended Land Pattern (C)	2.00mm Nom.


Electrical Characteristics	
Inductance	10uH +/-10% at 2.52MHz
Rated Current	600mA
Self-Resonant Frequency [Min.]	30MHz
Q [Typ.]	20 at 2.52MHz
DC Resistance [Nom.]	420mΩ
DC Resistance [Max.]	504mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 125degC
Soldering Method	Flow, Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.05g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

NLCV32T-100K-EFR

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




NLCV32T-100K-EFR



NLCV32T-100K-EFR



NLCV32T-100K-EFR




NLCV32T-100K-EFR


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

NLCV32T-100K-EFR

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




NLCV32T-100K-EFR(Amb. Temp. = 20degc)



NLCV32T-100K-EFR(DC = 0A)

NLCV32T-100K-EFR(DC = 0.3A)



NLCV32T-100K-EFR(Amb. Temp. = 20degc)

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.