






NLCV32T-221K-EF

Applications		Commercial Grade
Feature		Wire Wound
		No Directivity
		Ferrite Core
Series	NLCV-EF Series / NLCV32-EF Type	
Status	Production	



Size	
Length(L)	3.20mm +/-0.20mm
Width(W)	2.50mm +/-0.20mm
Thickness(T)	2.20mm +/-0.20mm
Recommended Land Pattern (A)	1.20mm Nom.
Recommended Land Pattern (B)	2.00mm Nom.
Recommended Land Pattern (C)	2.00mm Nom.


Electrical Characteristics	
Inductance	220uH +/-10% at 0.796MHz
Rated Current	80mA
Self-Resonant Frequency [Min.]	7MHz
Q [Typ.]	20 at 0.796MHz
DC Resistance [Nom.]	8.4Ω
DC Resistance [Max.]	10.92Ω

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105degC
Soldering Method	Flow, Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.05g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

NLCV32T-221K-EF


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




NLCV32T-221K-EF



NLCV32T-221K-EF



NLCV32T-221K-EF





NLCV32T-221K-EF

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.


NLCV32T-221K-EF

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



NLCV32T-221K-EF(DC = 0A)

NLCV32T-221K-EF(DC = 0.04A)



- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.