

## Is Now Part of



## ON Semiconductor®

## To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to <a href="mailto:Fairchild\_questions@onsemi.com">Fairchild\_questions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees



May 1995 Revised April 2001

## 74LCX16543

# Low Voltage 16-Bit Registered Transceiver with 5V Tolerant Inputs and Outputs

## **General Description**

The LCX16543 contains sixteen non-inverting transceivers containing two sets of D-type registers for temporary storage of data flowing in either direction. Each byte has separate control inputs which can be shorted together for full 16-bit operation. Separate Latch Enable and Output Enable inputs are provided for each register to permit independent input and output control in either direction of data flow.

The LCX16543 is designed for low voltage (2.5V or 3.3V)  $V_{CC}$  applications with capability of interfacing to a 5V signal environment

The LCX16543 is fabricated with an advanced CMOS technology to achieve high speed operation while maintaining CMOS low power dissipation.

#### **Features**

- 5V tolerant inputs and outputs
- 2.3V-3.6V V<sub>CC</sub> specifications provided
- 5.2 ns  $t_{PD}$  max ( $V_{CC} = 3.3V$ ), 20  $\mu$ A  $I_{CC}$  max
- Power down high impedance inputs and outputs
- Supports live insertion/withdrawal (Note 1)
- $\pm$ 24 mA Output Drive (V<sub>CC</sub> = 3.0V)
- Implements patented noise/EMI reduction circuitry
- Latch-up performance exceeds 500 mA
- ESD performance:

Human Body Model > 2000V

Machine Model > 200V

Note 1: To ensure the high-impedance state during power up or down,  $\overline{\text{OE}}$  should be tied to  $V_{CC}$  through a pull-up resistor: the minimum value or the resistor is determined by the current-sourcing capability of the driver.

#### **Ordering Code:**


Order Number	der Number Package Number Package Description				
74LCX16543MEA	MS56A	56-Lead Shrink Small Outline Package (SSOP), JEDEC MO-118, 0.300 Wide			
74LCX16543MTD	MTD56	56-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide			

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

#### **Connection Diagram**



## **Logic Symbol**



© 2001 Fairchild Semiconductor Corporation

DS012464

## **Pin Descriptions**

Pin Names	Description			
OEAB <sub>n</sub>	A-to-B Output Enable Input (Active LOW)			
OEBA <sub>n</sub>	B-to-A Output Enable Input (Active LOW)			
CEAB <sub>n</sub>	A-to-B Enable Input (Active LOW)			
CEBA <sub>n</sub>	B-to-A Enable Input (Active LOW)			
LEAB <sub>n</sub>	A-to-B Latch Enable Input (Active LOW)			
LEBA <sub>n</sub>	B-to-A Latch Enable Input (Active LOW)			
A <sub>0</sub> -A <sub>15</sub>	A-to-B Data Inputs or B-to-A 3-STATE Outputs			
B <sub>0</sub> -B <sub>15</sub>	B-to-A Data Inputs or A-to-B 3-STATE Outputs			

#### Data I/O Control Table

Inputs			Latch Status	Output Buffers
CEAB <sub>n</sub>	$\overline{\text{LEAB}}_{\text{n}}$	$\overline{\text{OEAB}}_{\text{n}}$	(Byte n)	(Byte n)
Н	Х	Х	Latched	High Z
X	Н	X	Latched	_
L	L	X	Transparent	_
X	X	Н	_	High Z
L	X	L	_	Driving

H = HIGH Voltage Level


## **Functional Description**

The LCX16543 contains sixteen non-inverting transceivers with 3-STATE outputs. The device is byte controlled with each byte functioning identically, but independent of the other. The control pins may be shorted together to obtain full 16-bit operation. The following description applies to each byte. For data flow from A to B, for example, the A-to-B Enable  $(\overline{CEAB}_n)$  input must be LOW in order to enter data from  $\mathrm{A}_0\mathrm{-A}_{15}$  or take data from  $\mathrm{B}_0\mathrm{-B}_{15}$ , as indicated in the Data I/O Control Table. With  $\overline{\text{CEAB}}_{\text{n}}$  LOW, a LOW signal on the A-to-B Latch Enable (LEABn) input

makes the A-to-B latches transparent; a subsequent LOWto-HIGH transition of the  $\overline{\text{LEAB}}_n$  signal puts the A latches in the storage mode and their outputs no longer change with the A inputs. With  $\overline{\text{CEAB}}_n$  and  $\overline{\text{OEAB}}_n$  both LOW, the 3-STATE B output buffers are active and reflect the data present at the output of the A latches. Control of data flow from B to A is similar, but using the  $\overline{CEBA}_n$ ,  $\overline{LEBA}_n$  and OEBA<sub>n</sub> inputs.

L = LOW Voltage Level

 $X = Immaterial \\ A-to-B data flow shown; B-to-A flow control is the same, except using $\overline{CEBA}_n$, $\overline{LEBA}_n$ and $\overline{OEBA}_n$.}$ 



## **Absolute Maximum Ratings**(Note 2)

Symbol	Parameter	Value	Conditions	Units	
V <sub>CC</sub>	Supply Voltage	−0.5 to +7.0		V	
VI	DC Input Voltage	−0.5 to +7.0		V	
Vo	DC Output Voltage	-0.5 to +7.0	Output in 3-STATE	V	
		$-0.5$ to $V_{CC} + 0.5$	Output in HIGH or LOW State (Note 3)	v	
I <sub>IK</sub>	DC Input Diode Current	-50	V <sub>I</sub> < GND	mA	
I <sub>OK</sub>	DC Output Diode Current	-50	V <sub>O</sub> < GND	mA	
		+50	V <sub>O</sub> > V <sub>CC</sub>	IIIA	
I <sub>O</sub>	DC Output Source/Sink Current	±50		mA	
I <sub>CC</sub>	DC Supply Current per Supply Pin	±100		mA	
I <sub>GND</sub>	DC Ground Current per Ground Pin	±100		mA	
T <sub>STG</sub>	Storage Temperature	-65 to +150		°C	

## **Recommended Operating Conditions** (Note 4)

Symbol	Parameter			Max	Units
V <sub>CC</sub>	Supply Voltage Opera		2.0	3.6	V
		Data Retention 1.5 3.6		3.6	V
V <sub>I</sub>	Input Voltage		0	5.5	V
Vo	Output Voltage	HIGH or LOW State	0	V <sub>CC</sub>	V
		3-STATE	0	5.5	V
I <sub>OH</sub> /I <sub>OL</sub>	Output Current	$V_{CC} = 3.0V - 3.6V$ $V_{CC} = 2.7V - 3.0V$ $V_{CC} = 2.3V - 2.7V$		±24	
		$V_{CC} = 2.7V - 3.0V$		±12	mA
		$V_{CC} = 2.3V - 2.7V$		±8	
T <sub>A</sub>	Free-Air Operating Temperature		-40	85	°C
Δt/ΔV	Input Edge Rate, V <sub>IN</sub> = 0.8V–2.0V, V <sub>CC</sub> = 3.0V		0	10	ns/V

Note 2: The Absolute Maximum Ratings are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the Absolute Maximum Ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 4: Unused (inputs or I/Os) must be held HIGH or LOW. They may not float.

#### **DC Electrical Characteristics**

Cumbal	Parameter	Conditions	V <sub>CC</sub>	$V_{CC}$ $T_A = -40^{\circ}C \text{ to } +85^{\circ}C$		Units
Symbol		Conditions	(V)	Min	Max	Units
V <sub>IH</sub>	HIGH Level Input Voltage		2.3 – 2.7	1.7		V
			2.7 – 3.6	2.0		V
V <sub>IL</sub>	LOW Level Input Voltage		2.3 – 2.7		0.7	V
			2.7 – 3.6		8.0	V
V <sub>OH</sub>	HIGH Level Output Voltage	$I_{OH} = -100 \mu A$	2.3 – 3.6	V <sub>CC</sub> - 0.2		
		$I_{OH} = -8 \text{ mA}$	2.3	1.8		
		I <sub>OH</sub> = -12 mA	2.7	2.2		٧
		I <sub>OH</sub> = -18 mA	3.0	2.4		
		$I_{OH} = -24 \text{ mA}$	3.0	2.2		
V <sub>OL</sub>	LOW Level Output Voltage	I <sub>OL</sub> = 100 μA	2.3 – 3.6		0.2	
		I <sub>OL</sub> = 8 mA	2.3		0.6	
		I <sub>OL</sub> = 12 mA	2.7		0.4	V
		I <sub>OL</sub> = 16 mA	3.0		0.4	
		I <sub>OL</sub> = 24 mA	3.0		0.55	
I <sub>I</sub>	Input Leakage Current	0 ≤ V <sub>I</sub> ≤ 5.5V	2.3 – 3.6		±5.0	μΑ
l <sub>OZ</sub>	3-STATE I/O Leakage	$0 \le V_O \le 5.5V$	2.3 – 3.6		±5.0	^
		$V_I = V_{IH}$ or $V_{IL}$	2.3 - 3.0		±3.0	μА
I <sub>OFF</sub>	Power-Off Leakage Current	$V_I$ or $V_O = 5.5V$	0		10	μΑ
	-	•	•	,		

Note 3:  $I_O$  Absolute Maximum Rating must be observed.

## DC Electrical Characteristics (Continued)

Symbol	Parameter	Conditions	V <sub>CC</sub>	$T_A = -40^{\circ}C$ to $+85^{\circ}C$		Units
Cymbol	i didilicici	Conditions	(V)	Min	Max	Omico
I <sub>CC</sub>	Quiescent Supply Current	$V_I = V_{CC}$ or GND	2.3 – 3.6		20	μА
		3.6V ≤ V <sub>I</sub> , V <sub>O</sub> ≤ 5.5V (Note 5)	2.3 – 3.6		±20	μΛ
$\Delta I_{CC}$	Increase in I <sub>CC</sub> per Input	$V_{IH} = V_{CC} - 0.6V$	2.3 – 3.6		500	μΑ

Note 5: Outputs in disabled or 3-STATE only.

## **AC Electrical Characteristics**

		$T_A = -40^{\circ}C$ to $+85^{\circ}C$ , $R_L = 500 \Omega$						
Symbol	Parameter	V <sub>CC</sub> = 3.	3V ± 0.3V	V <sub>CC</sub> = 2.7V		$\textrm{V}_{\textrm{CC}} = \textrm{2.5V} \pm \textrm{0.2V}$		Units
Зуппоп	Farameter	C <sub>L</sub> =	C <sub>L</sub> = 50 pF		C <sub>L</sub> = 50 pF		C <sub>L</sub> = 30 pF	
		Min	Max	Min	Max	Min	Max	
t <sub>PHL</sub>	Propagation Delay	1.5	5.2	1.5	6.0	1.5	6.2	ns
t <sub>PLH</sub>	$A_n$ to $B_n$ or $B_n$ to $A_n$	1.5	5.2	1.5	6.0	1.5	6.2	115
t <sub>PHL</sub>	Propagation Delay	1.5	6.5	1.5	7.5	1.5	7.8	ns
t <sub>PLH</sub>	$\overline{LEBA}_{n}$ to $A_{n}$ or $\overline{LEAB}_{n}$ to $B_{n}$	1.5	6.5	1.5	7.5	1.5	7.8	115
t <sub>PZL</sub>	Output Enable Time							
$t_{PZH}$	$\overline{OEBA}_n$ or $\overline{OEAB}_n$ to $A_n$ or $B_n$	1.5	6.5	1.5	7.0	1.5	8.5	ns
	$\overline{\text{CEBA}}_{\text{n}}$ or $\overline{\text{CEAB}}_{\text{n}}$ to $A_{\text{n}}$ or $B_{\text{n}}$	1.5	6.5	1.5	7.0	1.5	8.5	
t <sub>PLZ</sub>	Output Disable Time							
$t_{PHZ}$	$\overline{OEBA}_n$ or $\overline{OEAB}_n$ to $A_n$ or $B_n$	1.5	6.5	1.5	7.0	1.5	7.8	ns
	$\overline{\text{CEBA}}_n$ or $\overline{\text{CEAB}}_n$ to $A_n$ or $B_n$	1.5	6.5	1.5	7.0	1.5	7.8	
t <sub>S</sub>	Setup Time, HIGH or LOW,	2.5		2.5		3.0		ns
	Data to LEXX <sub>n</sub>							115
t <sub>H</sub>	Hold Time, HIGH or LOW,	1.5		1.5		2.0		ns
	Data to LEXX <sub>n</sub>							115
t <sub>W</sub>	Pulse Width, Latch Enable, LOW	3.0		3.0		3.5		ns
toshl	Output to Output Skew (Note 6)		1.0					ns
toslh			1.0					115

Note 6: Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW (t<sub>OSHL</sub>) or LOW-to-HIGH (t<sub>OSLH</sub>). Parameter guaranteed by design.

## **Dynamic Switching Characteristics**

Symbol	Parameter	Conditions	V <sub>CC</sub>	T <sub>A</sub> = 25°C	Units
-			(V)	Typical	
V <sub>OLP</sub>	Quiet Output Dynamic Peak V <sub>OL</sub>	$C_L = 50 \text{ pF}, V_{IH} = 3.3 \text{V}, V_{IL} = 0 \text{V}$	3.3	0.8	V
		$C_L = 30 \text{ pF}, V_{IH} = 2.5 \text{V}, V_{IL} = 0 \text{V}$	2.5	0.6	V
V <sub>OLV</sub>	Quiet Output Dynamic Valley V <sub>OL</sub>	$C_L = 50 \text{ pF}, V_{IH} = 3.3 \text{V}, V_{IL} = 0 \text{V}$	3.3	-0.8	V
		$C_L = 30 \text{ pF}, V_{IH} = 2.5 \text{V}, V_{IL} = 0 \text{V}$	2.5	-0.6	V

## Capacitance

Symbol	Parameter	Conditions	Typical	Units
C <sub>IN</sub>	Input Capacitance	$V_{CC} = Open, V_I = 0V \text{ or } V_{CC}$	7	pF
C <sub>I/O</sub>	Input/Output Capacitance	$V_{CC} = 3.3V$ , $V_I = 0V$ or $V_{CC}$	8	pF
C <sub>PD</sub>	Power Dissipation Capacitance	$V_{CC} = 3.3V$ , $V_{I} = 0V$ or $V_{CC}$ , $f = 10$ MHz	20	pF

## AC LOADING and WAVEFORMS Generic for LCX Family






FIGURE 1. AC Test Circuit ( $C_L$  includes probe and jig capacitance)


Test	Switch
t <sub>PLH</sub> , t <sub>PHL</sub>	Open
t <sub>PZL</sub> , t <sub>PLZ</sub>	6V at $V_{CC}$ = 3.3 $\pm$ 0.3V $V_{CC}$ x 2 at $V_{CC}$ = 2.5 $\pm$ 0.2V
t <sub>PZH</sub> ,t <sub>PHZ</sub>	GND




**Waveform for Inverting and Non-Inverting Functions** 




3-STATE Output High Enable and Disable Times for Logic



Propagation Delay. Pulse Width and  $t_{\text{rec}}$  Waveforms



Setup Time, Hold Time and Recovery Time for Logic



3-STATE Output Low Enable and Disable Times for Logic







FIGURE 2. Waveforms (Input Characteristics; f =1MHz,  $t_r = t_f = 3ns$ )

Symbol	V <sub>cc</sub>					
Cymbol	$3.3V \pm 0.3V$	2.7V	2.5V ± 0.2V			
V <sub>mi</sub>	1.5V	1.5V	V <sub>CC</sub> /2			
V <sub>mo</sub>	1.5V	1.5V	V <sub>CC</sub> /2			
V <sub>x</sub>	V <sub>OL</sub> + 0.3V	V <sub>OL</sub> + 0.3V	V <sub>OL</sub> + 0.15V			
V <sub>y</sub>	V <sub>OH</sub> – 0.3V	V <sub>OH</sub> – 0.3V	V <sub>OH</sub> – 0.15V			







Package Number MTD56

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

www.onsemi.com