



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng		
Company Unique ID	TE Connectivity	Response Date	2018-06-03	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	206486-2	Amount	11.39739767	Version	-	Identity			
Manufacturer Item Name	CPC RECPT ASSEMBLY SIZE 11-9	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	11-9 RCPT STD SEX				1.0	10.4884	g	
Material	2	PA66-GF22 FR(17)				1.0	10.4884	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	1.8	1.0	0.1887912	g	
Substance	3	Benzenesulfonamide, N-butyl-	Supplier	3622-84-2	0.28	1.0	0.02936752	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0010	1.0	1.0488E-4	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	20.0	1.0	2.09768	g	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.4	1.0	0.0419536	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	22.0	1.0	2.307448	g	
Substance	3	Polyamide 66 - ISO 1043-1 Term PA66	Supplier	1043-1-PA66	39.919	1.0	4.1868644	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	0.52442	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	10.0	1.0	1.04884	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.4	1.0	0.0419536	g	
Substance	3	Methanol	Supplier	67-56-1	0.15	1.0	0.0157326	g	
Substance	3	Benzene, 1,2-dimethyl-	Supplier	95-47-6	0.05	1.0	0.0052442	g	
Sub-Item	1	CPC RTNT INSERT SZ 1109,SRS II				1.0	0.90899767	g	
Material	2	PA66-GF22 FR(17)				1.0	0.90899767	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	1.8	1.0	0.01636196	g	
Substance	3	Benzenesulfonamide, N-butyl-	Supplier	3622-84-2	0.28	1.0	0.00254519	g	

Substance	3	Arsenic	Supplier	7440-38-2	0.0010	1.0	9.089977E-6	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	20.0	1.0	0.18179953	g	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.4	1.0	0.00363599	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	22.0	1.0	0.19997949	g	
Substance	3	Polyamide 66 - ISO 1043-1 Term PA66	Supplier	1043-1-PA66	39.919	1.0	0.36286278	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	0.04544988	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	10.0	1.0	0.09089977	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.4	1.0	0.00363599	g	
Substance	3	Methanol	Supplier	67-56-1	0.15	1.0	0.0013635	g	
Substance	3	Benzene, 1,2-dimethyl-	Supplier	95-47-6	0.05	1.0	4.545E-4	g	