






2.0mm pitch/Disconnectable Crimp style connectors



This is a thin, low-profile 2.0mm pitch connector 8.0mm in height after mounting and 4.5mm in width. It is designed to meet the demand for high-density connection of internal wires to printed circuit boards. It is compact, highly reliable and low in cost.

- Reliable contact
- Fully shrouded header
- Printed circuit board retention mechanism
- Surface mount model (SMT)

## Specifications —

- Current rating: 2A AC, DC (AWG #24)
- Voltage rating: 100V AC, DC
- Temperature range: -25°C to +85°C (including temperature rise in applying electrical current)
- Contact resistance: Initial value/ 10m  $\Omega$  max. After environmental testing/ 20m  $\Omega$  max.
- Insulation resistance: 1,000M  $\Omega$  min.
- Withstanding voltage: 800V AC/ minute
- Applicable wire: AWG #32 to #24
- Applicable PC board thickness: 0.8 to 1.6mm
- \* Compliant with RoHS.
- \* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.
- \* Contact JST for details.

## Standards -

Recognized E60389


Side entry type

Street LR20812

A R75087

Through-hole type (viewed from soldering side)

Top entry type




should be larger. The dimensions above should serve as a guideline. Contact JST for details.

<del>0</del>

Note: 1. Tolerances are non-cumulative: ±0.05mm for all centers. 2. Hole dimensions differ according to the kind of PC board and piercing method. If PC boards made of hard material are used, the hole dimensions

## SMT type (viewed from component side)




Note: 1. Tolerances are non-cumulative: ±0.05mm for all centers. 2. The dimensions above should serve as a guideline. Contact JST for details.

**ISSCO17.01(PH)** Downloaded from Arrow.com.

9.6 7.6


96

SM4 type Side entry type



# PH CONNECTOR

## Contact



Model No.		Q'ty /					
	mm <sup>2</sup>	AWG #	Insulation O.D. (mm)	reel			
SPH-002T-P0.5S	0.05~0.22	30~24	0.9~1.5	8,000			
SPH-002T-P0.5L	0.08~0.22	28~24	0.8~1.5				
SPH-004T-P0.5S	0.032~0.08	32~28	0.5~0.9	10,000			
Material and Finish							

Phosphor bronze, tin-plated (reflow treatment)

#### **RoHS compliance**

Note:


Contact JST for gold-plated products.
SPH-002T-P0.5L is low-insertion force type contact, for easier insertion/

withdrawal, which would be less resistant to the vibration. The crimp height is different from the standard.

3. Contact JST for details.

#### Note: \*Strip-crimp applicator

### Housing



<For reference> As the color identification, the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact


ex. PHR-2-00

(blank)...natural (white)

- BK...black R...red TR...tomato red BL...blue Y...yellow
- L...lemon yellow M...green D...orange N...brown
- P...purple PK...pink H...gray LE...light blue

FY...vivid yellow DPK...dark pink

### Through-hole type shrouded header



Circuits	Model No.	Dimensio	Q'ty / box	
		A	В	
2	PHR-2	2.0	5.8	1,000
3	PHR-3	4.0	7.8	1,000
4	PHR-4	6.0	9.8	1,000
5	PHR-5	8.0	11.8	1,000
6	PHR-6	10.0	13.8	1,000
7	PHR-7	12.0	15.8	1,000
8	PHR-8	14.0	17.8	1,000
9	PHR-9	16.0	19.8	1,000
10	PHR-10	18.0	21.8	1,000
11	PHR-11	20.0	23.8	1,000
12	PHR-12	22.0	25.8	1,000
13	PHR-13	24.0	27.8	1,000
14	PHR-14	26.0	29.8	1,000
15	PHR-15	28.0	31.8	1,000
16	PHR-16	30.0	33.8	1,000

#### PA 66, UL94V-0, natural (white)

RoHS compliance

	Model No.		Dimensions (mm)		Q'ty / box	
Circuits	Top entry type	Side entry type	А	В	Top entry type	Side entry type
2	B2B-PH-K-S	S2B-PH-K-S	2.0	5.9	1,000	1,000
3	B3B-PH-K-S	S3B-PH-K-S	4.0	7.9	1,000	1,000
4	B4B-PH-K-S	S4B-PH-K-S	6.0	9.9	1,000	500
5	B5B-PH-K-S	S5B-PH-K-S	8.0	11.9	1,000	500
6	B6B-PH-K-S	S6B-PH-K-S	10.0	13.9	1,000	500
7	B7B-PH-K-S	S7B-PH-K-S	12.0	15.9	500	500
8	B8B-PH-K-S	S8B-PH-K-S	14.0	17.9	500	250
9	B9B-PH-K-S	S9B-PH-K-S	16.0	19.9	500	250
10	B10B-PH-K-S	S10B-PH-K-S	18.0	21.9	500	250
11	B11B-PH-K-S	S11B-PH-K-S	20.0	23.9	500	250
12	B12B-PH-K-S	S12B-PH-K-S	22.0	25.9	400	250
13	B13B-PH-K-S	S13B-PH-K-S	24.0	27.9	250	250
14	B14B-PH-K-S	S14B-PH-K-S	26.0	29.9	250	250
15	B15B-PH-K-S	S15B-PH-K-S	28.0	31.9	250	200
16	B16B-PH-K-S	S16B-PH-K-S	30.0	33.9	250	200

#### Material and Finish

Post: Brass, copper-undercoated, tin-plated (reflow treatment) Wafer: PA 66, UL94V-0, natural (white)

**RoHS compliance** This product displays (LF)(SN) on a label.

<For reference> As the color identification, the following alphabet shall be put in the underlined part.

For availability, delivery and minimum order quantity, contact

- ex. B2B-PH-K-<u>oo</u>
  - S...natural (white)

K...black R...red TR...tomato red E...blue Y...yellow L...lemon yellow M...green


O...orange N...brown P...purple PK...pink H...gray


LE...light blue FY...vivid yellow (blank)...ivory




## **PH CONNECTOR**

## Through-hole type shrouded header (Low insertion force type)







Circuits	Model No.		Dimensions (mm)		Q'ty / box	
	Top entry type	Side entry type	Α	В	Top entry type	Side entry type
2	B2B-PH-KL	S2B-PH-KL	2.0	5.9	1,000	1,000
3	B3B-PH-KL	S3B-PH-KL	4.0	7.9	1,000	1,000
4	B4B-PH-KL	S4B-PH-KL	6.0	9.9	1,000	500
5	B5B-PH-KL	S5B-PH-KL	8.0	11.9	1,000	500
6	B6B-PH-KL	S6B-PH-KL	10.0	13.9	1,000	500
7	B7B-PH-KL	S7B-PH-KL	12.0	15.9	500	500
8	B8B-PH-KL	S8B-PH-KL	14.0	17.9	500	250
9	B9B-PH-KL	S9B-PH-KL	16.0	19.9	500	250
10	B10B-PH-KL	S10B-PH-KL	18.0	21.9	500	250
11	B11B-PH-KL	S11B-PH-KL	20.0	23.9	500	250
12	B12B-PH-KL	S12B-PH-KL	22.0	25.9	400	250
13	B13B-PH-KL	S13B-PH-KL	24.0	27.9	250	250
14	B14B-PH-KL	S14B-PH-KL	26.0	29.9	250	200
15	B15B-PH-KL	S15B-PH-KL	28.0	31.9	250	200
16	B16B-PH-KL	S16B-PH-KL	30.0	33.9	250	200

Post: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Wafer: PA 66, UL94V-0, gray

RoHS compliance This product displays (LF)(SN) on a label.


As the color identification, <For reference> the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact

ex. B2B-PH-KL-oo

(blank)...gray

R...red E...blue S...natural (white)

### SMT type shrouded header



	Model No.			Dimensions (mm)			
Circuits	Top entry type	Side entry type	А		Q'ty/		
	Top entry type			Top entry type	Side entry type	reel	
2	B2B-PH-SM4-TB	S2B-PH-SM4-TB	2.0	7.95	7.9	1,00	
3	B3B-PH-SM4-TB	S3B-PH-SM4-TB	4.0	9.95	9.9	1,00	
4	B4B-PH-SM4-TB	S4B-PH-SM4-TB	6.0	11.95	11.9	1,00	
5	B5B-PH-SM4-TB	S5B-PH-SM4-TB	8.0	13.95	13.9	1,00	
6	B6B-PH-SM4-TB	S6B-PH-SM4-TB	10.0	15.95	15.9	1,00	
7	B7B-PH-SM4-TB	S7B-PH-SM4-TB	12.0	17.95	17.9	1,00	
8	B8B-PH-SM4-TB	S8B-PH-SM4-TB	14.0	19.95	19.9	1,00	
9	B9B-PH-SM4-TB	S9B-PH-SM4-TB	16.0	21.95	21.9	1,00	
10	B10B-PH-SM4-TB	S10B-PH-SM4-TB	18.0	23.95	23.9	1,00	
11	B11B-PH-SM4-TB	S11B-PH-SM4-TB	20.0	25.95	25.9	1,00	
12	B12B-PH-SM4-TB	S12B-PH-SM4-TB	22.0	27.95	27.9	1,00	
13	B13B-PH-SM4-TB	S13B-PH-SM4-TB	24.0	29.95	29.9	1,00	
14	B14B-PH-SM4-TB	S14B-PH-SM4-TB	26.0	31.95	31.9	1,00	
15	B15B-PH-SM4-TB	S15B-PH-SM4-TB	28.0	33.95	33.9	1,00	
16	B16B-PH-SM4-TB		30.0	35.95	-	1,00	

#### Material and Finish

Post: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Wafer: PA, UL94V-0, natural (ivory) Solder tab: Brass, copper-undercoated, tin-plated (reflow treatment)

**RoHS compliance** This product displays (LF)(SN) on a label. Note: Contact JST for the top entry type headers with suction cap.

<For reference> As the color identification,

the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact

ex. B2B-PH-SM4-<u>oo</u>-TB


(blank)...natural (ivory)

- R...red E...blue M...green L...lemon yellow
- K...black DPK...dark pink



# PH CONNECTOR

## Unit for wire-to-wire connection



Circuits	Model No.	Dimensio	Q'ty/box			
Circuito	Widder No.	А	В	Q Uy/ DOX		
2	B2B-PH-TW-S	2.0	5.9	24,000		
3	B3B-PH-TW-S	4.0	7.9	9,000		
4	B4B-PH-TW-S	6.0	9.9	9,000		
5	B5B-PH-TW-S	8.0	11.9	9,000		
6	B6B-PH-TW-S	10.0	13.9	9,000		
8	B8B-PH-TW-S	14.0	17.9	6,000		
10	B10B-PH-TW-S	18.0	21.9	4,500		
11	B11B-PH-TW-S	20.0	23.9	4,500		
12	B12B-PH-TW-S	22.0	25.9	4,500		
Material and Finish						

Material and Finish

Post: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Wafer: PA 66, UL94V-0, natural

**RoHS compliance** This product displays (LF)(SN) on a label.