


PRODUCT NO.  
SEE TABLE



Copyright FCI

FCI  
FCIconnect.com

| ltr | ec'n no  | dr  | date     | surface  | tolerance | projection | product family |
|-----|----------|-----|----------|----------|-----------|------------|----------------|
| N   | V61633   | EPK | 9/17/90  | ISO 1902 | ISO 406   |            | CARD CONN.     |
| P   | V70994   | JM  | 10/19/97 | ISO 1902 | ISO 1701  |            |                |
| R   | V02523   | AZ  | 10/24/00 | ISO 1902 | ISO 1701  |            |                |
| S   | V21783   | CGD | 11/18/02 | ISO 1902 | ISO 1701  |            |                |
| T   | M05-0113 | MHT | 6/14/05  | ISO 1902 | ISO 1701  |            |                |
| U   | M07-0133 | MHT | 2/26/07  | ISO 1902 | ISO 1701  |            |                |
| V   | M08-0233 | MHT | 8/14/08  | ISO 1902 | ISO 1701  |            |                |

| ltr | ec'n no  | dr  | date     | surface  | tolerance | projection | product family |
|-----|----------|-----|----------|----------|-----------|------------|----------------|
| N   | V61633   | EPK | 9/17/90  | ISO 1902 | ISO 406   |            | CARD CONN.     |
| P   | V70994   | JM  | 10/19/97 | ISO 1902 | ISO 1701  |            |                |
| R   | V02523   | AZ  | 10/24/00 | ISO 1902 | ISO 1701  |            |                |
| S   | V21783   | CGD | 11/18/02 | ISO 1902 | ISO 1701  |            |                |
| T   | M05-0113 | MHT | 6/14/05  | ISO 1902 | ISO 1701  |            |                |
| U   | M07-0133 | MHT | 2/26/07  | ISO 1902 | ISO 1701  |            |                |
| V   | M08-0233 | MHT | 8/14/08  | ISO 1902 | ISO 1701  |            |                |



title  
GUIDE PIN  
CARD CONNECTOR

product family  
CARD CONN.

projection  
INCH/MM

scale  
4:1

dwg no  
66527

sheet 1 of 6

Product Customer Drawing

A3



| PRODUCT NO.<br>NOTE 9 | NO. OF<br>POS. | A DIM       | B DIM        | INSUL.<br>PLUG | SPECIAL |
|-----------------------|----------------|-------------|--------------|----------------|---------|
| 66527-001             |                |             | UNAVAILABLE  |                |         |
| -002                  | 2X2            | 1.00/2.54   | .458/11.63   | NO             |         |
| -003                  | 2X3            | 2.00/5.08   | .558/14.17   |                |         |
| -004                  | 2X4            | .360/7.62   | .658/16.71   |                |         |
| -005                  | 2X5            | .400/10.16  | .758/19.25   |                |         |
| -006                  | 2X6            | .500/12.70  | .858/21.79   |                |         |
| -007                  | 2X7            | .600/15.24  | .958/24.33   |                |         |
| -008                  | 2X8            | .700/17.78  | 1.058/26.87  |                |         |
| -009                  | 2X9            | .800/20.32  | 1.158/29.41  |                |         |
| -010                  | 2X10           | .900/22.86  | 1.258/31.95  |                |         |
| -011                  | 2X11           | 1.000/25.4  | 1.358/34.49  |                |         |
| -012                  | 2X12           | 1.100/27.94 | 1.458/37.03  |                |         |
| -013                  | 2X13           | 1.200/30.48 | 1.558/39.57  |                |         |
| -014                  | 2X14           | 1.300/33.02 | 1.658/42.11  |                |         |
| -015                  | 2X15           | 1.400/35.56 | 1.758/44.65  |                |         |
| -016                  | 2X16           | 1.500/38.10 | 1.858/47.19  |                |         |
| -017                  | 2X17           | 1.600/40.64 | 1.958/49.73  |                |         |
| -018                  | 2X18           | 1.700/43.18 | 2.058/52.27  |                |         |
| -019                  | 2X19           | 1.800/45.72 | 2.158/54.81  |                |         |
| -020                  | 2X20           | 1.900/48.26 | 2.258/57.35  |                |         |
| -021                  | 2X21           | 2.000/50.80 | 2.358/59.89  |                |         |
| -022                  | 2X22           | 2.100/53.34 | 2.458/62.43  |                |         |
| -023                  | 2X23           | 2.200/55.88 | 2.558/64.97  |                |         |
| -024                  | 2X24           | 2.300/58.42 | 2.658/67.51  |                |         |
| -025                  | 2X25           | 2.400/60.96 | 2.758/70.05  |                |         |
| -026                  | 2X26           | 2.500/63.50 | 2.858/72.59  |                |         |
| -027                  | 2X27           | 2.600/66.04 | 2.958/75.13  |                |         |
| -028                  | 2X28           | 2.700/68.58 | 3.058/77.67  |                |         |
| -029                  | 2X29           | 2.800/71.12 | 3.158/80.21  |                |         |
| -030                  | 2X30           | 2.900/73.66 | 3.258/82.75  |                |         |
| -031                  | 2X31           | 3.000/76.20 | 3.358/85.29  |                |         |
| -032                  | 2X32           | 3.100/78.74 | 3.458/87.83  |                |         |
| -033                  | 2X33           | 3.200/81.28 | 3.558/90.37  |                |         |
| -034                  | 2X34           | 3.300/83.82 | 3.658/92.91  |                |         |
| -035                  | 2X35           | 3.400/86.36 | 3.758/95.45  |                |         |
| -036                  | 2X36           | 3.500/88.90 | 3.858/97.99  |                |         |
| -037                  | 2X37           | 3.600/91.44 | 3.958/100.53 |                |         |
| -038                  | 2X38           | 3.700/93.98 | 4.058/103.07 |                |         |
| -039                  | 2X39           | 3.800/96.52 | 4.158/105.61 |                |         |
| 66527-040             | 2X40           | 3.900/99.06 | 4.258/108.15 | NO             |         |

OBS  
OBS  
OBS

|             |  |                                       |  |                     |  |            |  |                          |  |
|-------------|--|---------------------------------------|--|---------------------|--|------------|--|--------------------------|--|
| mat'l. code |  | surface                               |  | tolerance           |  | projection |  | product family           |  |
| ---         |  | ISO 1302                              |  | ISO 406<br>ISO 1701 |  |            |  | CARD CONN.               |  |
| ISO 1302    |  | tolerances unless otherwise specified |  | XX F10/FH3          |  | INCH/MM    |  | title                    |  |
| V           |  | angles                                |  | linear              |  | scale 4:1  |  | GUIDE PIN                |  |
|             |  | C.DAILY                               |  | 11/18/02            |  | 11/18/02   |  | CARD CONNECTOR           |  |
|             |  | H.SUNDY                               |  | 11/18/02            |  | 11/18/02   |  | sheet 3 of 6             |  |
|             |  | H.SUNDY                               |  | 11/18/02            |  | 11/18/02   |  | size A3                  |  |
|             |  | H.SUNDY                               |  | 11/18/02            |  | 11/18/02   |  | Product Customer Drawing |  |
| Sheet       |  | revision                              |  |                     |  |            |  |                          |  |
| Index       |  | Sheet                                 |  |                     |  |            |  |                          |  |

| PRODUCT NO.<br>NOTE 9 | NO. OF<br>POS. | A DIM        | B DIM        | INSUL.<br>PLUG | SPECIAL |
|-----------------------|----------------|--------------|--------------|----------------|---------|
| 66527-041             | 2X41           | 4.000/101.60 | 4.358/110.69 | NO             |         |
| -042                  | 2X42           | 4.100/104.14 | 4.458/113.23 |                |         |
| -043                  | 2X43           | 4.200/106.68 | 4.558/115.77 |                |         |
| -044                  | 2X44           | 4.300/109.22 | 4.658/118.31 |                |         |
| -045                  | 2X45           | 4.400/111.76 | 4.758/120.85 |                |         |
| -046                  | 2X46           | 4.500/114.30 | 4.858/123.39 |                |         |
| -047                  | 2X47           | 4.600/116.84 | 4.958/125.93 |                |         |
| -048                  | 2X48           | 4.700/119.38 | 5.058/128.47 |                |         |
| -049                  | 2X49           | 4.800/121.92 | 5.158/131.01 |                |         |
| -050                  | 2X50           | 4.900/124.46 | 5.258/133.55 |                |         |
| -051                  | 2X51           | 5.000/127.00 | 5.358/136.09 |                |         |
| -052                  | 2X52           | 5.100/129.54 | 5.458/138.63 |                |         |
| -053                  | 2X53           | 5.200/132.08 | 5.558/141.17 |                |         |
| -054                  | 2X54           | 5.300/134.62 | 5.658/143.71 |                |         |
| -055                  | 2X55           | 5.400/137.16 | 5.758/146.25 |                |         |
| -056                  | 2X56           | 5.500/139.70 | 5.858/148.79 |                |         |
| -057                  | 2X57           | 5.600/142.24 | 5.958/151.33 |                |         |
| -058                  | 2X58           | 5.700/144.78 | 6.058/153.87 |                |         |
| -059                  | 2X59           | 5.800/147.32 | 6.158/156.41 |                |         |
| -060                  | 2X60           | 5.900/149.86 | 6.258/158.95 |                |         |
| -061                  | 2X61           | 6.000/152.40 | 6.358/161.49 |                |         |
| -062                  | 2X62           | 6.100/154.94 | 6.458/164.03 |                |         |
| -063                  | 2X63           | 6.200/157.48 | 6.558/166.57 |                |         |
| -064                  | 2X64           | 6.300/160.02 | 6.658/169.11 |                |         |
| 66527-065             | 2X65           | 6.400/162.56 | 6.758/171.65 | NO             |         |
| 066-THRU              |                |              |              |                |         |
| 100                   |                |              |              |                |         |

OBSOLETE

|             |  |                                     |  |                     |  |            |  |                          |  |
|-------------|--|-------------------------------------|--|---------------------|--|------------|--|--------------------------|--|
| mat'l. code |  | surface                             |  | tolerance           |  | projection |  | product family           |  |
| ecr no      |  | ISO 1302                            |  | ISO 406<br>ISO 1701 |  |            |  | CARD CONN.               |  |
| date        |  | refer to unless otherwise specified |  | XX F10/FH3          |  | INCH/MM    |  | title                    |  |
| date        |  | linear                              |  | XXX F106/2X113      |  | scale 4:1  |  | GUIDE PIN                |  |
| date        |  | C.DAILY                             |  | XXX F1000/XXX4061   |  | scale 4:1  |  | CARD CONNECTOR           |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | dwg no                   |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | 66527                    |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | sheet 4 of 6             |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | size                     |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | A3                       |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | type                     |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | Product Customer Drawing |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | sheet                    |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | revision                 |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | sheet                    |  |
| date        |  | H.SUNDY                             |  | 11/18/02            |  | scale 4:1  |  | index                    |  |

