# Surface Mount Multilayer Ceramic Chip Capacitors (SMD MLCCs) **High Voltage COG Dielectric, 500 – 3,000 VDC** (Commercial Grade)




#### **Overview**

KEMET's High Voltage surface mount MLCCs in COG dielectric feature a 125°C maximum operating temperature and are considered "stable." The Electronics Industries Alliance (EIA) characterizes COG dielectric as a Class I material. Components of this classification are temperature compensating and are suited for resonant circuit applications or those where Q and stability of capacitance characteristics are required. COG exhibits no change in capacitance with respect to time and voltage and boasts a negligible change in capacitance with reference to ambient temperature. Capacitance change is limited to ±30ppm/°C from -55°C to +125°C.

These devices exhibit low ESR at high frequencies and find conventional use as snubbers or filters in applications such as switching power supplies and lighting ballasts. Their exceptional performance at high frequencies has made high voltage MLCC's the preferred dielectric choice of design engineers worldwide. In addition to their use in power supplies, these capacitors are widely used in industries related to automotive(hybrid), telecommunications, medical, military, aerospace, semiconductors and test/diagnostic equipment.

#### In addition to Commercial Grade, Automotive Grade devices are available which meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.



## Ordering Information

С	1210	C	332	J	C	G	Α	С	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance <sup>1</sup>	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish <sup>2</sup>	Packaging/ Grade (C-Spec)
	0603 0805 1206 1210 1808 1812 1825 2220 2225 2824 3040 3640 4540	C = Standard	Two significant digits and number of zeros.	$B = \pm 0.10 \text{ pF}$ $C = \pm 0.25 \text{ pF}$ $D = \pm 0.5 \text{ pF}$ $F = \pm 1\%$ $G = \pm 2\%$ $J = \pm 5\%$ $K = \pm 10\%$ $M = \pm 20\%$	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	G = COG	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table"

<sup>1</sup> Additional capacitance tolerance offerings may be available. Contact KEMET for details. <sup>2</sup> Additional termination finish options may be available. Contact KEMET for details.

© KEMET Electronics Corporation • KEMET Tower • One East Broward Boulevard Fort Lauderdale, FL 33301 USA • 954-766-2800 • www.kemet.com



## Packaging C-Spec Ordering Options Table

Packaging Type <sup>1</sup>	Packaging/Grade Ordering Code (C-Spec)
Bulk Bag/Unmarked	Not required (Blank)
7" Reel/Unmarked	TU
13" Reel/Unmarked	7411 (EIA 0603 and smaller case sizes) 7210 (EIA 0805 and larger case sizes)
7" Reel/Unmarked/2 mm pitch <sup>2</sup>	7081
13" Reel/Unmarked/2 mm pitch <sup>2</sup>	7082

<sup>1</sup> Default packaging is "Bulk Bag". An ordering code C-Spec is not required for "Bulk Bag" packaging.

<sup>1</sup> "Bulk Bag" packaging option is not available for case sizes larger than 2225 (5664 Metric).

<sup>1</sup> The terms "Marked" and "Unmarked" pertain to laser marking option of capacitors. All packaging options labeled as "Unmarked" will contain capacitors that have not been laser marked. The option to laser mark is not available on these devices. For more information see "Capacitor Marking".

<sup>2</sup> The 2 mm pitch option allows for double the packaging quantity of capacitors on a given reel size. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".

#### **Benefits**

- Operating temperature range of -55°C to +125°C
- Lead (Pb)-Free, RoHS and REACH compliant
- EIA 0603, 0805, 1206, 1210, 1808, 1812, 1825, 2220, 2225, 2824, 3040, 3640 and 4540 case sizes
- DC voltage ratings of 500 V, 630 V, 1 KV, 1.5 KV, 2 KV, 2.5 KV and 3 KV
- Capacitance offerings ranging from 1pF to 0.150µF
- Available capacitance tolerances of ±0.10pF, ±0.25pF, ±0.5pF, ±1%, ±2%, ±5%, ±10% and ±20%
- · No piezoelectric noise
- · Extremely low ESR and ESL
- High thermal stability
- · High ripple current capability

- Preferred capacitance solution at line frequencies and into the MHz range
- No capacitance change with respect to applied rated DC voltage
- Negligible capacitance change with respect to temperature from -55°C to +125°C
- · No capacitance decay with time
- · Non-polar device, minimizing installation concerns
- Automotive (AEC-Q200) grade available
- 100% pure matte tin-plated termination finish allowing for excellent solderability
- SnPb plated termination finish option available upon request (5% Pb minimum)


## **Applications**

Typical applications include switch mode power supplies (input filters, resonators, tank circuits, snubbed circuits, output filters), high voltage coupling and DC blocking, lighting ballasts, voltage multiplier circuits, DC/DC converters and coupling capacitors in Ćuk converters. Markets include power supply, LCD fluorescent backlight ballasts, HID lighting, telecom equipment, industrial and medical equipment/control, LAN/WAN interface, analog and digital modems, and automotive.

2



# **Dimensions – Millimeters (Inches)**



EIA Size Code	Metric Size Code	L Length	W Width	T Thickness	B Bandwidth	S Separation Minimum	Mounting Technique
0603	1608	1.60 (0.063) ±0.15 (0.006)	0.80 (0.032) ±0.15 (0.006)		0.35 (0.014) ±0.15 (0.006)	0.70 (0.028)	
0805	2012	2.00 (0.079) ±0.20 (0.008)	1.25 (0.049) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)	0.75 (0.030)	Solder Wave or Solder Reflow
1206	3216	3.20 (0.126) ±0.20 (0.008)	1.60 (0.063) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)		
1210	3225	3.20 (0.126) ±0.20 (0.008)	2.50 (0.098) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)		
1808	4520	4.70 (0.185) ±0.50 (0.020)	2.00 (0.079) ±0.20 (0.008)		0.60 (0.024) ±0.35 (0.014)		
1812	4532	4.50 (0.177) ±0.30 (0.012)	3.20 (0.126) ±0.30 (0.012)		0.60 (0.024) ±0.35 (0.014)		
1825	4564	4.50 (0.177) ±0.30 (0.012)	6.40 (0.252) ±0.40 (0.016)	See Table 2 for Thickness	0.60 (0.024) ±0.35 (0.014)		
2220	5650	5.70 (0.224) ±0.40 (0.016)	5.00 (0.197) ±0.40 (0.016)	-	0.60 (0.024) ±0.35 (0.014)	N/A	Solder Reflow
2225	5664	5.60 (0.220) ±0.40 (0.016)	6.40 (0.248) ±0.40 (0.016)	_	0.60 (0.024) ±0.35 (0.014)		Only
2824	7260	7.10 (0.280) ±0.40 (0.016)	6.10 (0.240) ±0.40 (0.016)	_	1.27 (0.050) ±0.40 (0.016)		
3040	7610	7.60 (0.300) ±0.40 (0.016)	10.20 (0.402) ±0.40 (0.016)		1.27 (0.050) ±0.40 (0.016)	-	
3640	9210	9.10 (0.358) ±0.40 (0.016)	10.20 (0.402) ±0.40 (0.016)		1.27 (0.050) ±0.40 (0.016)		
4540	-	11.40 (0.449) ±0.40 (0.016)	10.20 (0.402) ±0.40 (0.016)		1.27 (0.050) ±0.40 (0.016)		



#### **Qualification/Certification**

Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance & Reliability.

#### **Environmental Compliance**

Lead (Pb)-free, RoHS, and REACH compliant without exemptions (excluding SnPb termination finish option).

## **Electrical Parameters/Characteristics**

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +125°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±30 ppm/°C
Aging Rate (Maximum % Capacitance Loss/Decade Hour)	0%
<sup>1</sup> Dielectric Withstanding Voltage (DWV)	See Dielectric Withstanding Voltage (DWV) Table (5 ±1 seconds and charge/discharge not exceeding 50 mA)
<sup>2</sup> Dissipation Factor (DF) Maximum Limit at 25°C	0.1%
<sup>3</sup> Insulation Resistance (IR) Limit at 25°C	1,000 megohm microfarads or 100 GΩ (500 VDC applied for 120 ±5 seconds at 25°C)

<sup>1</sup>DWV is the voltage a capacitor can withstand (survive) for a short period of time. It exceeds the nominal and continuous working voltage of the capacitor.

<sup>2</sup>Capacitance and dissipation factor (DF) measured under the following conditions:

1 MHz ±100 kHz and 1.0 Vrms ±0.2 V if capacitance  $\leq$  1,000 pF

1 kHz ±50 Hz and 1.0 Vrms ±0.2 V if capacitance > 1,000 pF

<sup>3</sup>To obtain IR limit, divide  $M\Omega$ - $\mu$ F value by the capacitance and compare to G $\Omega$  limit. Select the lower of the two limits.

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

4



## **Dielectric Withstanding Voltage (DWV)**

EIA Case Size	500V	630V	≥ 1000V
0603		130% of rated voltage	
0805		< 620pF 150% of rated voltage ≥ 620pF 130% of rated voltage	
1206		< 5.1nF 150% of rated voltage ≥ 5.1nF 130% of rated voltage	
1210	150% of rated voltage	< 7.5nF 150% of rated voltage ≥ 7.5nF 130% of rated voltage	120% of rated voltage
1808		<ul> <li>&lt; 5.1nF 150% of rated voltage</li> <li>≥ 5.1nF 130% of rated voltage</li> </ul>	
1812		< 12nF 150% of rated voltage ≥ 12nF 130% of rated voltage	
≥1825		150% of rated voltage	

## **Post Environmental Limits**

H	ligh Temperatu	re Life, Biase	d Humidity, Mois	ture Resistanc	e
Dielectric	Rated DC Voltage	Capacitance Value	Dissipation Factor (Maximum %)	Capacitance Shift	Insulation Resistance
COG	All	All	0.5	0.3% or ±0.25 pF	10% of Initial Limit



## Table 1A - Capacitance Range/Selection Waterfall (0603 - 1808 Case Sizes)

		Case	Siz	ze/	/Se	erie	es	C	)60	BC	C	)80	5C		<b>C</b> 1	1200	6C			<b>C</b> 1	1210	C				C	1808	BC		
	Сар	V	oltag	je C	ode	9		C	В	D	C	В	D	C	В	D	F	G	С	В	D	F	G	С	В	D	F	G	z	н
Capacitance	Code	Rated	l Vol	tag	e (V	/DC)		500	630	1000	500	630	1000	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000	2500	3000
			apad			e	-					1	-	P		ct Av	ailab	ility a		hip T	hick	ness	Code	s			-			(-)
1.0 - 9.1 pF*	109 - 919*	BCC	<u>Tole</u>	ran	ce						DG	DG	DG		See	lable	e 2 fo	r Chi	p i hi	ckne	ss Di	mens	ions	LB	LB	LB	LB	LB	LB	LB
10 pF - 47pF*	109 - 919		F	G	J	к	м				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
11 pF	110		F		J		м				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
12 pF	120		F	G	J		м				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
13 pF	130		F		J	K					DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
15 pF	150		F	G	J		М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
16 pF	160		F		J		М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
18 pF	180		F	G	J		м				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
20 pF	200		F	G	J		М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
22 pF	220		F	G	J		М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
24 pF	240		F	-	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
27 pF	270		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
30 pF	300		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
33 pF	330		F	G	J	K	м				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
36 pF	360		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
39 pF	390		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
43 pF	430		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
47 pF	470		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FΜ	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
51 pF	510		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
56 pF	560		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FΜ	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
62 pF	620		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
68 pF	680		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
75 pF	750		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	EF	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
82 pF	820		F	G	J	K	М				DG	DG	DG	ED	ED	ED	ED	EF	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
91 pF	910		F	_	J	K	М				DG	DG	DG	ED	ED	ED	ED	EF	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
100 pF	101		F	G	J	K	М	CG	CG	CG	DG	DG	DG	ED	ED	ED	ED	EF	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LC	LB
110 pF	111		F	-	J		М	CG	CG	CG	DG	DG	DG	ED	ED	ED	ED	EG	FM	FM	FΜ	FM	FM	LB	LB	LB	LB	LB	LC	LB
120 pF	121		F	G	J		М	CG	CG	CG	DG	DG	DG	ED	ED	ED	ED	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LB	LC	LB
130 pF	131		F	G	J		М	CG	CG	CG	DG	DG	DG	ED	ED	ED	ED	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LB	LC	LC
150 pF	151		F	G	J	_	M	CG	CG	CG	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LB	LC	LC
160 pF	161		F		J		M	CG	CG	CG	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	LC
180 pF	181		F	G	J	K	М	CG	CG	CG	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	LC
200 pF	201		F	G	J	K	M	CG	CG	CG	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	
220 pF	221		F	G	J	K	M	CG	CG	CG	DG	DG	DG	ED	ED	ED	EG	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	
240 pF	241		F	_	J	K	M	CG	CG		DG	DG	DG	ED	ED	ED	EG	EG	FG	FG	FG	FM	FM	LA	LA	LA	LB	LC	LC	
270 pF	271		F	G	J		М	CG	CG		DG	DG	DG	ED	ED	ED	EG	EG	FG	FG	FG	FK	FK	LA	LA	LA	LB	LC	LC	
300 pF	301		F	G	J		M	CG	CG		DG	DG	DN	ED	ED	EF	EG		FG	FG	FG	FK	FK	LA			LB	LC	LC	
330 pF	331		F	G	J		M	CG	CG		DG	DG	DN	ED	ED	EF	EG		FG	FG	FG	FK	FK				LB	LC	LC	
360 pF	361		F	G	J		M	CG	CG		DG	DG DG	DN DN	ED	ED ED	EF EF	EG EG		FG	FG	FG FG	FK FK	FS FS				LB LB	LA	LC LC	
390 pF 430 pF	391 431		F	-	J		M	CG CG	CG CG		DG DG	DG	DN	ED ED	ED	EF	EG		FG FG	FG FM	FG	FK	FS	LA LA	LA LB	LA LB	LB	LA LA	LC	
	431 471		F			K	M M	CG	CG		DG	DG	DP	ED	ED	EF	EG		FG	FM	FM	FS	FS	LA	LB	LB	LC	LA		
470 pF 510 pF	511		F	-	J		M	CG	CG		DG	DG	DP	ED	ED	EG	EG		FG	FM	FM	FS	FS	LA	LB	LB	LC	LA		
560 pF	561		F	G	J		M	CG	CG		DG	DG	DP	ED	ED	EG	EG		FG	FM	FM	FS	FS	LA	LB	LB	LC	LB		
620 pF	621		F	G	J	K	M	CG	CG		DG	DG	DG	ED	ED	EG	10		FG	FM	FM	FS	FS	LA	LB	LB	LA	LC		
680 pF	681		F	G	J	K	M	CG	CG		DG	DG	DG	ED	ED	EG			FG	FM	FM	FS	FS	LB	LB	LB	LA	LC		
750 pF	751		F		J		M	00	00		DG	DG	DG	ED	EF	EG			FG	FM	FM	FM		LB	LB	LB	LA			
820 pF	821		F	G	J		M				DG	DG	DG	ED	EF	EG			FG	FM	FM	FM		LB	LB	LB	LA			
910 pF	911		F		J		м				DN	DN		ED	EF	EG			FM	FM	FM	FY		LB	LB	LB	LA			
1,000 pF	102		F		J		М				DN	DN		ED	EF	EG			FM	FM	FM	FY		LB	LB	LB	LB			
1,100 pF	112			_		K					DN	DN		EF	EG	ED			FM	FK	FK	FS		LC	LC	LC	LB			
		Rateo	_			_		500	630	1000	500	630	1000	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000	2500	3000
Capacitance	Cap Code		oltag				-	ى د	B	≓ D	C C	B	→	C C	B	₽ D	₩ F	5 G	C C	B	∓ D	<del>≈</del> F	R G	C B D E G					Ri Z	т Н
	Coue	Cas					_		0603			0805		-		1206			-		- 1210						1808			

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91) KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).

These products are protected under US Patents 7,172,985 and 7,670,981, other patents pending, and any foreign counterparts.

© KEMET Electronics Corporation • KEMET Tower • One East Broward Boulevard Fort Lauderdale, FL 33301 USA • 954-766-2800 • www.kemet.com



#### Table 1A – Capacitance Range/Selection Waterfall (0603 – 1808 Case Sizes) cont'd

		0	Ca	se	S	iz	e/	S	eri	es	; (	C0	60	3C	(	:08	805	5C		C	120	6 <b>C</b>			С	121	OC				С	180	<b>8C</b>		
	Сар	Г		v	olt	age	e C	ode	e			C	В	D	С		В	D	C	В	D	F	G	С	В	D	F	G	С	В	D	F	G	Z	н
Capacitance	Code	F	R	ate	d V	olt	age	e (\	/DC	;)	993	n	630	1000	500		630	1000	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000	2500	3000
		Г		C	ap	aci	ita	nc	е		Τ								F				bility						es						
				•	To	ler	an	ce	_											See	Tabl	<u>e 2 fo</u>	or Chi	p Thi	ckne	ss Di	mens	sions							
1,200 pF	122					F	G	J	K	:   N	1				D		DN		EF	EG	ED			FM	FK	FK	FS		LC	LC	LC	LC			
1,300 pF	132					F	G	J	K	.   N	1				D	1   1	DN		EF	EG	ED			FM	FS	FS			LC	LC	LC	LC			
1,500 pF	152					F	G	J	K	.   N	1				DF	ו י	DP		EF	EG	ED			FK	FS	FS			LC	LC	LC	LC			
1,600 pF	162					F	G	J	K	N	1				DF	וו	DP		EF	EG	ED			FK	FS	FS			LC	LC	LC				
1,800 pF	182	Γ	T			F	G	J	K	N	1				DO	; I	DG		EF	EG	EF			FK	FS	FS			LC	LC	LC				
2,000 pF	202					F	G	J	K	N	1				DO	;   I	DG		EG	EB	EF			FK	FL	FS			LC	LA	LB				
2,200 pF	222					F	G	J	K	I N	Л				D	3   I	DG		EG	EB	EF			FK	FL	FS			LC	LA	LB				
2,400 pF	242					F	G	J	ĸ	N	۸İ				D	;   I	DG		EG	EB	EG			FS	FL	FS			LC	LA	LB				
2,700 pF	272	L				F	G	J	ĸ		۸İ				D	;   I	DG		EG	EB	EG			FS	FL	FS			LC	LA	LC				
3,000 pF	302	L				F	G	J	K	_	1								EB	EB				FS	FL	FF			LA	LA	LA				
3,300 pF	332					F	G	J	K		A L								EB	EB				FS	FM	FG			LA	LA	LA				
3,600 pF	362					F	G	J	K		1								EC	EC				FL	FM	FG			LA	LB	LA				
3,900 pF	392					F	G	J	K		1								EC	EC				FL	FY	FL			LA	LB	LA				
4,300 pF	432					F	G	J	K										ED	ED				FM	FY	FL			LA	LC	LA				
4,700 pF	472	Г	Т	T	_	F	G	J	K	_					1	T			ED	ED				FM	FY	FM			LA	LC	LB			-	_
5,100 pF	512					F	G	Ĵ	K										EE	EE				FY	FS	FM			LA	LB	LB				
5,600 pF	562					F	G	J	K										EF	EF				FY	FS	FM			LB	LC	LC				
6,200pF	622					F	G	J	K										EF	EF				FY	FE	FY			LC	LC	LC				
6,800pF	682					F	G	J	K										EG	EG				FY	FE	FY			LC	LC	LC				
7,500pF	752	Ŀ			_	F	G		K	_									EG	EG				FS	FF				LA	LA	20				
8,200 pF	822					F	G	J.	K										EG	EG				FS	FF				LA	LA					
9,100 pF	912					F	G		K										EG	EG				FF	FF				LA	LA					
10,000 pF	103					F	G	J	K										EH	EH				FG	FG				LA	LA					
12,000 pF	123					F	G		K															FG	FG				LA	LA					
15,000 pF	153	L	T		_	F	G	J	K	_														FM	FM				LB	LB					
18,000 pF	183					F	G	J	K															FM	FM				LC	LC					
22,000 pF	223					F	G	J																FY	FY										
		t	R	ate			-			_		3	630	1000	200		630	1000	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000	2500	3000
Capacitance	Cap	┝					_	<u>`</u>		<u> </u>	_	-			-	-					-	-		-			1	1						1	1
Sapacitance	Code	╞				age					+		B	D	C		В	D	C	B	D	F	G	C	B	D	F	G	C B D F G Z				H		
			(	Cas	es	SIZ	e/S	sei	ries	;		C	0603	SC .	1	CU	805	U		C	1206	UC		1	(	:1210	U		C1808C						

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91) KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).

These products are protected under US Patents 7,172,985 and 7,670,981, other patents pending, and any foreign counterparts.

Downloaded from Arrow.com.

7



## Table 1B - Capacitance Range/Selection Waterfall (1812 - 2225 Case Sizes)

		Ca	ise S	Size/	/Seri	es			C1	81:	2 <b>C</b>					C1	82	5 <b>C</b>					C2	22	<b>0C</b>					C2	22	5C		
Capacitance	Сар		Vol	tage C	ode		С	в	D	F	G	z	н	С	В	D	F	G	z	н	С	в	D	F	G	z	н	С	в	D	F	G	z	н
	Code	F	Rated N	Voltag	e (VDC	:)	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000
				pacita				-	-	-	2	2	e		Proc	luct	Ava	ilab	ility	and	Chi	ip T	hick	nes	s Co	odes			-	-	-	2	0	
10 pF - 47pF*	100 - 470*	F	G	oleran	Ce K	М	GK	θK	CK	θK	GK	C.K.	CK	HG					r Ch нс			JK	JK	_	1sio JK	ns JK	JK	KF	KF	KF	KF	KF	KF	K
11 pF	110	F	G	J	K	M	GK				GK											JK	JK	JK	JK	JK		KF	KF	KF	KF	KF		K
12 pF	120	F	G	J	К	М	GK				GK											JK	JK	JK	JK	JK		KF	KF	KF	KF	KF	KF	ĸ
13 pF	130	F	G	J	К	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	K
15 pF	150	F	G	J	K	M	GK	GK	GK		GK										JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	K
16 pF	160	F	G	J	K	M	GK	GK	GK		GK										JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	K
18 pF	180	F	G	J	K	M	GK	GK	GK		GK											JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	K
20 pF	200	F	G	J	K	M	GK	GK	GK	GK					HG						JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	ŀ
22 pF	220	F	G	J	K	M	GK	GK	GK		GK											JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	ŀ
24 pF	240	F	G	J	K	M	GK	_		GK					HG					_		JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	k
27 pF	270	F	G	J	K	M	GK				GK											JK	JK	JK	JK	JK	JK		KF	KF	KF	KF	KF	ł
30 pF	300 330	F	G G	J	K K	M	GK GK				GK GK				HG						JK	JK JK	JK JK	JK JK	JK JK	JK JK		KF KF	KF KF	KF KF	KF KF	KF KF	KF KF	k
33 pF		r c	G	J	K	M															JK	JK	JK	JK	JK	JK				KF	KF	KF	KF	ľ
36 pF 39 pF	360 390	F	G	J	K	M	GK GK	GK GK			GK GK											JK JK	JK JK	JK JK	JK JK	JK JK	JK JK	KF	KF KF	KF	KF	KF	KF	r F
43 pF	430	F	G	J	K	M	GK	GK	GK		GK								HG	_	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	ł
43 pr 47 pF	470	F	G	J	ĸ	M	GK	GK	GK		GK										JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	ŀ
51 pF	510	F	G	J	ĸ	M	GK	GK			GK										JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	ŀ
56 pF	560	F	G	Ĵ	ĸ	M	GK	GK	GK		GK											JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	li
62 pF	620	F	G	Ĵ	ĸ	M	GK	GK	GK	GK					HG						JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	
68 pF	680	F	G	J	K	M		GK			GK		_				_	_	_	_	_	JK	JK	JK	JK	JK	JK		KF	KF	KF	KF	KF	
75 pF	750	F	G	J	к	м					GK										JK	JK	JK	JK	JK	JK	JK		KF	KF	KF	KF	KF	
82 pF	820	F	G	J	К	М	GK				GK											JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	1
91 pF	910	F	G	J	К	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	
100 pF	101	F	G	J	K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	ł
110 pF	111	F	G	J	K	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	
120 pF	121	F	G	J	K	M	GK	GK	GK	GK	GK							HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	1
130 pF	131	F	G	J	K	M	GK	GK	GK	GK					HG				HG		JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	
150 pF	151	F	G	J	K	M	GK	GK	GK		GK										JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	
160 pF	161	F	G	J	K	M	GK	GK			GK				_				HG	_	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	1
180 pF	181	F	G	J	K	M	GK				GK											JK	JK	JK	JK	JK		KF	KF	KF	KF	KF	KF	
200 pF	201	F	G	J	K	M	GH	GH			GH										JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	
220 pF	221	F	G G	J	K K	M	GH	GH			GH											JK JK	JK JK	JK JK	JK JK	JK JK	JK		KF	KF	KF	KF KE	KF	
240 pF 270 pF	241 271	F	G	JJ	K	M	GH GH	GH GH	GH GH		GH GH										JK JK	JK	JK	JK	JK	JK	JK	KE KE	KE KE	KE KE	KE KE	KE	KE KE	
300 pF	301	F	G	J	K	M	GH	GH	GH		GH								HE	_	JK	JK	JK	JK	JK	JK	JK	KE	KE	KE	KE	KE		1
330 pF	331	F	G	J	K	M	GH				GH								HE		JE	JE	JE	JE	JE	JK		KE		KE	KE	KE		
360 pF	361	F	G	J	K	M	GK	GK	GK		GH								HE		JE	JE	JE	JE	JE	JK	JK	KE	KE	KE	KE	KE		
390 pF	391	F	G	J	ĸ	M	GK				GK											JE		JE	JE	JK		KE			KE	KE		
430 pF	431	F	G	J	K	M	GK				GK				HE							JE		JE	JE	JK		KE			KE	KE		
470 pF	471	F	G	J	K	М	_				GK				HE							JE	JE	JE	JE		JK		KF	KF	KF		KE	
510 pF	511	F	G	J	K	M					GH				HE						JK	JK	JK	JK	JK	JK		KF	KF	KF	KF		KE	
560 pF	561	F	G	J	К	М					GH				HE						JK	JK	JK	JK	JK	JK		KF	KF	KF	KF		KE	
620 pF	621	F	G	J	К	М	GH	GH	GH	GK	GH	GM		HE	HE	HE	HE	HG	HE	ΗK	JK	JK	JK	JK	JK	JK	JL	KF	KF	KF	KF	KE	KF	
680 pF	681	F	G	J	К	М					GH	GO			HE					ΗK		JE		JK	JK	JK	JL	KF	KF	KF	KF	KE	KF	ĺ
750 pF	751	F	G	J	K	М				GK					HE						JE	JE	JE	JK	JK	JK		KE				KE		
820 pF	821	F	G	J	K	М				GK					HE							JE			JK	JK		KE					KF	
910 pF	911	F	G	J	K	M	î	_		GH		2	0		HE					2	_	JK	JK			JK	JN	KE	KE	KE			KF	
	6	Rated Voltage (VDC)					500	630	1000	1500	2000	2500	3000	500	630	1000				3000	500	630	1000	1500	2000	2500	3000			1000	1500	2000		
Capacitance	Cap Code		Vol	tage C	ode		C	В	D	F	G	Z	н	C	В	D	F	G	Z	н	H C B D F G Z					Н	C	В	D	F	G	Z		
		Case Size/Series							C	1812	20					C1	825	C					C2	220	)C					C2	2225	5C		

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91) KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).

These products are protected under US Patents 7,172,985 and 7,670,981, other patents pending, and any foreign counterparts.

© KEMET Electronics Corporation • KEMET Tower • One East Broward Boulevard Fort Lauderdale, FL 33301 USA • 954-766-2800 • www.kemet.com 8



## Table 1B - Capacitance Range/Selection Waterfall (1812 - 2225 Case Sizes) cont'd

		Ca	ise S	Size/	'Seri	es			C1	81	2C					C1	82	5C					C2	22	0C					C2	22	5C		
Capacitance	Сар		Vol	tage C	ode		с	В	D	F	G	Z	н	с	В	D	F	G	z	н	С	в	D	F	G	z	Н	С	В	D	F	G	z	н
oapacitance	Code	R	ated \	Voltag	e (VDC	;)	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000
				pacita oleran					-	-	7	7	e		Proc	luct	Ava	ilab	ility	and	l Ch	ip T knes	hick	nes	s Co	des				-	-	~	2	<u> </u>
1,000 pF	102	F	G	J	K	М	GH	GH	GH	GH	GM			HE	_	HE	_	_	_	<u>ו עו</u>	JE	JK	JK	JK	JK	JK	JN	KE	KE	KE	KF	KE	KF	KJ
1,100 pF	112	F	G	J	К	М	GH	GK	GK	GH	GO			HE	HE	HE	HG	HG	HJ		JE	JK	JK	JK	JK	JK		KE	KE	KE	KF	KF	KF	
1,200 pF	122	F	G	J	K	М	GH	GK	GK	GH	GO			HE	HE	HE	HG	HG	HJ		JE	JK	JK	JK	JK	JL		KE	KE	KE	KF	KF	KF	
1,300 pF	132	F	G	J	K	М	GH	GK	GK	GH	GO			HE	HE	HE	HG	HE	HJ		JE	JK	JK	JK	JE	JL		KE	KE	KE	KF	KF	КН	
1,500 pF	152	F	G	J	K	М	GK	GK	GK	GK	GO			HE	HE	HE	HG	HE	HK		JE	JK	JK	JK	JE	JL		KE	KE	KE	KF	KF	KH	
1,600 pF	162	F	G	J	К	М	GK	GK	GK	GK				HE	HG	HG	HG	HG	ΗK		JE	JK	JK	JK	JE	JL		KE	KE	KE	KF	KE	KH	
1,800 pF	182	F	G	J	К	М	GK	GK	GK	GM				HE	HG	HG	HG	HG			JE	JK	JK	JK	JE	JN		KE	KE	KE	KF	KE	KH	
2,000 pF	202	F	G	J	K	М	GK	GK	GK	GM				HE	HG	HG	HE	HJ			JE	JK	JK	JE	JK			KE	KE	KE	KF	KE	KJ	
2,200 pF	222	F	G	J	K	М	GK	GK	GK	GO				HE	HG	HG	HE	HJ			JE	JK	JK	JE	JK			KE	KE	KE	KF	KF	KJ	
2,400 pF	242	F	G	J	K	М	GK	GH	GK	GO				HE	HG	HG	HE	HJ			JK	JK	JK	JE	JL			KE	KE	KE	KE	КН		
2,700 pF	272	F	G	J	К	М	GΚ	GH	GK	GO				HE	HG	HG	HE	нк			JK	JK	JK	JE	JL			KE	KE	KE	KE	кн		
3,000 pF	302	F	G	J	К	М	GΚ	GH	GK					НG	HG	HG	HE	нк			JK	JK	JK	JE	JL			KE	KE	KE	KE	кн		
3,300 pF	332	F	G	J	K	М	GK	GH	GK					HG	HG	HG	HG				JK	JK	JK	JK	JN			KE	KE	KE	KE	KJ		
3,600 pF	362	F	G	J	К	М	GK	GH	GM					HG	HG	HG	HG				JK	JK	JK	JK	JN			KE	KF	KF	KF	КJ		
3,900 pF	392	F	G	J	К	М	GΚ	GH	GM					HG	HG	HG	HJ				JK	JK	JK	JK	JN			KE	KF	KF	KF	KJ		
4,300 pF	432	F	G	J	K	М	GH	GH	GO					HG	HG	HG	HJ				JK	JK	JK	JK				KE	KF	KF	KF			
4,700 pF	472	F	G	J	K	М	GH	GH	GO					HG	HG	HG	HJ				JK	JK	JK	JL				KE	KF	KF	KH			
5,100 pF	512	F	G	J	K	М	GH	GK	GO					HG	HE	HG	ΗK				JK	JK	JK	JL				KE	KF	KF	KH			
5,600 pF	562	F	G	J	К	М	GH	GK	GO					НG	HE	HG	нк				JK	JK	JK	JN				KE	KF	KF	кн			
6,200pF	622	F	G	J	К	м	GH	GK	GH					НG	HE	HG					JK	JE	JE	JN				KE	KF	KF	КJ			
6,800pF	682	F	G	J	К	м	GH	GM	GH					НG	HE	HJ					JK	JE	JK	JN				KE	KF	KF	КJ			
7,500pF	752	F	G	J	к	м	GН	GМ	GK					НG	HE	НJ					JK	JE	JK					KF	KE	KF				
8,200 pF	822	F	G	J	K	M	GK		GK					HG	HE						JK	JE	JL					KF	KE	KF				
9,100 pF	912	F	G	J	K	M	GM		GM					HE		HK					JE	JE	JL					KF		KH				
10,000 pF	103	F	G	J	K	M	GM							HE		НК					JE	JE	JL					KF	KE	КН				
12,000 pF	123	F	G	J	K	M	GO	GH						HE	HG						JE	JK	JN					KE	KE	КН				
15,000 pF	153	F	G	Ĵ	K	M	GO								HJ						JE	JL	•						KF	KJ				
18,000 pF	183	F	G	J	K	M	GH														JE	JL						_	KH					
22,000 pF	223	F	G	J	ĸ	M	GH							HJ							JK	JN							KJ					
27,000 pF	273	F	G	Ĵ	ĸ	M	GK							HJ							JL	JN							KJ					
33,000 pF	333	F	G	Ĵ	ĸ	M	GM							нк							JN	0						КН						
39,000 pF	393	F	G	Ĵ	ĸ	M	<b> </b>																					KJ						
		R	hote (	netio	e (VDC	3	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000	500	630	1000	1500	2000	2500	3000
	Cap		-		· ·	<i>''</i>	с С	تف B	₽ D	₽ F	20 20 20	Z 25	<u></u> В	ъ Б	فت B	9 D	۲۲ F	ନ୍ଥ G	22 Z	<u></u> Я	5 2	فت B	9 D	₽ F	ק G	Z 25	<u></u> В	ы С	فت B	9 D	5 F	5 6	Z 25	<u></u> В Н
Capacitance	Code		Case	tage C				D		F 1812		2	п		D	-	۲ 825	-	2	•	ι υ	D	-	r 2220	-	2	п	U.	D	-	F 2225		2	

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91) KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).

These products are protected under US Patents 7,172,985 and 7,670,981, other patents pending, and any foreign counterparts.



## Table 1C - Capacitance Range/Selection Waterfall (2824 - 4540 Case Sizes)

			ise Siz Series			C	2824	IC			C	3040	C			C	3640	C			C	4540	C	
Capacitance	Сар	Vo	ltage Co	de	C	В	D	F	G	C	В	D	F	G	C	В	D	F	G	C	В	D	F	G
	Code	vo	Rated Itage (V	DC)	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000
		Ca	apacitan Foleranc	ce										ity and Chip 1							1	1	1	
10 - 2,000 pF	100 - 202	J	K	М																				
2,200 pF	222	J	K	M	TA	TA	TA	TA	TA															
2,400 pF 2,700 pF	242 272	J	K K	M	ТА	ТА	ТА	TA	ТА															
2,700 pF 3,000 pF	302	J	K	M		IA	IA	IA	IA															
3,300 pF	332	J	K	M	TA	TA	TA	TA	TA	QB	QB	QB	QB	QB										
3,600 pF	362	J	K	M																				
3,900 pF	392	J	К	M	TA	TA	TA	TA	ТВ	QB	QB	QB	QB	QB	MA	MA	MA	MA	MA					
4,300 pF	432	J	к	М																				
4,700 pF	472	J	K	M	TA	TA	TA	ТВ	TB	QB	QB	QB	QB	QB	MA	MA	MA	MA	MA	SA	SA	SA	SA	SA
5,100 pF 5,600 pF	512 562	J	K K	M	ТА	ТА	TA	тв	тс	ОВ	QB	QB	QB	ОВ	ма	МА	ма	ма	МА	SA	SA	SA	SA	SA
6,200 pF	622	J	K	M		IA	IA	ID	10	ŲВ	QВ	QВ	ŲБ	ŲВ	MA	WA	MA	MA	MA	SA	SA	SA	SA	SA
6,800 pF	682	Ĵ	ĸ	M	ТА	TA	TA	ТВ		ОВ	QB	OB	QB	QC	МА	МА	MA	MA	MA	SA	SA	SA	SA	SA
7,500 pF	752	J	к	м																				
8,200 pF	822	J	К	М	TA	TA	TA	TC		QB	QB	QB	QC	QC	MA	MA	MA	MA	MB	SA	SA	SA	SA	SA
9,100 pF	912	J	K	М																				
10,000 pF	103	J	K	M	TA	TA	TA			QB	QB	QB	QC	QD	MA	MA	MA	MA	MB	SA	SA	SA	SA	SB
12,000 pF 15,000 pF	123 153	J J	K K	M	TA TA	TA TA	TA TB			QB QB	QB QB	QB QB	QD OD		MA MA	MA	MA MA	MB MB	MB MC	SA SA	SA SA	SA SA	SA SB	SB SB
18,000 pF	183	J	K	M	TA	TA	TB			QB	QB	QB	QD		MA	MA	MA	MC	WIC	SA	SA	SA	SB	SC
22,000 pF	223	Ĵ	ĸ	M	TA	ТВ	TC			QB	QB	QC			MA	MA	MA			SA	SA	SA	SB	
27,000 pF	273	J	к	м	TA	ΤВ				QB	QB	QC			MA	MA	MA			SA	SA	SA	SC	
33,000 pF	333	J	К	М	TB	TB				QB	QC	QC			MA	MA	MB			SA	SA	SA		
39,000 pF	393	J	K	M	TB	TC				QB	QC	QD			MA	MA	MB			SA	SA	SB		
47,000 pF	473	J	K K	M	TB TC					QB	QC				MA	MB	MC			SA	SA	SB SB		
56,000 pF 68,000 pF	563 683	J J	K	M						QC QC	QD OD				MA MB	MB MC				SA SA	SA SB	SB		
82,000 pF	823	J	K	M						QC					MB	IVIC				SA	SB	30		
0.1 µF	104	J	ĸ	M						QD					мс					SB	SC			
0.12 µF	124	J	K	М											мс					SB				
0.15 µF	154	J	K	М					-					-					-	SC				5
		Rated	Voltage	(VDC)	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000
Capacitance	Cap	Va	ltage Co	de	C	В	D	F	G	С	В	D	F	G	C	В	D	F	G	С	В	D	F	G
	Code	Case	e Size/S	eries		C	2824	С			C	3040	С			C	3640	С			C	4540	С	-

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91) KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).

These products are protected under US Patents 7,172,985 and 7,670,981, other patents pending, and any foreign counterparts.



## Table 2A – Chip Thickness/Tape & Reel Packaging Quantities

Code		Thickness ±	i uper e	)uantity	i lastic (	Quantity
	Size	Range (mm)	7" Reel	13" Reel	7" Reel	13" Reel
CG	0603	0.80 ± 0.10*	4,000	15,000	0	0
DN	0805	0.78 ± 0.10*	4,000	15,000	0	0
DP	0805	0.90 ± 0.10*	4,000	15,000	0	0
DG	0805	1.25 ± 0.15	0	0	2,500	10,000
EB	1206	0.78 ± 0.10	4,000	10,000	4,000	10,000
EC ED	1206	0.90 ± 0.10	0	0	4,000	10,000
ED EE	1206 1206	1.00 ± 0.10 1.10 ± 0.10	0 0	0 0	2,500 2,500	10,000 10,000
EF	1200	$1.10 \pm 0.10$ $1.20 \pm 0.15$	0	0	2,500	10,000
EG	1206	1.60 ± 0.15	0	0	2,000	8,000
EH	1206	1.60 ± 0.10	0	0	2,000	8,000
FE	1210	1.00 ± 0.10	Ő	Ő	2,500	10,000
FF	1210	1.10 ± 0.10	0	0	2,500	10,000
FG	1210	1.25 ± 0.15	0	0	2,500	10,000
FL	1210	1.40 ± 0.15	0	0	2,000	8,000
FM	1210	1.70 ± 0.20	0	0	2,000	8,000
FY	1210	2.00 ± 0.20	0	0	2,000	8,000
FK	1210	2.10 ± 0.20	0	0	2,000	8,000
FS	1210	2.50 ± 0.30	0	0	1,000	4,000
LA	1808	1.40 ± 0.15	0	0	1,000	4,000
LB	1808	1.60 ± 0.15	0	0	1,000	4,000
LC	1808	2.00 ± 0.15	0	0	1,000	4,000
GH GK	1812	1.40 ± 0.15	0 0	0 0	1,000	4,000
GM	1812 1812	1.60 ± 0.20 2.00 ± 0.20	0	0	1,000 500	4,000 2,000
GO	1812	2.50 ± 0.20	0	0	500	2,000
HE	1825	1.40 ± 0.15	0	0	1,000	4,000
HG	1825	1.60 ± 0.20	0	0	1,000	4,000
HJ	1825	2.00 ± 0.20	0	0	500	2,000
НК	1825	2.50 ± 0.20	0	0	500	2,000
JE	2220	1.40 ± 0.15	0	0	1,000	4,000
JK	2220	1.60 ± 0.20	0	0	1,000	4,000
JL	2220	2.00 ± 0.20	0	0	500	2,000
JN	2220	2.50 ± 0.20	0	0	500	2,000
KE	2225	1.40 ± 0.15	0	0	1,000	4,000
KF	2225	1.60 ± 0.20	0	0	1,000	4,000
KH	2225	2.00 ± 0.20	0	0	500	2,000
KJ TA	2225	$2.50 \pm 0.20$	0 0	0 0	500 750	2,000
TA	2824 2824	1.40 ± 0.15 2.00 ± 0.20	0	0	300	2,500 2,000
TC	2824	2.50 ± 0.20	0	0	300	2,000
QB	3040	2.30 ± 0.20 1.40 ± 0.15	0	0	500	1,650
QC	3040	$2.00 \pm 0.20$	0	0	500	1,650
QD	3040	$2.50 \pm 0.20$	Ő	0 0	350	1,400
MĂ	3640	1.40 ± 0.15	0	0 0	250	1,550
MB	3640	2.00 ± 0.20	0	0	250	1,550
MC	3640	2.50 ± 0.20	0	0	250	1,000
SA	4540	1.40 ± 0.15	0	0	200	1,500
SB	4540	2.00 ± 0.20	0	0	200	1,500
SC	4540	2.50 ± 0.20	0	0	200	1,500
Thickness	Case	Thickness ±	7" Reel	13" Reel	7" Reel	13" Reel
Code	Size	Range (mm)	Paper C	)uantity	Plastic	Quantity

Package quantity based on finished chip thickness specifications.



#### Table 2B - Bulk Packaging Quantities

Dookogi		Loose Packaging				
Packayi	ng Type	Bulk Bag (default)				
Packagin	g C-Spec <sup>1</sup>	N/	/A²			
Case	Size	Packaging Quantities (	pieces/unit packaging)			
EIA (in)	Metric (mm)	Minimum	Maximum			
0603	1608					
0805	2012		50,000			
1206	3216		50,000			
1210	3225					
1808	4520	1				
1812	4532					
1825	4564	]	20,000			
2220	5650					
2225	5664					

<sup>1</sup> The "Packaging C-Spec" is a 4 to 8 digit code which identifies the packaging type and/or product grade. When ordering, the proper code must be included in the 15th through 22nd character positions of the ordering code. See "Ordering Information" section of this document for further details. Commercial Grade product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging. Contact KEMET if you require a bulk bag packaging option for Automotive Grade products.

<sup>2</sup> A packaging C-Spec (see note 1 above) is not required for "Bulk Bag" packaging (excluding Anti-Static Bulk Bag and Automotive Grade products). The 15th through 22nd character positions of the ordering code should be left blank. All product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging.




#### Table 3 – Chip Capacitor Land Pattern Design Recommendations per IPC-7351

EIA Size Code	Size Size Land Protrusion (mm)				Density Level B: Median (Nominal) Land Protrusion (mm)			Density Level C: Minimum (Least) Land Protrusion (mm)								
oouc	oouc	C	Y	X	V1	V2	C	Y	X	V1	V2	C	Y	X	V1	V2
0603	1608	0.90	1.15	1.10	4.00	2.10	0.80	0.95	1.00	3.10	1.50	0.60	0.75	0.90	2.40	1.20
0805	2012	1.00	1.35	1.55	4.40	2.60	0.90	1.15	1.45	3.50	2.00	0.75	0.95	1.35	2.80	1.70
1206	3216	1.60	1.35	1.90	5.60	2.90	1.50	1.15	1.80	4.70	2.30	1.40	0.95	1.70	4.00	2.00
1210	3225	1.60	1.35	2.80	5.65	3.80	1.50	1.15	2.70	4.70	3.20	1.40	0.95	2.60	4.00	2.90
1808	4520	2.30	1.75	2.30	7.40	3.30	2.20	1.55	2.20	6.50	2.70	2.10	1.35	2.10	5.80	2.40
1812	4532	2.15	1.60	3.60	6.90	4.60	2.05	1.40	3.50	6.00	4.00	1.95	1.20	3.40	5.30	3.70
1825	4564	2.15	1.60	6.90	6.90	7.90	2.05	1.40	6.80	6.00	7.30	1.95	1.20	6.70	5.30	7.00
2220	5650	2.75	1.70	5.50	8.20	6.50	2.65	1.50	5.40	7.30	5.90	2.55	1.30	5.30	6.60	5.60
2225	5664	2.70	1.70	6.90	8.10	7.90	2.60	1.50	6.80	7.20	7.30	2.50	1.30	6.70	6.50	7.00
2824	7260	3.45	1.70	6.60	9.60	7.60	3.35	1.50	6.50	8.70	7.00	3.25	1.30	6.40	8.00	6.70
3040	7610	3.70	1.70	10.70	10.10	11.70	3.60	1.50	10.60	9.20	11.10	3.50	1.30	10.50	8.50	10.80
3640	9210	4.45	1.70	10.70	11.60	11.70	4.35	1.50	10.60	10.70	11.10	4.25	1.30	10.50	10.00	10.80
4540	-	5.60	1.70	10.70	13.90	11.70	5.50	1.50	10.60	13.00	11.10	5.40	1.30	10.50	12.30	10.80

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).

Image below based on Density Level B for an EIA 1210 case size.





## **Soldering Process**

#### **Recommended Soldering Technique:**


- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- · All other EIA case sizes are limited to solder reflow only

#### **Recommended Reflow Soldering Profile:**

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/ J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

Profile Feature	Terminat	ion Finish	
Tomereature	SnPb	100% Matte Sn	
Preheat/Soak			
Temperature Minimum (T <sub>Smin</sub> )	100°C	150°C	
Temperature Maximum (T <sub>Smax</sub> )	150°C	200°C	
Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$	60 – 120 seconds	60 – 120 seconds	
Ramp-Up Rate (T <sub>L</sub> to T <sub>p</sub> )	3°C/second maximum	3°C/second maximum	
Liquidous Temperature $(T_L)$	183°C	217°C	
Time Above Liquidous ( $t_L$ )	60 – 150 seconds	60 – 150 seconds	
Peak Temperature (T <sub>P</sub> )	235°C	260°C	
Time Within 5°C of Maximum Peak Temperature (t <sub>P</sub> )	20 seconds maximum	30 seconds maximum	
Ramp-Down Rate $(T_p \text{ to } T_L)$	6°C/second maximum	6°C/second maximum	
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum	

Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.





## Table 4 – Performance & Reliability: Test Methods and Conditions

Stress	Reference	Test or Inspection Method
Terminal Strength	JIS-C-6429	Appendix 1, Note: Force of 1.8 kg for 60 seconds.
Board Flex	JIS-C-6429	Appendix 2, Note: Standard termination system – 2.0 mm (minimum) for all except 3 mm for COG. Flexible termination system – 3.0 mm (minimum).
		Magnification 50 X. Conditions:
Caldarability	J-STD-002	a) Method B, 4 hours at 155°C, dry heat at 235°C
Solderability	J-51D-002	b) Method B at 215°C category 3
		c) Method D, category 3 at 260°C
Temperature Cycling	JESD22 Method JA-104	1,000 cycles (-55°C to +125°C). Measurement at 24 hours +/-4 hours after test conclusion.
Discolution	MIL-STD-202 Method	Load Humidity: 1,000 hours 85°C/85% RH and 200 VDC maximum. Add 100 K ohm resistor. Measurement at 24 hours +/-4 hours after test conclusion.
Biased Humidity	103	Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours +/-4 hours after test conclusion.
Moisture Resistance	MIL-STD-202 Method 106	t = 24 hours/cycle. Steps 7a and 7b not required. Measurement at 24 hours +/-4 hours after test conclusion.
Thermal Shock	MIL-STD-202 Method 107	-55°C/+125°C. Note: Number of cycles required – 300. Maximum transfer time – 20 seconds. Dwell time – 15 minutes. Air – Air.
High Temperature Life	MIL-STD-202 Method 108	1,000 hours at 125°C (85°C for X5R, Z5U and Y5V) with 1.2 X rated voltage applied.
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC for 1,000 hours.
Vibration	MIL-STD-202 Method 204	5 g's for 20 min., 12 cycles each of 3 orientations. Note: Use 8" X 5" PCB 0.031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz
Mechanical Shock	MIL-STD-202 Method 213	Figure 1 of Method 213, Condition F.
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.


#### Storage and Handling

Downloaded from Arrow.com.

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature–reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.



## Construction



## **Capacitor Marking (Optional):**

Laser marking option is not available on:

- COG, Ultra Stable X8R and Y5V dielectric devices
- · EIA 0402 case size devices

Downloaded from Arrow.com.


- EIA 0603 case size devices with Flexible Termination option.
- KPS Commercial and Automotive grade stacked devices.

These capacitors are supplied unmarked only.



#### **Tape & Reel Packaging Information**

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12, 16 and 24 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.



## Table 5 – Carrier Tape Configuration, Embossed Plastic & Punched Paper (mm)

	Таре	Embosse	d Plastic	Punche	d Paper
EIA Case Size	Size	7" Reel	13" Reel	7" Reel	13" Reel
	(W)*	Pitch	(P <sub>1</sub> )*	Pitch	(P <sub>1</sub> )*
01005 - 0402	8			2	2
0603	8			2/4	2/4 -
0805	8	4	4	4	4
1206 - 1210	8	4	4	4	4
1805 - 1808	12	4	4		
≥ 1812	12	8	8		
2824	16	12	12		
3040 - 4540	24	16	16		
KPS 1210	12	8	8		
KPS 1812 & 2220	16	12	12		
Array 0508 & 0612	8	4	4		

\*Refer to Figures 1 and 2 for W and  $P_1$  carrier tape reference locations. \*Refer to Tables 6 and 7 for tolerance specifications.

#### New 2 mm Pitch Reel Options\*

Packaging Ordering Code (C-Spec)	Packaging Type/Options
C-3190	Automotive grade 7" reel unmarked
C-3191	Automotive grade 13" reel unmarked
C-7081	Commercial grade 7" reel unmarked
C-7082	Commercial grade 13" reel unmarked

\* 2 mm pitch reel only available for 0603 EIA case size.


2 mm pitch reel for 0805 EIA case size under development.

#### Benefits of Changing from 4 mm to 2 mm Pitching Spacing

- · Lower placement costs
- Double the parts on each reel results in fewer reel changes and increased efficiency
- Fewer reels result in lower packaging, shipping and storage costs, reducing waste



## Figure 1 – Embossed (Plastic) Carrier Tape Dimensions



# Table 6 – Embossed (Plastic) Carrier Tape Dimensions

Metric will govern

	Constant Dimensions — Millimeters (Inches)									
Tape Size	D <sub>o</sub>	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	R Reference Note 2	S <sub>1</sub> Minimum Note 3	T Maximum	T1 Maximum		
8 mm					25.0 (0.984)					
12 mm	1.5+0.10/-0.0 (0.059+0.004/-0.0)	1.75±0.10 (0.069±0.004)	4.0±0.10 (0.157±0.004)	2.0±0.05 (0.079±0.002)	30	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)		
16 mm					(1.181)					
24 mm	1.5+0.10/-0.0 (0.059+0.004/-0.0)	1.75±0.10 (0.069±0.004)	4.0±0.10 (0.157±0.004)	2.0±0.10 (0.078±0.003)	30 (1.181)	5 (0.196)	0.250 (0.009)	0.350 (0.013)		
		Varial	ble Dimensions	s – Millimeters	(Inches)					
Tape Size	Pitch	E₂ Minimum	F	P <sub>1</sub>	T <sub>2</sub> Maximum	W Maximum	A <sub>0</sub> ,B <sub>0</sub>	& K <sub>0</sub>		
8 mm	Single (4 mm)	6.25 (0.246)	3.5±0.05 (0.138±0.002)	4.0±0.10 (0.157±0.004)	2.5 (0.098)	8.3 (0.327)				
12 mm	Single (4 mm) & Double (8 mm)	10.25 (0.404)	5.5±0.05 (0.217±0.002)	8.0±0.10 (0.315±0.004)	4.6 (0.181)	12.3 (0.484)	Not	0.5		
16 mm	Triple (12 mm)	14.25 (0.561)	7.5±0.05 (0.138±0.002)	12.0±0.10 (0.157±0.004)	4.6 (0.181)	16.3 (0.642)	NOL	e J		
24 mm	16 mm	22.25 (0.875)	11.5±0.10 (0.452±0.003)	16.0±0.10 (0.629±0.004)	3 (0.118)	24.3 (0.956)				

1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.

2. The tape with or without components shall pass around R without damage (see Figure 6).

3. If S, < 1.0 mm, there may not be enough area for cover tape to be properly applied (see EIA Standard 481 paragraph 4.3 section b).

4. B, dimension is a reference dimension for tape feeder clearance only.

5. The cavity defined by  $A_{0}$ ,  $B_{0}$  and  $K_{0}$  shall surround the component with sufficient clearance that:

(a) the component does not protrude above the top surface of the carrier tape.

(b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.

(c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3).

(d) lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4).


(e) for KPS Series product,  $A_0$  and  $B_0$  are measured on a plane 0.3 mm above the bottom of the pocket.

(f) see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.

@ KEMET Electronics Corporation  $\bullet$  KEMET Tower  $\bullet$  One East Broward Boulevard Fort Lauderdale, FL 33301 USA  $\bullet$  954-766-2800  $\bullet$  www.kemet.com



## Figure 2 – Punched (Paper) Carrier Tape Dimensions



# Table 7 – Punched (Paper) Carrier Tape Dimensions

Metric will govern

Constant Dimensions – Millimeters (Inches)									
Tape Size	D <sub>0</sub>	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	T <sub>1</sub> Maximum	G Minimum	R Reference Note 2		
8 mm	1.5+0.10/-0.0 (0.059+0.004/-0.0)	1.75±0.10 (0.069±0.004)	4.0±0.10 (0.157±0.004)	2.0±0.05 (0.079±0.002)	0.10 (0.004) Maximum	0.75 (0.030)	2 (0.984)		
	Variable Dimensions – Millimeters (Inches)								
Tape SizePitchE2 MinimumF $P_1$ T MaximumW Maximum $A_0 B_0$							$\mathbf{A}_{0}\mathbf{B}_{0}$		
8 mm	Half (2 mm)	6.25	3.5±0.05	2.0±0.05 (0.079±0.002)	1.1	8.3 (0.327)	Note 1		
8 mm	Single (4 mm)	(0.246)	(0.138±0.002)	4.0±0.10 (0.157±0.004)	(0.098)	8.3 (0.327)	Note 1		

1. The cavity defined by  $A_{o'}B_{o}$  and T shall surround the component with sufficient clearance that:

a) the component does not protrude beyond either surface of the carrier tape.

b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.

c) rotation of the component is limited to 20° maximum (see Figure 3).

d) lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4).

e) see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.

2. The tape with or without components shall pass around R without damage (see Figure 6).



#### **Packaging Information Performance Notes**


- 1. Cover Tape Break Force: 1.0 Kg minimum.
- 2. Cover Tape Peel Strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength
8 mm	0.1 to 1.0 newton (10 to 100 gf)
12 and 16 mm	0.1 to 1.3 newton (10 to 130 gf)
24 mm	0.1 to 1.6 newton (10 to 160 gf)


The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.

**3. Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624*.


#### Figure 3 – Maximum Component Rotation



## Figure 4 – Maximum Lateral Movement




#### Figure 5 – Bending Radius





#### **Figure 6 – Reel Dimensions**



Note: Drive spokes optional; if used, dimensions B and D shall apply.


#### Table 8 – Reel Dimensions

Metric will govern


	Constant Dimensions — Millimeters (Inches)								
Tape Size	А	D Minimum							
8 mm	170.0.00								
12 mm	178±0.20 (7.008±0.008)	1.5 (0.059)	13.0+0.5/-0.2 (0.521+0.02/-0.008)	20.2 (0.795)					
16 mm	or 330±0.20		(111111111)	(0					
24 mm	(13.000±0.008)	1.2 (0.047) 13.0 + -0. (0.521 + -0.		21 (0.826)					
	Variable	Dimensions — Millimeter	rs (Inches)						
Tape Size	N Minimum	W <sub>1</sub>	W <sub>2</sub> Maximum	W <sub>3</sub>					
8 mm		8.4+1.5/-0.0 (0.331+0.059/-0.0)	14.4 (0.567)						
12 mm	50 (1.969)	12.4+2.0/-0.0 50 (0.488+0.078/-0.0)		Shall accommodate tape					
16 mm		16.4+2.0/-0.0 (0.646+0.078/-0.0)	22.4 (0.882)	width without interference					
24 mm		25+1.0/-0.0 (0.984+0.039/-0.0)	27.4+1.0/-1.0 (1.078+0.039/-0.039)						



## Figure 7 – Tape Leader & Trailer Dimensions



## Figure 8 – Maximum Camber





#### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

KEMET is a registered trademark of KEMET Electronics Corporation.