


High Isolation Power Transformer

Shaped Core Platform SMD



- Ⓢ Flyback Converter Transformer
- Ⓢ Designed for Broadcom ACPL-32JT and ACPL-302J IGBT Gate Driver
- Ⓢ Compact and cost effective industrial design
- Ⓢ PH9363NL: Basic insulation, 2.8mm creepage
- Ⓢ PH9496NL: Basic insulation, 6.2mm creepage
- Ⓢ PH0416NL: Reinforced insulation, 8.3mm creepage

Electrical Specifications @ 25°C - Operating Temperature -40°C to +125°C

Part Number	Inductance (Pri) ($\mu\text{H} \pm 10\%$)	Primary Current (A MAX)	Inductance (Sec) ($\mu\text{H} \pm 10\%$)	DCR (Sec) (Ω MAX)	Leakage Inductance (Pri) (μH Max)	Turns Ratio	Isolated Voltage (Vrms)
PH9363NL	60	1.0	240	0.60	3.0	1:2	2500 / 1 minute
PH9496NL	52	1.7	332	0.22	1.2	1:2.53	2500 / 1 minute
PH0416NL	43	1.0	172	1.2	2	1:2	5000 / 1 minute




Notes:

1. These transformers are approved by Broadcom to deliver a isolated 18V IGBT drive voltage from a 8V-18V source.
2. Optional Tape & Reel packing can be ordered by adding a "T" suffix to the part number.
3. Other turns ratios and isolation levels available on request.
4. The rated primary current is based on a peak flux density of 220mT.

Mechanical

Schematic



PH9363NL



Weight1.4grams
Tape & Reel500/reel
Tray100/tray

Dimensions: mm

Unless otherwise specified,
all tolerances are ± 0.25




FINAL OUTLINE


High Isolation Power Transformer

Shaped Core Platform SMD




PH9496NL



Mechanical



Schematic




Weight2.6grams
Tape & Reel175/reel
Tray90/tray
Dimensions: mm

Unless otherwise specified,
all tolerances are±0.25




PH0416NL



Mechanical



Schematic



Weight2.6grams
Tape & Reel150/reel
Tray80/tray
Dimensions: mm

Unless otherwise specified,
all tolerances are±0.25

For More Information

Americas - proinfo_power_americas@yageo.com | Europe - proinfo_power_emea@yageo.com | Asia - proinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.