



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER	PACKAGE QUANTITY	MAXIMUM BUNDLE DIAMETER	LENGTH = "L" ±.2 [5]
MLT2DH-L	50	2.0" [50]	18.5" [470]
MLT4DH-L	50	4.0" [101]	28.0" [711]
MLT5DH-L	50	5.0" [127]	34.0" [863]
MLT6DH-Q	50	6.0" [152]	40.0" [1016]



BODY WRAPS AROUND TWO TIMES ENTERING HEAD TWICE (NOT TO SCALE)

- NOTES:
- APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, AND HTMT
 - MINIMUM LOOP TENSILE STRENGTH - 600 LBS. (2669 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
 - BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
 - TOLERANCES:
 .XXX = ±.010 [.25] .XX = ±.02 [.5]
 .X = ±.03 [.8] ANGLES = ±2°
 - MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED EDGES ALONG STRAP BODY



REV							TITLE					
							DOUBLE WRAPPED METAL LOCKING TIE HEAVY SERIES					
							CUSTOMER DRAWING					
							ITEM REVISION NAME	N41142BS/05				
							DATASET FILE NAME	N41142BS/05				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL: 304 STAINLESS STEEL				
05A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01042	.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					
04A	2/12	MIM	RGRO	----	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	----	THIRD ANGLE PROJECTION	DRAWING NUMBER: N41142BS_DC				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							JAMB	2/12	DPN	2:1		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[MLT4DH-L](#) [MLT6DH-Q](#) [MLT5DH-L](#) [MLT2DH-L](#)