



LFS1K0.1505.6W.C.010-6

Conductivity Sensor

For various conductivity measurement applications


Benefits & Characteristics

- Wide conductivity and temperature range
- Fast response time
- Optimal accuracy
- Resistance to various chemicals¹⁾
- Excellent long-term stability
- Integrated RTD for temperature measurement and / or compensation
- Four-electrode measurement²⁾

1) Aggressive media can influence the long-term stability. Chemical resistance of the sensor in the end application must be tested by the customer.

2) Two-electrode configuration available upon request.

Illustration³⁾



3) For actual size, see dimensions.

Technical Data

| | | |
|---|---|----------------------|
| Conductivity range: | 100 $\mu\text{S}/\text{cm}$ to 200 mS/cm (Extended range from 10 $\mu\text{S}/\text{cm}$ to 200 mS/cm possible with cell constant correction) | |
| Cell constant ⁴⁾ : | typical 0.68 cm^{-1} | |
| Nominal resistance: | 1000 Ω at 0 $^{\circ}\text{C}$ | |
| Measurement frequency range: | 100 Hz to 10 kHz | |
| Maximum excitation voltage (between pin 1 and pin 6): | < 0.7 Vpp (electrolysis of the analyte has to be avoided) | |
| Operating temperature range: | -30 $^{\circ}\text{C}$ to +100 $^{\circ}\text{C}$ | |
| Temperature sensor: | Pt1000 | |
| Temperature coefficient (Pt1000): | 3850 ppm/K | |
| Measuring current (Pt1000) ⁵⁾ : | 0.3 mA | |
| Temperature sensor accuracy (dependent on temperature range): | IEC 60751 F0.6 | C (IST AG reference) |
| Dimensions (L x W x H / H2 in mm) | 14.9 \pm 0.3 x 5.5 \pm 0.3 x 0.65 \pm 0.1 / 1.2 \pm 0.3 | |
| Connection: | Pt/Ni-wires, \varnothing 0.2 mm | |

The LFS1505 supersedes the LFS155 which is no longer in production



The LFS1505 supersedes the LFS155 which is no longer in production

Temperature dependence of resistivity: according to IEC 60751:

-50 °C to 0 °C $R(T) = R_0 \times (1 + A \times T + B \times T^2 + C \times (T-100) \times T^3)$

0 °C to 150 °C $R(T) = R_0 \times (1 + A \times T + B \times T^2)$

A = $3.9083 \times 10^{-3} \times \text{°C}^{-1}$

B = $-5.775 \times 10^{-7} \times \text{°C}^{-2}$

C = $-4.183 \times 10^{-12} \times \text{°C}^{-4}$

R_0 = resistance value in Ω at $T = 0 \text{ °C}$


T = temperature in accordance with ITS90

Storage temperature: -20 °C to +100 °C


4) Cell constant is strongly affected by external objects coming close to the front surface of the sensor.

5) Selfheating must be considered

Product Photo



Pin Assignment



| | | | | | |
|-------|-------|-------|-------|-------|-------|
| 1 | 2 | 3 | 4 | 5 | 6 |
| I_2 | V_2 | T_2 | T_1 | V_1 | I_1 |

I: applied current V: measured voltage T: temperature sensor

Order Information

| | | |
|------------------------|--------------|------------------------|
| Description: | Item number: | Former main reference: |
| LFS1K0.1505.6W.C.010-6 | 103857 | 090.00079 |



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved