/ISHAY

DG441, DG442

Vishay Siliconix

Quad SPST CMOS Analog Switches

DESCRIPTION

The DG441, DG442 monolithic quad analog switches are designed to provide high speed, low error switching of analog and audio signals. The DG441 has a normally closed function. The DG442 has a normally open function. Combining low on-resistance (50 Ω , typ.) with high speed (t_{ON} 150 ns, typ.), the DG441, DG442 are ideally suited for upgrading DG201A/202 sockets. Charge injection has been minimized on the drain for use in sample-and-hold circuits.

To achieve high voltage ratings and superior switching performance, the DG441, DG442 are built on Vishay Siliconix's high-voltage silicon-gate process. An epitaxial layer prevents latchup.

Each switch conducts equally well in both directions when on, and blocks input voltages to the supply levels when off.

FEATURES

- Halogen-free according to IEC 61249-2-21 Definition
- Low on-resistance: 50 Ω
- Low leakage: 80 pA
- Low power consumption: 0.2 mW
- Fast switching action t_{ON}: 150 ns
- Low charge injection Q: 1 pC
- DG201A/DG202 upgrades
- TTL/CMOS-compatible logic
- Single supply capability
- Compliant to RoHS Directive 2002/95/EC


BENEFITS


- Less signal errors and distortion
- Reduced power supply requirements
- Faster throughput
- Improved reliability
- Reduced pedestal errors
- Simplifies retrofit
- Simple interfacing

APPLICATIONS

- Audio switching
- Battery powered systems
- Data acquisition
- Hi-Rel systems
- Sample-and-hold circuits
- Communication systems
- Automatic test equipment
- Medical instruments

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION





TRUTH TABLE						
Logic	DG441	DG442				
0	On	Off				
1	Off	On				
Logic "0" ≤ 0.8 V						

Logic "1" ≥ 2.4 V

Document Number: 70053 S11-1066-Rev. J, 30-May-11 www.vishay.com

This document is subject to change without notice. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000 Downloaded from Arrow.com.



COMPLIANT

HALOGEN

FREE

Vishay Siliconix



ORDERING INFORM	DRDERING INFORMATION					
Temp. Range	Package	Part Number				
	16 pip plastic DID	DG441DJ DG441DJ-E3				
- 40 °C to 85 °C	16-pin plastic DIP	DG442DJ DG442DJ-E3				
		DG441DY DG441DY-E3 DG441DY-T1 DG441DY-T1-E3				
	16-pin narrow SOIC	DG442DY DG442DY-E3 DG442DY-T1 DG442DY-T1-E3				

ABSOLUTE MAXIMUM RATINGS						
Parameter		Limit	Unit			
V+ to V-		44				
GND to V-		25				
Digital Inputs ^a , V _S , V _D		(V-) - 2 to (V+) + 2 or 30 mA, whichever occurs first	V			
Continuous Current (any terminal)		30	mA			
Current, S or D (pulsed at 1 ms, 10 % duty cycle)		100	ША			
Storogo Tomporaturo	(AK suffix)	- 65 to 150	°C			
Storage Temperature	(DJ, DY suffix)	- 65 to 125				
	16-pin plastic DIP ^c	450				
Power Dissipation (Package) ^b	16-pin CerDIP ^d	900	mW			
	16-pin narrow SOIC ^d	900	IIIVV			
	LCC-20 ^d	1200				


Notes:

a. Signals on S_X, D_X, or IN_X exceeding V+ or V- will be clamped by internal diodes. Limit forward diode current to maximum current ratings. b. All leads welded or soldered to PC board.

c. Derate 6 mW/°C above 75 °C.

d. Derate 12 mW/°C above 75 °C.

SCHEMATIC DIAGRAM Typical Channel



www.vishay.com 2 Document Number: 70053 S11-1066-Rev. J, 30-May-11

This document is subject to change without notice. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000 Downloaded from Arrow.com.



Vishay Siliconix

SPECIFICATIO	NS ^a (Du	ual Supplie						-		
			Test Conditions			A Suffix - 55 °C to 125 °C		D Suffix - 40 °C to 85 °C		
			Unless Otherwise Specified V+ = 15 V, V- = -15 V			- 55 °C 1	0 125 °C	- 40 °C	to 85 °C	
Parameter		Symbol	$V_{IN} = 2.4 \text{ V}, 0.8 \text{ V}^{\text{f}}$	Temp. ^b	Typ. ^c	Min. ^d	Max. ^d	Min. ^d	Max. ^d	Uni
Analog Switch		,				L				1
Analog Signal Range ^e		V _{ANALOG}		Full		- 15	15	- 15	15	V
Drain-Source On-Resistance		R _{DS(on)}	$I_{S} = -10 \text{ mA}, V_{D} = \pm 8.5 \text{ V}$ V+ = 13.5 V, V- = -13.5 V	Room Full	50		85 100		85 100	
On-Resistance Match	Between	$\Delta R_{DS(on)}$	$I_{S} = -10 \text{ mA}, V_{D} = \pm 10 \text{ V}$ V+ = 15 V, V- = -15 V	Room Full			4 5		4 5	Ω
Switch Off Leakage Cu	urrent	I _{S(off)}	V+ = 16.5, V- = - 16.5 V	Room Full	± 0.01	- 0.5 - 20	0.5 20	- 0.5 - 5	0.5 5	
Content on Leakage Of		I _{D(off)}	$V_D = \pm 15.5 \text{ V}, V_S = \pm 15.5 \text{ V}$	Room Full	± 0.01	- 0.5 - 20	0.5 20	- 0.5 - 5	0.5 5	nA
Channel On Leakage	Current	I _{D(on)}	V+ = 16.5 V, V- = -16.5 V $V_{S} = V_{D} = \pm 15.5 V$	Room Full	± 0.08	- 0.5 - 40	0.5 40	- 0.5 - 10	0.5 10	
Digital Control										
Input Current V _{IN} Low		Ι _{ΙL}	V _{IN} under test = 0.8 V, All Other = 2.4 V	Full	- 0.01	- 500	500	- 500	500	nA
Input Current V _{IN} High		IIH	V _{IN} under test = 2.4 V All Other = 0.8 V	Full	0.01	- 500	500	- 500	500	11/-
Dynamic Characteris	tics									
Turn-On Time		t _{ON}	$R_L = 1 \text{ k}\Omega, C_L = 35 \text{ pF}$	Room	150		250		250	
Turn-Off Time	DG441	t _{OFF}	$V_{S} = \pm 10 V$	Room	90		120		120	ns
	DG442	011	See Figure 2	Room	110		210		210	
Charge Injection ^e		Q	$C_L = 1 \text{ nF}, V_S = 0 \text{ V}$ $V_{gen} = 0 \text{ V}, R_{gen} = 0 \Omega$	Room	- 1					рC
Off Isolation ^e		OIRR	$R_1 = 50 \Omega, C_1 = 5 pF$	Room	60					
Crosstalk (Channel-to- Channel)		X _{TALK}	f = 1 MHz	Room	100					dE
Source Off Capacitance ^e C _S		C _{S(off)}	f = 1 MHz	Room	4					
Drain Off Capacitance	e	C _{D(off)}		Room	4					pF
Channel On Capacitar	nce ^e	C _{D(on)}	V _{ANALOG} = 0 V	Room	16					
Power Supplies										
Positive Supply Curren	nt	l+		Full	15		100		100	
Negative Supply Curre	nt	I-	V+ = 16.5 V, V- = - 16.5 V V _{IN} = 0 or 5 V	Room Full	- 0.0001	- 1 - 5		- 1 - 5		μ4
Ground Current		I _{GND}		Full	- 15	- 100		- 100]

www.vishay.com

3

This document is subject to change without notice. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000 Downloaded from Arrow.com

Vishay Siliconix



SPECIFICATIONS	a (Single S	Supply)							
		Test Conditions Unless Otherwise Specified			-	uffix o 125 °C		uffix to 85 °C	
Parameter	Symbol	V+ = 12 V, V- = 0 V V _{IN} = 2.4 V, 0.8 V ^f	Temp. ^b	Typ. ^c	Min. ^d	Max. ^d	Min. ^d	Max. ^d	Unit
Analog Switch	-					1			
Analog Signal Range ^e	V _{ANALOG}		Full		0	12	0	12	V
Drain-Source On-Resistance	R _{DS(on)}	I _S = - 10 mA, V _D = 3 V, 8 V V+ = 10.8 V	Room Full	100		160 200		160 200	Ω
Dynamic Characteristics									
Turn-On Time	t _{ON}	$R_L = 1 \text{ k}\Omega, C_L = 35 \text{ pF}$	Room	300		450		450	
Turn-Off Time	t _{OFF}	V _S = 8 V See Figure 2	Room	60		200		200	ns
Charge Injection	Q	$C_L = 1nF$, $V_{gen} = 6$ V, $R_{gen} = 0$ Ω	Room	2					рС
Power Supplies									
Positive Supply Current	l+		Full	15		100		100	
Negative Supply Current	I-	V+ = 13.2 V, V- = 0 V V _{IN} = 0 or 5 V	Room Full	- 0.0001	- 1 - 100		- 1 - 100		μA
Ground Current	I _{GND}		Full	- 15	- 100		- 100		

Notes:

a. Refer to PROCESS OPTION FLOWCHART.

b. Room = 25 $^{\circ}$ C, Full = as determined by the operating temperature suffix.

c. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.

d. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet.

e. Guaranteed by design, not subject to production test.


f. V_{IN} = input voltage to perform proper function.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.





Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)









Document Number: 70053 S11-1066-Rev. J, 30-May-11 www.vishay.com

V_S - Source Voltage (V)

Charge Injection vs. Source Voltage

5


This document is subject to change without notice. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Vishay Siliconix



15

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



www.vishay.com 6


Document Number: 70053 S11-1066-Rev. J, 30-May-11

This document is subject to change without notice. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000 Downloaded from Arrow.com.




DG441, DG442 Vishay Siliconix

TEST CIRCUITS




 C_{L} (includes fixture and stray capacitance)




Note:


Figure 2. Switching Time

Logic input waveform is inverted for DG442.





C = 1 mF tantalum in parallel with 0.01 mF ceramic






Figure 5. Off Isolation




Figure 6. Source/Drain Capacitances


Document Number: 70053 S11-1066-Rev. J, 30-May-11


www.vishay.com

This document is subject to change without notice. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Vishay Siliconix

APPLICATIONS





SHA'






Figure 9. Precision-Weighted Resistor Programmable-Gain Amplifier

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?70053.

www.vishay.com 8 Document Number: 70053 S11-1066-Rev. J, 30-May-11


This document is subject to change without notice. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000 Downloaded from Arrow.com.




Package Information Vishay Siliconix

SOIC (NARROW): 16-LEAD


JEDEC Part Number: MS-012









PDIP: 16-LEAD








	MILLIN	IETERS	INC	HES		
Dim	Min	Max	Min	Max		
Α	3.81	5.08	0.150	0.200		
A ₁	0.38	1.27	0.015	0.050		
В	0.38	0.51	0.015	0.020		
B ₁	0.89	1.65	0.035	0.065		
С	0.20	0.30	0.008	0.012		
D	18.93	21.33	0.745	0.840		
Е	7.62	8.26	0.300	0.325		
E ₁	5.59	7.11	0.220	0.280		
e ₁	2.29	2.79	0.090	0.110		
e _A	7.37	7.87	0.290	0.310		
L	2.79	3.81	0.110	0.150		
Q 1	1.27	2.03	0.050	0.080		
S	0.38	1.52	.015	0.060		
ECN: S-0 DWG: 54	3946—Rev. I 182	D, 09-Jul-01				

Application Note 826

Vishay Siliconix



RECOMMENDED MINIMUM PADS FOR SO-16



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index

www.vishay.com 24



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.