









372 Series, TR5 Fuse, Time Lag



Agency Approvals

| Agency | Agency File Number | Ampere Range |
|---|--|--|
|  | 97187 116448 | 0.050A - 4A 5A - 6.3A |
|  | JET1896-31007-2002 | 1A - 5A |
|  | 1410865 | 0.050A - 6.3A |
|  | E67006 | 0.040A - 6.3A |
|  | SU05024-7010 SU05024-7011 SU05024-7006 SU05024-7007 SU05024-7008 SU05024-7009 SU05024-7012 | 0.050 - 0.100A 0.125 - 0.800A 1A - 2.5A 3.15A 4A 5A 6.3A |
|  | CQC07012020855 | 5A - 6.3A |
|  | 2007010207240346 | 0.040A - 4A |

Description

The 372 Series are TR5® Fuses, Time-Lag type, 250V rated fuses, that are designed in accordance to IEC 60127-3.

Features

- Halogen free, Lead-free and RoHS compliant
- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shock safe casing
- Vibration resistant
- Available from 0.040A to 6.3A

Applications

- Battery Chargers
- Consumer electronics
- Power supplies
- Industrial Controllers

Electrical Characteristics

| % of Ampere Rating | Opening Time |
|--------------------|--|
| 150% | 1 Hour, Min. |
| 210% | 2 Minutes, Max. |
| 275% | 400 ms, Min. ; 10 Sec., Max. |
| 400% | 150 ms, Min. ; 3 Sec., Max. |
| 1000% | 20 ms, Min. ; 150 ms, Max. |

Additional Information



Datasheet



Resources



Samples

Electrical Characteristics

| Amp Code | Rated Current | Voltage Rating | Breaking Capacity | Nominal Cold Resistance (Ohms) | Voltage Drop 1.0xI _N max. (mV) | Power Dissipation 1.5xI _N max. (mW) | Melting Integral 10xI _N min. (A ² s) | Agency Approvals | | | | | | |
|----------|---------------|----------------|-------------------|--------------------------------|---|--|--|------------------|---|---|---|-----|---|---|
| | | | | | | | | | | | | | | |
| 0040 | 40mA | 250V | 35A@250VAC | 10.1650 | 900 | 90 | 0.0090 | | | X | | | | |
| 0050 | 50mA | 250V | | 6.4950 | 500 | 70 | 0.0108 | X | X | X | | | X | X |
| 0063 | 63mA | 250V | | 3.8000 | 400 | 80 | 0.0278 | X | X | X | | | X | X |
| 0080 | 80mA | 250V | | 2.8750 | 370 | 100 | 0.0384 | X | X | X | | | X | X |
| 0100 | 100mA | 250V | | 1.7030 | 300 | 110 | 0.0800 | X | X | X | | | X | X |
| 0125 | 125mA | 250V | | 1.3500 | 260 | 120 | 0.1094 | X | X | X | | | X | X |
| 0160 | 160mA | 250V | | 0.7780 | 200 | 130 | 0.1792 | X | X | X | | | X | X |
| 0200 | 200mA | 250V | | 0.5750 | 170 | 140 | 0.3120 | X | X | X | | | X | X |
| 0250 | 250mA | 250V | | 0.4000 | 150 | 150 | 0.4938 | X | X | X | | | X | X |
| 0315 | 315mA | 250V | | 0.2760 | 140 | 160 | 0.3969 | X | X | X | | | X | X |
| 0400 | 400mA | 250V | | 0.2050 | 130 | 170 | 1.4080 | X | X | X | | | X | X |
| 0500 | 500mA | 250V | | 0.1550 | 125 | 180 | 2.0000 | X | X | X | | | X | X |
| 0630 | 630mA | 250V | | 0.1150 | 120 | 200 | 3.0958 | X | X | X | | | X | X |
| 0800 | 800mA | 250V | | 0.1000 | 110 | 220 | 5.7600 | X | X | X | | | X | X |
| 1100 | 1.00A | 250V | | 0.0790 | 110 | 360 | 75.000 | X | X | X | X | | X | X |
| 1125 | 1.25A | 250V | | 0.0550 | 95 | 450 | 13.7500 | X | X | X | X | | X | X |
| 1160 | 1.60A | 250V | | 0.0420 | 95 | 450 | 19.9680 | X | X | X | X | | X | X |
| 1200 | 2.00A | 250V | | 0.0300 | 85 | 600 | 30.0000 | X | X | X | X | | X | X |
| 1250 | 2.50A | 250V | | 0.0220 | 80 | 700 | 35.0000 | X | X | X | X | | X | X |
| 1315 | 3.15A | 250V | | 0.0173 | 80 | 1100 | 77.3955 | X | X | X | X | | X | X |
| 1400 | 4.00A | 250V | 40A / 250 VAC | 0.0129 | 75 | 1200 | 126.4000 | X | X | X | X | X | X | |
| 1500 | 5.00A | 250V | 50A / 250 VAC | 0.0094 | 80 | 1300 | 115.0000 | X | X | X | X | CQC | X | |
| 1630 | 6.30A* | 250V | 50A / 250 VAC | 0.0070 | 58 | 1250 | 138.9150 | X | X | X | | CQC | X | |

1 Per UL, approved breaking capacity is 50 A at 250 V.


* Conducting path min. 0.2 mm²

Notes:


1) 1.00 means the number one with two decimal places. 1,000 means the number one thousand.

2) Resistance is measured at 10% of rated current, 25°C.


Temperature Re-rating Curve



Average Time Current Curves



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

| Wave Parameter | Lead-Free Recommendation |
|---|-----------------------------------|
| Preheat: (Depends on Flux Activation Temperature) | (Typical Industry Recommendation) |
| Temperature Minimum: | 100°C |
| Temperature Maximum: | 150°C |
| Preheat Time: | 60-180 seconds |
| Solder Pot Temperature: | 260°C Maximum |
| Solder Dwell Time: | 2-5 seconds |

Recommended Hand-Solder Parameters:


Solder Iron Temperature: 350°C +/- 5°C
Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

Product Characteristics


| | |
|----------------------------------|---|
| Materials | Base/Cap: Brown Thermoplastic Polyamide PA 6.6, UL 94 V-0 Round Pins: Copper, Tin-plated |
| Lead Pull Strength | 10 N (IEC 60068-2-21) |
| Solderability | 260°C, ≤ 3s. (Wave) 350°C, ≤ 1s. (Soldering Iron) |
| Soldering Heat Resistance | 260°C, 10s. (IEC 60068-2-20) 350°C, 3s. (Soldering Iron) |
| Operating Temperature | -40°C to +85°C (Consider re-rating) |
| Climatic Category | -40°C/+85°C/21 days (IEC 60068-1,-2-1,-2-2,-2-78) |
| Stock Conditions | +10°C to +60°C RH ≤ 75% yearly average, without dew, maximum value for 30 days-95% |
| Vibration Resistance | 24 cycles at 15 min. each (IEC 60068-2-6) 10 - 60 Hz at 0.75 mm amplitude 60 - 2000 Hz at 10G's acceleration |

Dimensions



Long Leads (L=18.8mm)
Short Leads (L=4.3mm)

Part Numbering System



Packaging

| Packaging Option | Packaging Specification | Quantity | Quantity & Packaging Code | Taping Width |
|-------------------|-------------------------|----------|---------------------------|--------------|
| 372 Series | | | | |
| Tape & Ammopack | N/A | 1,000 | 0001 | N/A |
| Short Leads | N/A | 1,000 | 0411 | N/A |
| Short Leads | N/A | 200 | 0431 | N/A |
| 3.3mm Leads | N/A | 1,000 | 0511 | N/A |

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.