

This document was generated on 01/20/2015

# PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 43045-2000

Status: Active

Overview: Micro-Fit 3.0<sup>TM</sup> Connectors

**Description:** Micro-Fit 3.0™ Header, Surface Mount Compatible, Dual Row, Right Angle, with Snap-

in Plastic Peg PCB Lock, 20 Circuits, Tin (Sn) Plating, Glow Wire Compatible

**Documents:** 

3D Model Test Summary TS-43045-001 (PDF)
Drawing (PDF) RoHS Certificate of Compliance (PDF)

Product Specification PS-43045 (PDF) Product Literature (PDF)

# **Agency Certification**

CSA LR19980 TUV R72081037 UL E29179

### General

Product Family PCB Headers Series 43045

Application Power, Wire-to-Board Comments "High Temperature|So

"High Temperature|Square Pin|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for

possible product options."

Overview <u>Micro-Fit 3.0™ Connectors</u>


 Product Literature Order No
 987650-5984

 Product Name
 Micro-Fit 3.0™

 UPC
 800754375016

# **Physical**

Breakaway No Circuits (Loaded) 20 Circuits (maximum) 20 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 **Glow-Wire Compliant** Yes Mated Height 10.29mm Material - Metal **Brass** Material - Plating Mating Tin Material - Plating Termination Tin



# EU RoHS ELV and RoHS Compliant REACH SVHC Not Reviewed Low-Halogen Status

Low-Halogen

**China RoHS** 

# Need more information on product environmental compliance?

Email <u>productcompliance@molex.com</u>
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the <u>Contact Us</u> section for any non-product compliance questions.

## Search Parts in this Series

43045 Series

# **Mates With**

43025 Micro-Fit 3.0™ Receptacle Housing

Material - Resin High Temperature Thermoplastic

Net Weight 3.080/g Number of Rows 2

Orientation Right Angle

**PCB** Locator Yes **PCB** Retention Yes PCB Thickness - Recommended 1.60mm Packaging Type Tray Pitch - Mating Interface 3.00mm Plating min - Mating 0.254µm Polarized to PCB Yes Shrouded Fully Stackable No Surface Mount Compatible (SMC) Yes

Temperature Range - Operating -40°C to +105°C Termination Interface: Style Through Hole

**Electrical** 

Current - Maximum per Contact 5A Voltage - Maximum 600V

**Solder Process Data** 

Duration at Max. Process Temperature (seconds) 30

Lead-free Process Capability SMC & Wave Capable (TH only)

Max. Cycles at Max. Process Temperature 3
Process Temperature max. C 260

**Material Info** 

**Reference - Drawing Numbers** 

Product Specification PS-43045, RPS-43045-003, RPS-43045-004

Sales Drawing SD-43045-001 Test Summary TS-43045-001

This document was generated on 01/20/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION