


**Search**

Home > Products > Fuses > Axial Radial Thru Hole Fuses > TE5 Fuses > 395 > 39501600440

Print

## 39501600440 - 395 Series



Series: 395

[Fuse 395 Datasheet](#)

**Features:**

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shocksafe casing
- Vibration resistant
- Halogen free
- CCCe for China import

Click on part number below for individual TC curve files.

Questions? [Contact Littelfuse Support](#)

**Check Stock**

**Order Samples**

**NEW!**  
Product Selection Guide eCatalog  
[Read Now](#)

**Electronics**  
News and Information  
**SIGN UP NOW**

Feedback

**Electrical Characteristics** | **Technical Resources** | **Environmental Info**

Property (Mouseover for details)	Value
Ampere Rating (A)	0.16
Nominal Melting I <sup>2</sup> T (A <sup>2</sup> sec)	0.0037
Interrupting Rating	100A@125VAC
Min Operating Temp °C	-40
Max Operating Temp (°C)	85
Moisture Sensitivity Level	MIL-STD-202 Method 106
Nominal Power Dissipation (W)	150
Nominal Voltage Drop (mV)	1000
Nominal Cold Resistance (Ohms)	4.285
Opening	Fast-Acting (F)
Package Size	TE5 (8.5x8mm)
VAC (V)	125

**Connect with Littelfuse**

Sign up to receive special offers and news

For more details about how we use your information, check our [Privacy Statement](#).



Mobile Site

**About Littelfuse**

- About Littelfuse
- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

**Explore Littelfuse**

- Capabilities Brochures
- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

**Technical Resources**

- Application Designs
- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents