



D25810K

5 Kilo SDS-Max Dedicated Chipping Hammer

Selling Proposition

- Ideal for light demolition, surface preparation or chiseling grooves and channel openings in brick, masonry and light concrete
- Ergonomic, compact and slim line design maximises control and offers easy access to confined spaces
- Unique dust sealing protection to prevent even the finest dust ingress into the hammer mechanism delivering high durability and extended tool life
- Efficient mechanism delivers impact blows directly to the bit without losses through excessive vibration and rebound dampening reduces stress to the tool
- Soft rubber grip handles improve user comfort lowering fatigue during extended use

Standard Equipment

- Multi-position side handle
- Heavy duty carrying case

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Tool Holder	SDS-Max
Battery chemistry	
Battery Voltage	
Battery Capacity	
Power Input	1050 Watts
Power Output	000 Watt
Impact energy (EPTA 05/2009)	7.1 J
Load Speed	N/A rpm