



Products | Custom Design | Media | Optic Types | Where To Buy | Contact Us

✉ [sales@carclo-optics.com](mailto:sales@carclo-optics.com)

☎ +44 1753 575 011

**LinkedIn**®



## 26.5mm Narrow Spot Frosted TIR (10124)










Part no.	10124
Drawing no.	60423
Family	26.5mm
Type	TIR
Diameter	26.5
Beam	Narrow Spot
Finish	Frosted




## LEDs & Performances

Select LED to view available holders

Manu.	Performance Data	Images	IES/STP
 <a href="#">Avago Jade White</a>	Eff: 86.6 FWHM: 14 Cd/lm: 11.2		<a href="#">View</a>
 <a href="#">Cree XLamp CSP XD16 Cool White</a>	Eff: 84.5 FWHM: 11 Cd/lm: 13.9	 	<a href="#">View</a>
	Eff: 83.4 FWHM: 18		<a href="#">View</a>

[Cree XLamp MH-B White](#)

Cd/lm: 5.9



[Cree XLamp MK-R White](#)

Eff: 79  
FWHM: 21  
Cd/lm: 5.6




[View](#)



[Cree XLamp MX-6 White](#)

Eff: 83.1  
FWHM: 15  
Cd/lm: 9.6



[View](#)



[Cree XLamp XB-D White](#)

FWHM: 10  
Cd/lm: 20.7



[View](#)



[Cree XLamp XHP-50 Gen 2 White](#)

Eff: 82  
FWHM: 20  
Cd/lm: 4.7





[View](#)



[Cree XLamp XHP-50 White](#)

Eff: 83.7  
FWHM: 18  
Cd/lm: 5.24




[View](#)



[Cree XLamp XHP35 HI White](#)

Eff: 83.2  
FWHM: 11  
Cd/lm: 16.1




[View](#)



[Cree XLamp XHP35 White](#)

Eff: 83  
FWHM: 14  
Cd/lm: 9.4




[View](#)



[Cree XLamp XM-L White](#)

Eff: 82.8  
FWHM: 15  
Cd/lm: 11.4




[View](#)



[Cree XLamp XM-L2 White](#)

FWHM: 15  
Cd/lm: 12.5




[View](#)



[Cree XLamp XP-C White](#)

Eff: 84.9  
FWHM: 8  
Cd/lm: 29.6




[View](#)



[Cree XLamp XP-E White](#)

Eff: 83.1  
FWHM: 10  
Cd/lm: 19.9



[View](#)




[Cree XLamp XP-E2 White](#)

FWHM: 9  
Cd/lm: 21.5



[Cree XLamp XP-G White](#)

Eff: 82.3  
FWHM: 12  
Cd/lm: 15.7




[View](#)



[Cree XLamp XP-G2 White](#)

Eff: 84.5  
FWHM: 11  
Cd/lm: 19.8




[View](#)



[Cree XLamp XP-G3 White](#)

Eff: 83  
FWHM: 11  
Cd/lm: 15.64





[View](#)



[Cree XLamp XP-L HI White](#)

Eff: 83.2  
FWHM: 10  
Cd/lm: 18.6





[View](#)



[Cree XLamp XP-L White](#)

Eff: 83.2  
FWHM: 13  
Cd/lm: 12




[View](#)



[Cree XLamp XP-L2 White](#)

Eff: 84  
FWHM: 15  
Cd/lm: 8.1




[View](#)

Eff: 85



[Cree XLamp XQ-A Blue](#)

FWHM: 9  
Cd/lm: 23.1





[View](#)



[Cree XLamp XQ-A Green](#)

Eff: 85  
FWHM: 9  
Cd/lm: 23.1




[View](#)




[Cree XLamp XQ-A Red](#)

Eff: 85  
FWHM: 9  
Cd/lm: 22.6



[View](#)

Eff: 83  
FWHM: 7




[View](#)






Cd/lm: 40.29



[Cree XLamp XQ-A White](#)



Eff: 84.5  
FWHM: 10  
Cd/lm: 18.3





[View](#)

[Cree XLamp XQ-E HI Blue](#)



Eff: 84.5  
FWHM: 10  
Cd/lm: 18.2




[View](#)

[Cree XLamp XQ-E HI Green](#)



Eff: 84.5  
FWHM: 10  
Cd/lm: 18.5




[View](#)

[Cree XLamp XQ-E HI Red](#)



[Cree XLamp XQ-E HI White](#)

Eff: 83  
FWHM: 7  
Cd/lm: 29.84



[View](#)



[Cree XLamp XR White](#)

Eff: 85.4  
FWHM: 15  
Cd/lm: 7.9

[View](#)



[Cree XLamp XR-C White](#)

Eff: 85.4  
FWHM: 11  
Cd/lm: 20.4

[View](#)



[Cree XLamp XR-E White](#)


Eff: 84.9  
FWHM: 11  
Cd/lm: 14.5

[View](#)



[Cree XLamp XT-E HE White](#)

Eff: 85  
FWHM: 12  
Cd/lm: 12.6



[View](#)



[Cree XLamp XTE White](#)

FWHM: 11  
Cd/lm: 18.2



[View](#)




[Everlight Shuen White](#)

Eff: 84.8  
FWHM: 12  
Cd/lm: 15.1




[View](#)



[LEDEngin 3W White](#)

Eff: 81.8  
FWHM: 15  
Cd/lm: 8.8




[View](#)



[LEDEngin 5W White](#)

Eff: 81.3  
FWHM: 14  
Cd/lm: 10.4




[View](#)



[LG 3535LG White](#)

Eff: 87.8  
FWHM: 11  
Cd/lm: 20.9




[View](#)



[Lite-On R38386AS - S R38 IR](#)

Eff: 85  
FWHM: 11  
Cd/lm: 16




[View](#)



[LUMILEDS LUXEON 3030 White](#)

Eff: 81  
FWHM: 9  
Cd/lm: 20.75




[View](#)



[LUMILEDS LUXEON 3535 HV White](#)

Eff: 83.1  
FWHM: 9  
Cd/lm: 21.33





[View](#)



[LUMILEDS LUXEON 3535 L White](#)

Eff: 83  
FWHM: 9  
Cd/lm: 20.1




[View](#)



[LUMILEDS LUXEON 3535L Blue](#)

Eff: 85.5  
FWHM: 11  
Cd/lm: 14.4





[View](#)



[LUMILEDS LUXEON 3535L Green](#)

Eff: 85.5  
FWHM: 11  
Cd/lm: 14.7




[View](#)



[LUMILEDS LUXEON 3535L Red](#)

Eff: 85.5  
FWHM: 10  
Cd/lm: 18.3




[View](#)



[LUMILEDS LUXEON 5050 White](#)

Eff: 85.5  
FWHM: 18  
Cd/lm: 6.7




[View](#)



[LUMILEDS LUXEON C Blue](#)

Eff: 80.5  
FWHM: 10  
Cd/lm: 16.7




[View](#)



[LUMILEDS LUXEON C Lime](#)

Eff: 81.5  
FWHM: 11  
Cd/lm: 16.4



[View](#)




[LUMILEDS LUXEON C Red](#)

Eff: 79.5  
FWHM: 12  
Cd/lm: 13.3




[View](#)



[LUMILEDS LUXEON C White](#)

Eff: 80.7  
FWHM: 9  
Cd/lm: 9.1




[View](#)



[LUMILEDS LUXEON CSP 05 White](#)

Eff: 81  
FWHM: 8  
Cd/lm: 22.4





[View](#)



[LUMILEDS LUXEON CSP 10 White](#)

Eff: 65  
FWHM: 9  
Cd/lm: 15.22




[View](#)

Eff: 85.5



[LUMILEDS LUXEON CZ](#)

FWHM: 9  
Cd/lm: 21.9



[View](#)



[LUMILEDS LUXEON IR Compact 850nm](#)

Eff: 84.5  
FWHM: 10  
Cd/lm: 17.7




[View](#)



[LUMILEDS LUXEON IR Domed 60 Degree](#)

Eff: 83  
FWHM: 12  
Cd/lm: 13.4



[View](#)



[LUMILEDS LUXEON IR Domed 90 Degree](#)

Eff: 84  
FWHM: 11  
Cd/lm: 15.7




[View](#)





[LUMILEDS LUXEON M White](#)

FWHM: 22  
Cd/lm: 5



[View](#)



[LUMILEDS LUXEON MX White](#)

Eff: 84  
FWHM: 20  
Cd/lm: 4.4




[View](#)



[LUMILEDS LUXEON MZ White](#)

Eff: 83.8  
FWHM: 14  
Cd/lm: 8.5




[View](#)



[LUMILEDS LUXEON Q White](#)

Eff: 81.3  
FWHM: 10  
Cd/lm: 17.1




[View](#)



[LUMILEDS LUXEON R White](#)

Eff: 83  
FWHM: 12  
Cd/lm: 16.4




[View](#)



[LUMILEDS LUXEON Rebel ES White](#)

Eff: 83  
FWHM: 12  
Cd/lm: 16.4



[View](#)



[LUMILEDS LUXEON Rebel White](#)

Eff: 82.4  
FWHM: 10  
Cd/lm: 17.9




[View](#)



[LUMILEDS LUXEON T White](#)


Eff: 83  
FWHM: 12  
Cd/lm: 16.4



[View](#)




Eff: 82.7  
FWHM: 10  
Cd/lm: 18.9




[View](#)

[LUMILEDS LUXEON TX White](#)



[LUMILEDS LUXEON V White](#)

Eff: 83  
FWHM: 16  
Cd/lm: 7.8




[View](#)



[LUMILEDS LUXEON V2 White](#)

Eff: 85  
FWHM: 13  
Cd/lm: 12





[View](#)



[LUMILEDS LUXEON Z ES White](#)

Eff: 83  
FWHM: 8  
Cd/lm: 26.54





[View](#)



[LUMILEDS LUXEON Z White](#)

Eff: 82.8  
FWHM: 7  
Cd/lm: 32.5



[View](#)



[Nichia 219 White](#)

Eff: 80.1  
FWHM: 12  
Cd/lm: 17.6




[View](#)



[Nichia 229A White](#)

Eff: 83.5  
FWHM: 16  
Cd/lm: 7.9




[View](#)



[Nichia 757G White](#)

Eff: 85.5  
FWHM: 12  
Cd/lm: 13





[View](#)



[Nichia NCSW E17A White](#)

Eff: 85  
FWHM: 10  
Cd/lm: 17.9




[View](#)



[Nichia NF2W 385AR-V2 White](#)

Eff: 85.5  
FWHM: 13  
Cd/lm: 12




[View](#)



[Nichia NFMW 481AR White](#)

Eff: 7  
FWHM: 17  
Cd/lm: 5.6




[View](#)



[Nichia NFMW 484AR White](#)

Eff: 85.5  
FWHM: 19  
Cd/lm: 5.7




[View](#)



[Nichia NFMW 486AR White](#)

Eff: 85.5  
FWHM: 18  
Cd/lm: 6.2




[View](#)



[Nichia NFMW 488AR White](#)

Eff: 85.5  
FWHM: 18  
Cd/lm: 5.8




[View](#)



[Nichia NV4W 144AR White](#)

Eff: 80.5  
FWHM: 21  
Cd/lm: 4.6



[View](#)












[Nichia NVSL 219B White](#)

Eff: 84.5  
FWHM: 11  
Cd/lm: 15.4




[View](#)

				
	<a href="#">Nichia NVSW 219C White</a>	Eff: 84.5 FWHM: 13 Cd/lm: 11.8	 	<a href="#">View</a>
	<a href="#">Nichia NVSW 319A White</a>	Eff: 84 FWHM: 14 Cd/lm: 10.3	 	<a href="#">View</a>
	<a href="#">Nichia NVSW E21A White</a>	Eff: 81 FWHM: 9 Cd/lm: 23.6	 	<a href="#">View</a>
		Eff: 83		



[Nichia Top Emitting NCSL 119-H3 White](#)

FWHM: 10  
Cd/lm: 19.1




[View](#)



[Nichia Top Emitting NFSW 036 White](#)

Eff: 84.6  
FWHM: 10  
Cd/lm: 16.4




[View](#)



[Nichia Top Emitting NS3W 183T White](#)

Eff: 82.4  
FWHM: 16  
Cd/lm: 8.6




[View](#)



[Osram OS DURIS E 2835 White](#)

Eff: 85.5  
FWHM: 12  
Cd/lm: 13.9




[View](#)



**OSRAM**  
Opto Semiconductors

[Osram OS DURIS E2 White](#)

Eff: 83  
FWHM: 8  
Cd/lm: 28.34





[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS E3 White](#)

Eff: 86.6  
FWHM: 8  
Cd/lm: 27.3




[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS P10 White](#)

Eff: 83.9  
FWHM: 17  
Cd/lm: 5.4



[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS P8 White](#)

Eff: 83.2  
FWHM: 10  
Cd/lm: 19.4





[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S10 White](#)

Eff: 85  
FWHM: 21  
Cd/lm: 3.9





[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S2 White](#)

Eff: 87.1  
FWHM: 9  
Cd/lm: 21.5




[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S5 Deep Blue](#)

Eff: 85.5  
FWHM: 12  
Cd/lm: 14.2





[View](#)

Eff: 85.5

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S5 Green](#)

FWHM: 11  
Cd/lm: 15.3




[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S5 Red](#)

Eff: 85.5  
FWHM: 11  
Cd/lm: 16.7





[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S5 White](#)

Eff: 83  
FWHM: 9  
Cd/lm: 19.75




[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S8 Gen2 White](#)

Eff: 88  
FWHM: 18  
Cd/lm: 7.21




[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS DURIS S8 White](#)

Eff: 87.71  
FWHM: 18  
Cd/lm: 6.57




[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS Osconiq P3737 White](#)

Eff: 83  
FWHM: 14  
Cd/lm: 9.6




[View](#)

**OSRAM**  
Opto Semiconductors

[Osram OS OSLOM Black SFH 4725S IR](#)

Eff: 92  
FWHM: 11  
Cd/lm: 18.2



[View](#)

**OSRAM**  
Opto Semiconductors


[Osram OS OSLOM Pure CSP GW VJLPE 1](#)

Eff: 85.5  
FWHM: 9  
Cd/lm: 22.7



[View](#)


White




**OSRAM**  
Opto Semiconductors

Osram OS OSLOON Square Flat White

Eff: 85  
FWHM: 11  
Cd/lm: 16.6




[View](#)




**OSRAM**  
Opto Semiconductors

Osram OS OSLOON Square Gen 3 White

Eff: 83  
FWHM: 10  
Cd/lm: 19.4




[View](#)




**OSRAM**  
Opto Semiconductors

Osram OS OSLOON Square White

Eff: 82  
FWHM: 10  
Cd/lm: 19.3




[View](#)






[Osram OS OSLON SSL 80 degree White](#)

Eff: 84.7  
FWHM: 10  
Cd/lm: 20.2




[View](#)



[Plessey PLW 7070GA White](#)

Eff: 83.5  
FWHM: 22  
Cd/lm: 4.2



[View](#)



[Samsung 3535 LH351A White](#)

FWHM: 12  
Cd/lm: 18.3




[View](#)



[Samsung 3535 LH351B White](#)

Eff: 83  
FWHM: 11  
Cd/lm: 16




[View](#)



[Samsung 3535 LH351D White](#)

Eff: 84.5  
FWHM: 16  
Cd/lm: 8.5





[View](#)



[Samsung 3535 LH351Z White](#)

Eff: 83  
FWHM: 9  
Cd/lm: 20.16




[View](#)



[Samsung CSP LH181B White](#)

Eff: 85.5  
FWHM: 12  
Cd/lm: 13.8



[View](#)




[Samsung CSP LH231B White](#)

Eff: 85.5  
FWHM: 13  
Cd/lm: 11.4



[View](#)




[Samsung CSP LM101B White](#)

Eff: 85.5  
FWHM: 10  
Cd/lm: 18.3



[View](#)




[Samsung WH5 White](#)

Eff: 85.2  
FWHM: 14  
Cd/lm: 9



[View](#)




[Seoul CSP SZ8Y22 White](#)

Eff: 85.5  
FWHM: 13  
Cd/lm: 11.8



[View](#)








[Seoul CSP SZ8Y22P White](#)

Eff: 85.5  
FWHM: 14  
Cd/lm: 11




[View](#)



[Seoul CSP SZ8Y50 White](#)

Eff: 85.5  
FWHM: 23  
Cd/lm: 4.2





[View](#)



[Seoul MidPower MJT3030 White](#)

Eff: 83  
FWHM: 9  
Cd/lm: 19



[View](#)



[Seoul MidPower MJT4040 White](#)

Eff: 83.6  
FWHM: 12  
Cd/lm: 11.44





[View](#)



[Seoul MJT 5050 White](#)

Eff: 83.2  
FWHM: 14  
Cd/lm: 9.9




[View](#)



[Seoul P4 White](#)

Eff: 85.5  
FWHM: 12  
Cd/lm: 12.4




[View](#)



[Seoul P4 White](#)

Eff: 82.13  
FWHM: 12  
Cd/lm: 12.8




[View](#)



[Seoul SZ8Y11 White](#)

Eff: 84.5  
FWHM: 11  
Cd/lm: 17.3





[View](#)



[Seoul SZ8Y15 White](#)

Eff: 86  
FWHM: 10  
Cd/lm: 19.9





[View](#)



[Seoul SZ8Y19 White](#)

Eff: 83  
FWHM: 11  
Cd/lm: 15.19




[View](#)



[Seoul Z - Power Z5M White](#)

Eff: 83.7  
FWHM: 11  
Cd/lm: 19.9



[View](#)



[SSC Z - Power Z1 White](#)

Eff: 83.7  
FWHM: 16  
Cd/lm: 7




[View](#)



[SSC Z - Power Z5 White](#)

Eff: 84.7  
FWHM: 9  
Cd/lm: 23.7




[View](#)



[SSC Z - Power Z5P White](#)

FWHM: 11  
Cd/lm: 20.5




[View](#)



[Stanley 1N White](#)

Eff: 81.3  
FWHM: 15  
Cd/lm: 8.7




[View](#)

**STANLEY**

[Stanley 6J White](#)

Eff: 84  
FWHM: 18  
Cd/lm: 7.5




[View](#)

**STANLEY**

[Stanley 6J White](#)

Eff: 83  
FWHM: 18  
Cd/lm: 6.49




[View](#)

**TOSHIBA**

[Toshiba TL 1L2 White](#)

Eff: 82  
FWHM: 10  
Cd/lm: 17.6




[View](#)

**TOSHIBA**

[Toshiba TL 1L4 White](#)

Eff: 82  
FWHM: 10  
Cd/lm: 17.4



[View](#)

