

Hammer drill driver XR 18V 1.7Ah Li-Ion Brushless - POWERSTACK renforcée DCD85ME2GT-QW

McLaren
FORMULA 1 TEAM

DEWALT

OFFICIAL TOOLS AND STORAGE PARTNER

13 mm Self Clamping Metal Chuck: Heavy Duty Chuck

- Variable speed trigger allows speed control
- Swivel LEDs: better visibility in dark and confined spaces
- 15 Torque control settings: precise adjustment of the clamping force. User can adapt the tool to desired performance and finish
- Brushless engine: more power, efficiency and durability
- Ergonomic handle: more comfortable for longer life
- Reinforced Battery: Glass Reinforced Nylon Coating:

More resistant coating against fuels, greases and some petrochemicals.
Robust design and non-marking coating

battery type	1.7Ah Li-Ion
Chuck capacity	1.5-13 mm
No load speed	0-650/2000 tr/min
Hard/soft torque	90 / 27 Nm
Impact rate	0-34000 cps/min
Chuck type	Métal
∅ wood/metal/concrete drilling	55 / 13 / 13 mm
Torque setting	15
Weight	1.64 kg
Gencod	5035048807903

LIMITED EDITION McLaren*



POWERSTACK™

18V XR TSTAK™

DEWALT
3 ANS DE GARANTIE
UNIVERSITÄT LA MITTLE BRUNNEN LES 4
GARANTIES DES JOURS SUIVANT L'ACHAT
RENDEZ-VOUS SUR WWW.DEWALT.FR/FORMULA1

Standard Equipment :

2 reinforced POWERSTACK batteries, charger, belt clip, magnetic bit holder, TSTAK box.

* Within available stocks