

Temperature Switch with Selectable Hysteresis


Features

- · Factory Set Temperature Switch
- · Available Temperature Switch Thresholds:
 - T_{SET} = -35°C,-25°C, -15°C, -5°C, 5°C, 15°C, 25°C, 35°C, 45°C, 55°C, 65°C, 75°C, 85°C, 95°C, 105°C, 115°C, 125°C
- Wide Operating Voltage Range: 2.7V to 5.5V
- Low Supply Current: 25 μA (typical)
- Temperature Switch Accuracy:
 - ±1°C (typical)
 - ±4°C (maximum) -15°C to +75°C
 - ±6°C (maximum) -40°C to +125°C
- Switch Threshold Options (Hot/Cold):
 - Rising Temp.: MCP9501/2 (Hot Option)
 - Falling Temp.: MCP9503/4 (Cold Option)
- Output Configuration Options:
 - Active Low, Open-Drain Output: MCP9501/3
 - Uses External Pull-up Resistor
 - Active-High, Push-Pull Output: MCP9502/4
- User Selectable Hysteresis: 2°C or 10°C (typical)
- · 5-lead SOT-23 package

Applications

- Power Supply Critical Temperature Shutdown
- · Temperature Alarm
- Thermostat Control
- Fan Control
- Base-Stations
- Automotive

Typical Performance




Description

Microchip Technology's MCP9501/2/3/4 family of devices are temperature switches with $\pm 1^{\circ} C$ (typical) accurate factory set output thresholds. These devices are ideal for high power supply systems where an overtemperature protection circuit is needed. These devices do not require external components, consume 25 μA (typical), and the factory set thresholds provide simplicity.

In addition, this family of devices provide user selectable 2°C and 10°C (typical) switch hysteresis, and various output configurations. The MCP9501/2 outputs switch for rising temperatures while the MCP9503/4 switch for falling temperature, with the relative hysteresis at the set thresholds. This family of devices is also available with Active-High Push-Pull and Active-Low Open-Drain outputs, the MCP9502/4 and the MCP9501/3, respectively. The Push-Pull output is ideal for a microcontroller interface while the Open-Drain output can be used for level shifting, wired-OR configuration, or as a heater on/off switch.


The MCP9501/2/3/4 operate from 2.7V to 5.5V supply. This family is available with space saving 5-lead SOT-23 package.

Package Types




OUTPUT FUNCTIONAL DESCRIPTION

MCP9501, Hot-Option (Open-Drain, Active-Low)




Available temperature thresholds for Option P or for rising temperature only: +5°C, +15°C, +25°C, +35°C, +45°C, +55°C, +65°C, +75°C, +85°C, +95°C, +105°C, +115°C, +125°.

MCP9502, Hot-Option (Push-Pull, Active-High)



Available temperature thresholds for Option P or for rising temperature only: +5°C, +15°C, +25°C, +35°C, +45°C, +55°C, +65°C, +75°C, +85°C, +95°C, +105°C, +115°C, +125°.

MCP9503, Cold-Option (Open-Drain, Active-Low)



Available temperature thresholds for Option P or for rising temperature only:


+5°C, +15°C, +25°C.

Available temperature thresholds for Option N or for falling temperature only:

-35°C, -25°C, -15°C, -5°C.

Temperature

MCP9504, Cold-Option (Push-Pull, Active-High)



Available temperature thresholds for Option P or for rising temperature

only: +5°C, +15°C, +25°C.

Available temperature thresholds for Option N or for falling temperature only: -35°C, -25°C, -15°C, -5°C.

Contact Microchip for all other

threshold options.

1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

V _{DD}	6.0V
Voltage at all Input/Output pins	GND – 0.3V to 6.0V
Input/Output Current	20 mA
Storage temperature	65°C to +150°C
Ambient temp. with power applied	40°C to +125°C

Junction Temperature (T _J)+15	0°C
ESD protection on all pins (HBM:MM) (4 kV/40	0V)
Latch-Up Current at each pin (25°C) ±200	mΑ

†Notice: Stresses above those listed under "Maximum ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

DC CHARACTERISTICS

Electrical Specifications: Unless otherwise indicated, $V_{DD} = 2.7V$ to 5.5V, $T_A = -40^{\circ}C$ to +125°C, and GND = Ground.									
Parameters	Sym	Min	Тур	Max	Unit	Conditions			
Sensor Accuracy									
-15 °C \leq T _A \leq +75°C		-4	±1	+4	°C	Note 1			
-40 °C $\leq T_A \leq +125$ °C		-6	±2	6	°C				
Power Supply									
Operating Voltage	V_{DD}	2.7	_	5.5	V				
Operating Current	I _{DD}	_	25	40	μΑ				
Line-Regulation	Δ°C/ΔV	1	0.2	_	°C/V	$V_{DD} = 2.7V \text{ to } 5.5V$			
Hysteresis									
Trip Point Hysteresis	T _{HYST}		2		°C	HYST = GND			
			10	_	°C	HYST = V _{DD}			
Hysteresis Select Input	V_{IH}	$0.8V_{DD}$	_	_	V				
	V_{IL}	1	_	0.2V _{DD}	V				
	I _{Leak}	1	0.1		μΑ				
Open-Drain Output Leakage	I _{Leak}	1	0.1	10	μΑ	MCP9501/3			
Output Voltage High	V _{OH}	$0.8V_{DD}$	_	_	V	$I_{OUT} = 5 \text{ mA (MCP9502/4)}$			
Output Voltage Low	V_{OL}		_	0.2V _{DD}	V	I _{OUT} = 5 mA			
Turn On Time	T _{ON}		1	_	ms				
SOT23-5	t _{RES}	_	1.7	_	S	Time to 63% (89°C). +25°C (Air) to +125°C (oil bath)			

Note 1: This specification is tested at mid supply of 4.1V for optimum operation across the supply voltage range of 2.7V to 5.5V.

TEMPERATURE CHARACTERISTICS

Electrical Specifications: Unless otherwise indicated, $V_{DD} = 2.7V$ to 5.5V, $T_A = -40$ °C to +125°C, and GND = Ground.							
Parameters	Sym	Min	Тур	Max	Units	Conditions	
Temperature Ranges							
Specified Temperature Range	T _A	-40	_	+125	°C	(Note 1)	
Operating Temperature Range	T _A	-40	_	+125	°C		
Storage Temperature Range T _A -65 — +150 °C							
Thermal Package Resistances							
Thermal Resistance, 5L-SOT23	$\theta_{\sf JA}$		220.7	_	°C/Ω		

Note 1: Operation in this range must not cause T_J to exceed Maximum Junction Temperature (+150°C).

2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.

Note: Unless otherwise indicated, V_{DD} = 2.7V to 5.5V, T_A = -40°C to +125°C, GND = Ground, $R_{PULL-UP}$ = 10 k Ω (MCP9501/3 only) and 0.1 μ F bypass capacitor.




FIGURE 2-1: Temperature Accuracy.




FIGURE 2-2: Hysteresis vs. Temperature.




FIGURE 2-3: Supply Current vs. Temperature.




FIGURE 2-4: Leakage vs. Temperature.




FIGURE 2-5: V_{OL}, V_{OH} vs. Temperature.




FIGURE 2-6: Power On Reset Threshold vs. Temperature.

Note: Unless otherwise indicated, V_{DD} = 2.7V to 5.5V, T_A = -40°C to +125°C, GND = Ground, $R_{PULL-UP}$ = 10 k Ω (MCP9501 only) and 0.1 μ F bypass capacitor.




FIGURE 2-7: Temperature Accuracy Distribution at -15°C.




FIGURE 2-8: Temperature Accuracy Distribution at 5°C.




FIGURE 2-9: Temperature Accuracy Distribution at 65°C.




FIGURE 2-10: Temperature Accuracy Distribution at 105°C.




FIGURE 2-11: Temperature Accuracy Distribution at 115°C.




FIGURE 2-12: Temperature Accuracy Distribution at 125°C.

3.0 PIN DESCRIPTIONS

TABLE 3-1: PIN FUNCTION TABLE

MCP9501/2/3/4	Cumbal	Description	
SOT-23-5	Symbol	Description	
1	GND	Ground	
2	GND	Ground (must be connected to ground)	
3	HYST	Hysteresis Selection Input:	
		HYST = GND → Hysteresis is 2°C (typical)	
		HYST = V _{DD} → Hysteresis is 10°C (typical)	
4	V_{DD}	Power pin	
5	Output	Output Options:	
		MCP9501 → Open-Drain, Active-Low Output (Hot-Option)	
		MCP9502 → Push-Pull, Active-High Output (Hot-Option)	
		MCP9503 → Open-Drain, Active-Low Output (Cold-Option)	
		MCP9504 → Push-Pull, Active-High Output (Cold-Option)	

3.1 Ground (GND)

The GND pin is the system ground pin. Pin 2 must be connected to system ground. Pin 1 can also be connected to system ground which would provide better thermal conduction to the die.

3.2 Hysteresis Input (HYS)

This is an input pin which can be connected to V_{DD} or GND to select output hysteresis. Either 2°C (HYST = GND) or 10°C (HYST = V_{DD}) of typical hysteresis can be selected.

3.3 Power Pin (V_{DD})

The operating voltage range, as specified in the DC electrical specification table, is applied on this pin.

3.4 Switch Output (Output)

This output is triggered when temperature rises or falls beyond the programmed trip temperature threshold. MCP9501/3 require an external pull-up resistor.

4.0 FUNCTIONAL DESCRIPTION

The MCP9501/2/3/4 temperature switch family integrates a thermal diode, a comparator, and a factory selectable resistive network used to set the temperature thresholds. The available output thresholds range from -35°C to 125°C at 10°C increments. There is no additional configuration required to operate this device. The selectable output hysteresis is controlled using a single input pin. When this pin is connected to ground, the output hysteresis is 2°C (typical) and when connected to V_{DD} the output hysteresis is 10°C (typical). Figure 4-1 shows the functional block diagram.




FIGURE 4-1: Functional Block Diagram.

There are two output configurations for this family, a push-pull and an open-drain output with active-high and active-low assertions. These assertion options are referred to as Cold and Hot options, primarily due to the direction of selected hysteresis. For the Cold option, temperature has to fall below the threshold for the output to assert High, and de-assert Low when the temperature rises above the threshold plus the hysteresis. For example, a 65°C threshold and 2°C (typical) hysteresis, when temperature falls below 65°C the output asserts High, and the de-asserts Low when temperature rises above 67°C. For the Hot option, the opposite is true. When temperature rises above 65°C, the output asserts Low, and de-asserts High when the temperature falls below 63°C. Figure 4-2 shows a graphical description for the Hot and Cold options.




FIGURE 4-2: Output Hysteresis.

The Push-Pull output is ideal for a microcontroller interface using an input/output pin or an interrupt input pin. The open-drain option can be used with multiple sensors in a wired-OR configuration or as a level shifter.

4.1 Application Information

The MCP9501/2/3/4 temperature switch family integrates a temperature sensor and a comparator circuit which outputs an alert signal when the factory set temperature threshold is exceeded. No additional component is required for device operation, which provides simplicity to the system designer. The device output options provide design flexibility for various applications such as overtemperature protection circuit or a closed loop temperature control unit. This device can be interfaced to a closed loop fan controller network without the need for a microcontroller.




FIGURE 4-3: Fan Controller Using MCP9502.

The MCP9501/2/3/4 provide Open-Drain output where multiple sensors from multiple PCB hot-spots can be connected to a single processor I/O input with a wired-OR configuration. The MCP9501 requires an external pull-up resistor which can be used to level-shift the alert signal. For example, if the sensors are powered with $5V_{DD}$ and the controller or processor is powered with $3V_{DD}$, the external resistor can be level-shifted by connecting $3V_{DD}$ to the pull-up resistor as shown in Figure 4-4.




FIGURE 4-4: MCP9501 Wired-OR Output Configuration with Level-shift.

4.1.1 LAYOUT CONSIDERATION AND THERMAL CONSIDERATION

This family of sensors measures temperature by monitoring the voltage level of a thermal diode located in the die. A low-impedance thermal path between the die and the PCB is provided by the pins. Therefore, the sensor effectively monitors PCB temperature. For efficient performance, it is recommended to layout the device as close to the heat source as possible.

When connecting an external resistor to the MCP9501/3, the current through the pull-up resistor must be considered to prevent self-heat due to power. This can be determined using Equation 4-1.

EQUATION 4-1: EFFECT OF SELF-HEATING

$$T_{J} - T_{A} = \theta_{JA}(V_{DD} \times I_{DD} + V_{OL} \times I_{OUT})$$
 Where:
$$T_{J} = \text{Junction Temperature}$$

$$T_{A} = \text{Ambient Temperature}$$

$$\theta_{JA} = \text{Package Thermal Resistance}$$

$$(220.7 \text{ °C/W})$$

$$V_{OL} = \text{Sensor Output Low Voltage}$$

$$I_{OUT} = \text{Output Current}$$

For example, at room temperature, when the output asserts Active-Low and maximum $I_{DD}=50\,\mu\text{A},$ $V_{DD}=5.5\text{V},$ $V_{OL}=0.3\text{V}$ and $I_{OUT}=5\,\text{mA}$ (see the specification table), the self heating due to power dissipation (T_J - T_A) is ~0.4°C.

4.1.2 POWER SUPPLY REJECTION

The MCP9501/2/3/4 family does not require any additional components. However, it is recommended that a decoupling capacitor of 0.1 μF to 1 μF be used between the V_{DD} and GND pins. A high-frequency ceramic capacitor is recommended. It is necessary for the capacitor to be located as close as possible to the power pins in order to provide effective noise protection.




FIGURE 4-5: Power-supply Filter using a Single Resistor.

For applications where a switching regulator is used to power the sensor, it is recommended to add a 200Ω resistor in series to V_{DD} to filter out the switcher noise. It is also recommended to add the series resistor in applications where a linear regulator is used to step-down a switching regulator voltage to power the sensor, as shown in Figure 4-5. For example, if a linearly regulated 3.3V from a 5V switching regulator is used to power the sensor, add a 200Ω series resistor.

The MCP9501/2/3/4 family of sensors is designed to prevent false output trigger due to high frequency power supply or system noise. Figure 4-6 shows the device performance with a high frequency signal added on $V_{DD}.$ The output is not triggered due to the signal added on $V_{DD}.$ With some applications, it is recommended to add a bypass capacitor of 0.1 μF to 1 $\mu F.$





FIGURE 4-6: Power Supply Rejection.

N	Ο.	TC	-0	
IV	u	ıc	_ •	_


5.0 PACKAGING INFORMATION

5.1 Package Marking Information

5-Lead SOT-23







Device Code		Device	Code					
Hot Options								
MCP9501PT-005E/OT	WVNN	MCP9502PT-005E/OT	XLNN					
MCP9501PT-015E/OT	WWNN	MCP9502PT-015E/OT	XMNN					
MCP9501PT-025E/OT	WXNN	MCP9502PT-025E/OT	XPNN					
MCP9501PT-035E/OT	WYNN	MCP9502PT-035E/OT	XQNN					
MCP9501PT-045E/OT	WZNN	MCP9502PT-045E/OT	XRNN					
MCP9501PT-055E/OT	X1NN	MCP9502PT-055E/OT	XSNN					
MCP9501PT-065E/OT	X2NN	MCP9502PT-065E/OT	XTNN					
MCP9501PT-075E/OT	X3NN	MCP9502PT-075E/OT	XUNN					
MCP9501PT-085E/OT	X4NN	MCP9502PT-085E/OT	XVNN					
MCP9501PT-095E/OT	X5NN	MCP9502PT-095E/OT	XWNN					
MCP9501PT-105E/OT	X6NN	MCP9502PT-105E/OT	XXNN					
MCP9501PT-115E/OT	X7NN	MCP9502PT-115E/OT	XYNN					
MCP9501PT-125E/OT	X8NN	MCP9502PT-125E/OT	XZNN					
MCP9503PT-005E/OT	XHNN	MCP9501PT-005E/OT	Y9NN					
MCP9503PT-015E/OT	XJNN	MCP9501PT-015E/OT	YANN					
MCP9503PT-125E/OT	XKNN	MCP9501PT-025E/OT	YBNN					
Cold Options								
MCP9503NT-005E/OT	XBNN	MCP9501NT-005E/OT	Y3NN					
MCP9503NT-015E/OT	XCNN	MCP9501NT-015E/OT	Y4NN					
MCP9503NT-025E/OT	XDNN	MCP9501NT-025E/OT	Y5NN					
MCP9503NT-035E/OT	XENN	MCP9501NT-035E/OT	Y6NN					

Note: Contact Microchip for all other threshold options.

Legend: XX...X Customer-specific information

Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code


e3 Pb-free JEDEC designator for Matte Tin (Sn)

This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.

Note: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information.

5-Lead Plastic Small Outline Transistor (OT) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units			MILLIMETERS			
Dimension	on Limits	MIN	NOM	MAX			
Number of Pins	N		5				
Lead Pitch	е		0.95 BSC				
Outside Lead Pitch	e1		1.90 BSC				
Overall Height	Α	0.90	_	1.45			
Molded Package Thickness	A2	0.89	_	1.30			
Standoff	A1	0.00	_	0.15			
Overall Width	Е	2.20	_	3.20			
Molded Package Width	E1	1.30	_	1.80			
Overall Length	D	2.70	_	3.10			
Foot Length	L	0.10	_	0.60			
Footprint	L1	0.35	_	0.80			
Foot Angle	ф	0°	_	30°			
Lead Thickness	С	0.08	_	0.26			
Lead Width	b	0.20	-	0.51			

Notes:


- 1. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.127 mm per side.
- 2. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-091B

5-Lead Plastic Small Outline Transistor (OT) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension	Limits	MIN	MOM	MAX
Contact Pitch	Е			
Contact Pad Spacing	С		2.80	
Contact Pad Width (X5)	Х			0.60
Contact Pad Length (X5)	Υ			1.10
Distance Between Pads	G	1.70		
Distance Between Pads	GX	0.35		
Overall Width	Z			3.90

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2091A

APPENDIX A: REVISION HISTORY

Revision A (January 2011)

• Original Release of this Document.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NOXX	xxx x	/XX	Exa	imples:
•	 erature Temperature Threshold Range	Package	a)	MCP9501PT-025E/OT: Active-Low, Open-Drain Output, 25°C Switch Threshold, Hot Option,
Device:	MCP9502P Hot Option MCP9503N: Resistor Progr Hot Option Resistor Progr Cold Option	rammable Temperature Switch, rammable Temperature Switch, n rammable Temperature Switch,	b)	Extended Temp., 5LD SOT-23 pkg. MCP9502PT-025E/OT: Active-High, Push-Pull Output, 25°C Switch Threshold, Hot Option, Extended Temp., 5LD SOT-23 pkg.
Temperature Switch Threshold: Temperature Range:	005, 015, 025, 035, 045, 05, 115, 125 E = -40°C to +125°C	5, 065, 075, 085, 095, 105,	c)	MCP9503NT-025E/OT: Active-Low, Open-Drain Output, -25°C Switch Threshold, Cold Option, Extended Temp.,
Package:	OT = Plastic Small Outline	e Transistor (SOT-23), 5-lead	d)	5LD SOT-23 pkg. MCP9504NT-025E/OT: Active-High, Push-Pull Output, -25°C Switch Threshold, Cold Option, Extended Temp.,
			e)	5LD SOT-23 pkg. MCP9501PT-105E/OT: Active-Low, Open-Drain Output, 105°C Switch Threshold, Hot Option, Extended Temp., 5LD SOT-23 pkg.
			f)	MCP9502PT-105E/OT: Active-High, Push-Pull Output, 105°C Switch Threshold, Hot Option, Extended Temp., 5LD SOT-23 pkg.
			g)	MCP9503NT-035E/OT: Active-Low, Open-Drain Output, -35°C Switch Threshold, Cold Option, Extended Temp., 5LD SOT-23 pkg.
			h)	MCP9504NT-035E/OT: Active-High, Push-Pull Output, -35°C Switch Threshold, Cold Option, Extended Temp., 5LD SOT-23 pkg.

NOTES:

Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the
 intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our
 knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data
 Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

Trademarks

The Microchip name and logo, the Microchip logo, dsPIC, Keeloq, Keeloq logo, MPLAB, PIC, PICmicro, PICSTART, PIC³² logo, rfPIC and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

FilterLab, Hampshire, HI-TECH C, Linear Active Thermistor, MXDEV, MXLAB, SEEVAL and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, HI-TIDE, In-Circuit Serial Programming, ICSP, Mindi, MiWi, MPASM, MPLAB Certified logo, MPLIB, MPLINK, mTouch, Octopus, Omniscient Code Generation, PICC, PICC-18, PICDEM, PICDEM.net, PICkit, PICtail, REAL ICE, rfLAB, Select Mode, Total Endurance, TSHARC, UniWinDriver, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2011, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Printed on recycled paper.

ISBN: 978-1-60932-861-0

QUALITY MANAGEMENT SYSTEM

CERTIFIED BY DNV

ISO/TS 16949:2002

Microchip received ISO/TS-16949:2002 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.



Worldwide Sales and Service

AMERICAS

Corporate Office

2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://support.microchip.com Web Address:

www.microchip.com

Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Cleveland

Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

Dallas

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit

Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Kokomo

Kokomo, IN Tel: 765-864-8360 Fax: 765-864-8387

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara

Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

Toronto

Mississauga, Ontario,

Canada

Tel: 905-673-0699 Fax: 905-673-6509 ASIA/PACIFIC

Asia Pacific Office

Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon Hong Kong

Tel: 852-2401-1200 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733

Fax: 61-2-9868-6755 China - Beijing

Tel: 86-10-8528-2100 Fax: 86-10-8528-2104

China - Chengdu Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing

Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Hong Kong SAR

Tel: 852-2401-1200 Fax: 852-2401-3431

China - Nanjing

Tel: 86-25-8473-2460 Fax: 86-25-8473-2470

China - Qingdao

Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai

Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang

Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen

Tel: 86-755-8203-2660 Fax: 86-755-8203-1760

China - Wuhan

Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian

Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

China - Xiamen

Tel: 86-592-2388138 Fax: 86-592-2388130

China - Zhuhai

Tel: 86-756-3210040 Fax: 86-756-3210049 ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi

Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune

Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

Japan - Yokohama

Tel: 81-45-471-6166 Fax: 81-45-471-6122

Korea - Daegu

Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul

Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur

Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang

Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila

Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore

Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu

Tel: 886-3-6578-300 Fax: 886-3-6578-370

Taiwan - Kaohsiung

Tel: 886-7-213-7830 Fax: 886-7-330-9305

Taiwan - Taipei

Tel: 886-2-2500-6610 Fax: 886-2-2508-0102

Thailand - Bangkok

Tel: 66-2-694-1351 Fax: 66-2-694-1350 **EUROPE**

Austria - Wels

Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen

Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris

Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Munich

Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan

Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen

Tel: 31-416-690399 Fax: 31-416-690340

Spain - Madrid

Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

UK - Wokingham Tel: 44-118-921-5869

Fax: 44-118-921-5869

08/04/10